

SOLIS
Price and Specification Guide
GSA
GS-03F-084DA



TERMS & CONDITIONS | INFORMATION FOR ORDERING ACTIVITIES

General Services Administration Federal Supply Schedule

FSC Groups 7110, 7125
 Subcategory: Furniture
 CONTRACT NUMBER: GS-03F-084DA
 CONTRACT PERIOD: April 1, 2016 through March 31, 2026
 CONTRACTOR/ ADMINISTRATOR: Mira Jaksic-Husic
 Krug Inc.
 421 Manitou Drive
 Kitchener, Ontario, Canada
 Tel: 1-800-265-2796
 Fax: 1-800-265-2798

1. List of Special Item Numbers on Contract

33721P Packaged Office Furniture w Ancillary Installation Services
 33721 Office Furniture w Ancillary Installation Services
 339113H Healthcare Furniture w Ancillary Installation Services
 OLM Order Level Materials

2. SPECIAL ITEM NUMBER	MAXIMUM ORDER
33721P	\$5,000,000
33721	\$250,000
339113H	\$500,000
OLM	\$250,000

3. SPECIAL ITEM NUMBER	MINIMUM ORDER
33721P	\$100.00
33721	\$100.00
339113H	\$100.00
OLM	NA

4. Geographic Coverage

48 contiguous States and Washington, DC

5. Point of Production

Krug Inc.
 421 Manitou Drive
 Kitchener, Ontario, CANADA
 N2C 15L

6. Discount from List Prices

33721P Package Office Furniture Krug Product Discounts As Below
 GSA Teaming Partner Products at their
 Approved GSA Discount Terms. Krug
 Installation Charge 12.75% of Net Order
 (Max.). No Charge for Project Mgt Services.

33721 Office Furniture	
Executive Office Furniture	56.6%
Executive Conference Furniture	56.6%
Tables and Accessories	56.6%
Fully Upholstered Lounge Furniture	56.6%
Multiple Seating	56.6%
Multi-Purpose Seating	56.6%
Stacking Chairs	56.6%
Installation Ancillary to these products	12.75% Charge of Net Order (Max.)

339113H Healthcare Furniture	
Hospital Patient Room Furniture	56.6%
Hospital Geriatric Chairs & Lounge Seating	56.6%
Patient Service Systems	56.6%
Installation Ancillary to these products	12.75% Charge of Net Order (Max.)

7. Quantity Discounts (off Net pricing)

Multiple Seating, Multipurpose Seating, Stacking
 Chairs

25,001 – 50,000	1%
50,001 – 100,000	2%
100,001 – 150,000	3%
150,001 – 250,000	4%

Lounge Seating, Tables & Accessories

25,000 – 50,000	1%
50,001 – 75,000	2%
75,001 – 100,000	3%
100,001 – 180,000	4%
180,001 – 200,000	5%
200,001 – 250,000	6%

Hosp/Geriatric Chairs and Lounge, Patient Room
 Furniture, Patient Service Systems

\$100,000 - \$200,000	1%
\$200,000.01 - \$300,000	1.5%
\$300,000.01 - \$400,000	2%
\$400,000.01 - \$500,000	2.5%

Quantity Discounts for Executive Office and
 Executive Conference are no longer applicable
 based on the MAS Consolidation revisions to
 Maximum Order Limits.

8. Prompt Payment Terms

Net 30 Days

9. Visa and MasterCard are accepted above and

below the micro-purchase threshold.
 NOTE: No additional discount will be offered on
 orders placed using credit cards.

10. Foreign Items

All items manufactured in Canada.

11a. Time of Delivery

60-90 Days ARO for all items.

11b. Expedited Delivery

Please contract Krug GSA Customer Service for
 information on Expedited Delivery/Krug Express
 Program. 1-800-265-2796

11c. Overnight & 2 day Delivery

N/A

11d. Urgent Requirements

Please contact Krug for urgent requirements.

12. F.O.B. Point

Destination

13. Payment Address

Same as above

TERMS & CONDITIONS | INFORMATION FOR ORDERING ACTIVITIES

14. Warranty

For commercial products, Krug warrants the construction and the finish of all our products to be free from defects in materials and workmanship for a period of 10 years from the date of purchase. For Krug Healthcare products (as outlined in the US Healthcare price and specification Guide dated March 1, 2019), Krug warrants the construction and finish of all Healthcare products to be free from defects in materials and workmanship for the lifetime of their use. This warranty is applicable to products in use by their original purchaser. This warranty does not apply to components not manufactured by Krug including textiles, which are subject to the specific warranties of those manufacturers, if any. Textiles (fabric, leather, vinyl, or any other covering material) suppliers do not guarantee their products for durability and color fastness, and nor does Krug.

Casters, mechanical and electrical components have a warranty of five years from the date of purchase. The Krug warranty does not apply to COM-specified materials, damage caused by a carrier other than Krug, or variation in wood finishes due to natural wood color variation. Krug cannot be held responsible for variations in fabric dye lots from order to order. All fabric is carefully inspected when it is received, but a degree of variation in color should be expected. Repairs or replacement of any defect covered under this warranty by Krug will be made, at our option and method, at no charge to the original purchaser during the warranty period. Krug's judgement is final and binding with respect to the nature or cause of defects or damage, and the necessity or manner of repair or replacement.

This warranty does not apply to defects or damage resulting from:

- normal wear and tear occurring with the use of the product
- negligence, misuse, excessive use, alteration, improper cleaning or repair
- substitution or use of incorrect or unauthorized components or material
- handling or installation that is incorrect, or that causes damage or defect
- damage incurred by a freight carrier other than Krug
- wearing of finishes and fabrics, and normal variations in materials (including dye lot variations)
- properties of natural materials, including wood and leather
- exposure to environments with uncontrolled temperature and humidity (products must be transported, stored and used in climate controlled conditions)

Note, specific warranties for components and materials not manufactured by Krug: Height Adjustable Mechanism Warranty Krug warrants to the original consumer purchaser its Height Adjustable Mechanism that it will be free from defects in material and workmanship. This limited warranty covers material and manufacturing defects, which cause a non-conformance in the function of a table base and is limited to the following products and warranty term determined from their dates of purchase: a) Electronic components such as control boxes, hand switches and motors – two (2) years b) Mechanical components such as crank drives, spindles – five (5) years c) Structural components such as J-channels, feet and top supports – ten (10) years. The start of the warranty period is the documented date of your purchase of the product. The warranty herein is made to and for the benefit of the original consumer purchaser of the product and is non-transferable. If you discover a defect in material or workmanship during the warranty period, and Krug agrees that the defect exists, Krug will, at its option, repair or replace the Product at no charge to you, provided it is returned during the warranty period. In the unlikely event that your product should require repair or replacement during the warranty period, please contact Krug to obtain warranty service. The warranty period on replacement products is the remainder of the warranty on the original product or 30 days, whichever is longer.

Jordan Sleepers Heavy-Duty Mechanism, made with heavy gauge steel and minimal moving parts - is backed by a 5-year warranty on the mechanism itself, in addition to the lifetime warranty on the rest of the product. If it does become damaged or degraded, the mechanism can be field-replaced. Juno and Trevisa Overbed Tables have a 2-year warranty.

15. Export Packing Charges

Quoted upon request

16. Terms and Conditions of Government Commercial Credit Card

ACCEPTANCE: KRUG will accept the government commercial credit card but will not Offer any additional discount for orders placed using the credit card

17. Term and Conditions of Rental Maintenance and Repair.

N/A

18. Term and Conditions of Installation

N/A

19. Term and Conditions of Repair

N/A

20a. Term and Conditions for any other services

N/A

20. Service and Distribution points

Call contractor

21. Participating Dealers

Call contractor

22. Preventative Maintenance

N/A

23. Environmental Attributes

Krug maintains a program to reduce the impact on the environment of our products and operations.

24. Data Universal Number System (DUNS) number

251476669

25. Notification regarding registration in SAM.

Krug Inc.'s registration in SAM is current, accurate and valid.

26. Cage Code: 37310

i TERMS & CONDITIONS

SOLIS | GUEST BACK

- 2 Solis Environmental Summary
- 3 Solis Guest Features & Options
- 5 Solis Dimensions & COM Requirements
- 6 Solis Guest Pricing
- 7 Solis Replacement Components

SOLIS | PATIENT BACK

- 9 Solis Environmental Summary
- 10 Solis Dimensions & COM Requirements
- 11 Solis Patient Pricing
- 12 Solis Replacement Components

SOLIS | MULTIPLE GUEST & PATIENT SEATING

- 14 Solis Dimensions & COM Requirements | Guest
- 16 Solis Multiple Seating Pre-Configured Guest Units Pricing
- 17 Solis Multiple Seating Start, Center & End Guest Units Pricing
- 19 Solis Pre-Configured Freespan Multiple Seating Guest Units Pricing
- 21 Solis Dimensions & COM Requirements Patient Backs
- 22 Solis Multiple Seating Pre-Configured Patient Units Pricing
- 24 Solis Multiple Seating Start, Center & End Patient Units Pricing
- 26 Solis Pre-Configured Freespan Multiple Seating Patient Units Pricing
- 28 Solis Replacement Components

SOLIS | EASY ACCESS SEATING

- 33 Solis Environmental Summary
- 33 Solis Dimensions & COM Requirements
- 33 Solis Easy Access Chair Pricing

SOLIS | BEHAVIORAL HEALTH

- 34 Solis Environmental Summary
- 35 Solis Behavioral Health Features
- 36 Solis Behavioral Health Options
- 37 Solis Behavioral Health Guest Dimensions & COM Requirements
- 38 Solis Behavioral Health Guest Pricing
- 39 Solis Behavioral Health Patient Dimensions & COM Requirements
- 40 Solis Behavioral Health Patient Pricing
- 41 Solis Behavioral Health Guest Multiple Seating Dimensions & COM Requirements
- 42 Solis Behavioral Health Guest Multiple Seating Pricing
- 44 Solis Behavioral Health Patient Multiple Seating Dimensions & COM Requirements
- 45 Solis Behavioral Health Patient Multiple Seating Pricing
- 47 Solis Behavioral Health Replacement Parts

SOLIS | TABLES

- 50 Solis Environmental Summary
- 51 Solis Tables Features
- 52 Solis Linking Tables

- 53 Solis Free Standing Tables

GENERAL INFORMATION


- 54 Terms & Conditions
- 54 Warranty
- 56 KRUG Textiles - Upholstery Fabrics
- 58 KRUG Textiles - Leather & Faux Leather
- 60 Customer's Own Material (COM/COL)
- 60 CAL 133 & Moisture Barrier
- 61 Graded-In Upholstery Programs
- 61 *KRUGEXPRESS* Program
- 62 Wood Finishes
- 62 Standard Laminates
- 63 Metal Finishes
- 63 Urethane Color Options
- 63 Solid Surface Program

SOLIS | ENVIRONMENTAL SUMMARY

LEED CI CREDITS



MATERIAL CONTENT:



PRE-CONSUMER
RECYCLED CONTENT = 16%

POST-CONSUMER
RECYCLED CONTENT = 22%

CONTRIBUTES TO

CREDIT	CONTRIBUTES TO	POINTS
CREDIT 2.1 - 2.2	Construction Waste Management	1-2 point(s)
CREDIT 3.3	Resource Reuse	1 point
CREDIT 4.1	Recycled Content	1 point
CREDIT 4.2	Recycled Content	1 point
CREDIT 4.5	Low Emitting Materials, (PLEASE ENQUIRE) Composite Wood & Laminate Adhesives	1 point
CREDIT 5.1	Regional Materials*	1 point
CREDIT 7	Certified Wood (PLEASE ENQUIRE)	1 point

* This credit is only applicable if in total 20% of the combined value of the procurement of construction materials and in the furniture are manufactured within a radius of 500 miles. This credit will apply if the installation of the finished product occurs within 500 miles of Toronto, Ontario.

The above information regarding LEED contribution applies to both the upholstered as well as mesh back versions.

level® CERTIFICATION, AIR EMISSIONS AND FSC® CERTIFICATION



level® CERTIFICATION

BIFMA's e3 Furniture Sustainability Standard is a voluntary, multi-attribute standard that measures the degree of sustainability of furniture. This standard evaluates product and company environmental attributes and compliance systems in a wide range of elements which include Materials, Energy & Atmosphere, Human & Ecosystem Health and Social Responsibility. Solis products have earned level®, BIFMA's sustainability certification program for furniture, certification through third-party verification against the e3 standard.



AIR-EMISSIONS

All Solis products are supplied air-emissions certified. Contact customer service for information.

FSC®

In 2005, Krug received Forest Stewardship Council® (FSC®) Chain-of-Custody certification for our manufacturing facilities. The FSC® Chain-of-Custody tracks certified wood from seedling to final sale. It verifies that the material for our FSC® certified products only come from well-managed, FSC®-certified forests and other controlled sources. FSC® is dedicated to the promotion of responsible forest management worldwide helping to take care of forests for future generations. Solis and other Krug products can be specified with FSC® Certification. Contact customer service for further information, pricing and lead times.



Architects, designers, and building professionals can specify FSC®-certified products in order to achieve a point from the U.S. Green Building Council's Leadership in Energy and Environmental Design (LEED) Rating System.

SOLIS | FEATURES & OPTIONS



CLEAN OUT

All Solis seating models have a built-in clean out feature: a space at the back of the seat that allows dirt, debris and liquids to fall to the floor for easy clean up and maintenance - designed so that it does not detract from the comfort or appearance of the product.



STEEL SEAT FRAME

The structural seat frame is made from welded steel with a powder-coated finish that allows Solis to well exceed ANSI/BIFMA standards. Rounded arms provide support for safe and easy ingress and egress.



HIGH DENSITY FOAM

Solis features dual density foam that is soft on the outside for comfort, dense on the inside for high durability. The seat and back foam features a compound curvature that supports healthy sitting postures, while also designed to ease ingress and egress.



FLEX BACK

Solis sets a new standard for comfort and ergonomics in healthcare seating. The ergonomically-designed back has a slight flexing action, which significantly enhances comfort.



URETHANE ARM

Solis arms are durable, comfortable, and long lasting. Urethane arms are available in three color options; Black, Grey and Taupe.



WOODEN ARM

Wood arms are available in either beech or maple hardwood and in 22 Krug standard finishes. Maple arm caps are available for an up-charge of **\$80 list** per arm using beech pricing.

REPLACEABLE COMPONENTS

Solis chairs are uniquely designed to allow virtually all major components to be field replaced, providing a very cost effective means to significantly extend the life of the product. Seats, backs, arms, frames and casters are field replaceable. Pricing and model numbers can be viewed online at www.krug.ca.

TUBULAR STEEL CHAIR FRAME

The overall aesthetic frame of the chair is built from structural steel tubing, both elliptical and rectangular for exceptional strength and appealing design. The frame is electro welded and polished joints for ease of cleaning and a one piece look. Available in eight powder-coated finishes. Silver Metallic is offered as Krug's standard finish.

METAL FINISHES

Silver Metallic Standard - No Upcharge

Silver Metallic frames are available with an anti-microbial finish for an upcharge of **\$64 list** per arm frame pair or table. Additional Frame Finishes are available for an upcharge of **\$64 list** per seat/ table.

Available colors are: • White • Parchment • Sand • Taupe • Warm Grey • Cool Grey • Black

For all metal finishes other than Silver Metallic Standard, there is a minimum order quantity of 30 units per color. The anti-microbial finish is included in the additional finish up-charge. Upcharges for order quantities less than 30 units per color or custom metal finishes, please contact Customer Service to obtain a quote.

WALL SAVER

The angle of the back and the rear legs are designed to keep the back away from the wall, to prevent wear and damage to both the chairs and to the walls of the facility. Patient and Guest chairs with mesh backs are excluded as they do not have the wall saver feature.

LATEX-FREE

Krug products are made with latex-free materials, to prevent the allergic reaction that latex causes in some people.

GANGING

All Solis Freestanding chairs can be ganged using a ganging bracket. The powder-coated metal plate is fastened to the underside of the steel side rails using the pre-existing holes in the frame.

EASY ACCESS ADJUSTABLE GLIDES

With the larger footprint of this chair and critical importance of stability for the user, we have included adjustable glides on the front legs - this allows the Easy Access chair to be perfectly leveled to any floor for maximum safety and stability.

FINISH DURABILITY

The Krug Enduraguard finish, a proprietary catalyzed varnish formulation, has been repeatedly shown, through independent laboratory testing, to be the industry leader in durability and abrasion resistance. The Krug finish looks better longer than competitors, and is uniquely suited to the demands of healthcare environments.

WEIGHT CAPACITIES

Weight capacities are as follows:

Guest & Patient Chairs (21" & 24") - 500 lbs

Plus Chairs (30" & 44") - 750 lbs

Multiple Seating & Pre-configured - 500 lbs per seat

2-Seat Freespan - 525 lbs per unit

3-Seat Freespan = 750 lbs per unit

PLUS UPGRADE

Solis 30" and 44" models feature Plus Upgrade. Plus Upgraded seating has been engineered to support higher weight capacities, accommodating a wider variety of users.

[View Solis Images | www.krug.ca](http://www.krug.ca)

SOLIS | OPTIONS



ADJUSTABLE HEADREST

The adjustable headrest uses dual density foam providing excellent support and comfort. The headrest is securely fastened using an innovative clip allowing the headrest to be easily removed for cleaning and/or replacement. The headrest is easily adjusted by sliding the headrest vertically allowing the user to maximize their comfort.



EASY CLEAN BACKREST COVERS

Easy clean backrest covers are available on all mesh back Patient chairs. They are removable, replaceable and cleanable. The easy clean backrest cover features a foam interior for comfort and durability.



WOOD SIDE RAILS

Solis can be specified with solid wood side rails, which, along with the selection of wood arms and a choice of metal finishes, provides a warmer look and feel. All Solis wood components feature Krug's high durability Enduraguard finish. Wood Side Rails are available for an upcharge and are not available with closed arm panels.



CASTERS

Casters are available on all 21" and 24" guest and patient chairs. Two rear hard wheel casters or four hard wheel casters are available for an upcharge per chair. The option of soft wheel casters can be ordered for additional upcharge. Both hard and soft caster options are standard non-locking but can be specified locking at no additional charge. The Solis caster is not a heavy-duty caster - it is designed and rated for normal use and load bearing, but has the potential to fail with excessive use, force, or weight. The caster was designed to allow the chairs to be moved for ease of cleaning and furniture arranging. Krug is not responsible for caster breakage under any circumstances. Solis casters are field replaceable.



KINETIC BACK OPTION

This optional feature provides the chair back with a very pleasant and comfortable rocking motion, which can significantly enhance long-term sitting for patients and guests alike. The durable spring-loaded mechanism provides a range of motion of 20 degrees, and can be field-installed or replaced. It's available on any Solis chair back - Guest, Patient and Multiple Seating - with the exception of the 30" and 44" sizes.



SOLID SURFACE ARM

The optional Solid Surface Arm provides enhanced durability, protection and cleanability for the arms. This is field replaceable if this becomes damaged or degraded and is available in 8 standard colors. See [page 63](#) for color selection.

CAL133 & MOISTURE BARRIER

California Technical Bulletin 133 is a flammability test for seating. Krug offers a compliance method, in combination with non-flammable upholstery covers, may enable products to meet certification requirements for this test. This process at the same time also provides the products with a Moisture Barrier - a treatment that helps to prevent the passage of liquids and moisture to inside of the upholstered components - thereby conferring sanitary and anti-infection benefits. So when CAL 133 is specified, the product also automatically has a Moisture Barrier, and when a Moisture Barrier is specified, the product also features the compliance method and low flammability features of CAL 133.

The application of this up-charge and the compliance method does not mean that the specific configuration of product and upholstery cover are tested and officially certified as being CAL133 compliant. If the official certification is required, Krug will provide this (through an independent certified testing laboratory) at a charge of \$917 per item, plus the cost of the product to be tested. Lead time for certification testing is typically 4-8 weeks. Krug assumes no responsibility for the testing of our products in combination with upholstery covers, or for the results of any testing conducted. Some specific configurations of products and upholstery have already been tested. Please contact Customer Service for additional information.

REMOVABLE COVERS & REPLACEMENT COMPONENTS

Optional Removeable seat and back covers can be quickly installed on Solis products that were originally ordered with the Removable cover option. Replacement seat and back covers can also be installed on Solis products that were not originally ordered with the Removable cover option, with some simple staple removal on the original seats and backs. Complete Mesh backs can be ordered and field replaced.

CLEANABLE UNDER-SEAT SPLASHGUARD

All Solis seating models are available with a plastic moisture barrier that covers and encloses the underside of the seat (while still allowing air transfer and ventilation in and out of the seat cushion). The Splashguard significantly enhances the germ resistance properties of the product, by enclosing the part of the chair that can be most susceptible to infection-causing pathogens. The Splashguard is a smooth, easy to clean surface, either while on the chair or when removed, and is also field replaceable. The upcharges for the Splashguard are based on the size of the seat.

COMBINATION UPHOLSTERY OPTION

When combination upholstery is specified with fabric of the same grade or COM, an upcharge for dual fabrics is **\$33 list** per unit and **\$64 list** per unit for three fabrics will be applied. When graded in combination upholstery is selected, use the highest grade upholstery selected or to obtain a quote for blended grading contact Customer Service (please provide the fabrics specified and location of where each fabric is to be applied on the product).

SOLIS | GUEST, DIMENSIONS & COM REQUIREMENTS

DIMENSIONS & COM REQUIREMENTS

	Overall Width	Overall Depth	Overall Height	Seat Height	Height of Arms from Floor	Width Between Arms	Seat Depth	Shipping Weight	Cube	COM Yardage Seat & Back	COM Yardage Seat	COM Yardage Back	COM Yardage Closed Arm Panel
UPHOLSTERED BACK													
21" Seat	25	28	34.5	18.5	26	20	20	51	16	1.6	0.9	1.5	0.8
24" Seat	28	28	34.5	18.5	26	23	20	55	18	1.6	0.9	1.5	0.8
30" Seat	34	28	34.5	18.5	26	29	20	60	22	2.5	0.9	1.6	0.8
44" Seat	48	28	34.5	18.5	26	43	20	74	31	3.2	1.1	2.3	0.8
MESH BACK													
21" Seat	25	28	34.5	18.5	26	20	20	49	16	-	0.9	-	0.8
24" Seat	28	28	34.5	18.5	26	23	20	52	18	-	0.9	-	0.8

COM - YARDAGE REQUIREMENTS

	Yardage Seat & Back	Yardage Seat	Yardage Back	Yardage Closed Arm Panel
21" & 24" - One Chair	1.6	0.9	1.5	0.8
21" & 24" - Two Chairs	3.1	1.3	2.3	1.2
21" & 24" - Three Chairs	4.9	2.1	3.1	1.6
30" - One Chair	2.5	0.9	1.6	0.8
30" - Two Chairs	5	1.8	3.2	1.2
30" - Three Chairs	7.5	2.7	4.8	1.6
44" - One Chair	3.2	1.1	2.3	0.8
44" - Two Chairs	5.6	2.2	3.9	1.2
44" - Three Chairs	8.7	3.3	5.5	1.6

Multiple yardage requirements can also be used for Guest Back Easy Access chairs and Guest Back Start, Center, End Multiple seating.

Note: Some vinyls, leathers & upholsteries are not suitable for application on Solis seating.

The approval process is as follows:

1. A sample of the COM must be provided to Krug Customer Service prior to or at the time of order.

For Maharam, Momentum or CF Stinson, Krug will obtain the fabric sample.

2. The sample will be reviewed and the customer advised if the fabric is unsuitable.

3. The COM fabric or leather will be inspected when received at the factory, to identify any further concerns with its suitability.

MESH COLORS

- Slate
- Sand
- Celery
- Earth

- Warm Grey
- Terra
- Sky
- Olive

Mesh Specifications & Performance

ASTM D4157 Abrasion Resistance (Oscillatory Cylinder) 30,000 Rubs

ASTM D5034 Breaking Strength N 2167 Warp 1916 Weft

Flammability CAL177

AATCC TM8: Colorfastness to Crooking

Dry Class 5

Wet Class 5

ASTM D3511: Brush Pilling Rating 5

ASTM D6797: Ball Burst N 2486

Krug's Mesh backs covers are produced with Polyester yarns that are 100% recyclable. The yarn dying process is a closed loop system that recycles and recaptures 100% of the energy from the heating systems needed. All dyes contain no heavy metals, carcinogens or allergens.

SOLIS | GUEST | UPHOLSTERED BACKS










Solis Guest Chairs with Upholstered Backs are available in 21", 24", 30" and 44" widths.

SOLIS | GUEST | MESH BACKS



Solis Guest Chairs with Mesh Backs are available in 21" and 24" widths only.

SOLIS | GUEST

DESCRIPTION/MODEL	Arm Type	COM		COL		FABRIC GRADES			LEATHER		
		1	2	3	4	5	6	7	8	9	
	21" Open Arm, Mesh Back										
	SOL2-GM21OPU	Urethane	1012	1044	1080	1142	1209	1276	1342	1409	1512
	SOL2-GM21OPW	Beech	1138	1170	1203	1270	1336	1403	1467	1536	1639
	21" Open Arm, Upholstered Back										
	SOL2-GU21OPU	Urethane	1063	1117	1170	1279	1384	1492	1598	1705	1920
	SOL2-GU21OPW	Beech	1191	1244	1297	1404	1510	1618	1727	1833	2046
	24" Open Arm, Mesh Back										
	SOL2-GM24OPU	Urethane	1053	1086	1118	1185	1251	1316	1384	1451	1555
	SOL2-GM24OPW	Beech	1178	1212	1245	1311	1377	1445	1510	1578	1678
	24" Open Arm, Upholstered Back										
	SOL2-GU24OPU	Urethane	1106	1158	1213	1317	1425	1534	1640	1747	1962
	SOL2-GU24OPW	Beech	1230	1284	1340	1446	1555	1662	1767	1872	2088
	30" Open Arm, Upholstered Back										
	SOL2-GU30OPU	Urethane	1286	1372	1456	1622	1790	1957	2124	2294	2629
	SOL2-GU30OPW	Beech	1415	1497	1584	1748	1915	2085	2250	2419	2754
	44" Open Arm, Upholstered Back										
	SOL2-GU44OPU	Urethane	1491	1572	1659	1822	1991	2160	2327	2493	2828
	SOL2-GU44OPW	Beech	1617	1699	1782	1949	2118	2283	2453	2620	2956
	Solis Ganging Bracket SOL2-RLKBS				51						

Closed Arm Panels (per chair) - please add the following up charges for closed arm panels.

Fabric Grades	(COM) 1	2	(COL) 3	4	5	6	7	8	9
2 ARMS	418	448	477	531	588	643	699	757	869









Solis Guest Option Upcharges	\$ List	\$ List	
CAL 133 & Moisture Barrier (per yard)	64	Solid Surface Arm (per pair) - Gr A White	488
Guest chair - Removable Seat Cover (per seat)	90	Solid Surface Arm (per pair) - Gr A Color	505
21" & 24" - Removeable Back Cover (per back)	58	Solid Surface Arm (per pair) - Gr B	542
30" & 44" - Removeable Back Cover (per back)	90	Solid Surface Arm (per pair) - Gr C	586
21" & 24" Cleanable Under-seat Splashguard	40	Maple Arm upgrade per arm (add to beech price)	80
30" Cleanable Under-seat Splashguard	48	Beech Wood Side Rails Upgrade (per chair)	127
44" Cleanable Under-seat Splashguard	64	Maple wood Side Rails Upgrade (per chair)	159
Combination Upholstery - Dual Fabrics	33	Kinetic Back option (not available for 30" & 44")	120
Combination Upholstery - Three Fabrics	64	Non-Marring Glide	37
Non-locking Soft Casters (21" & 24" chairs) -4 set	184		
Non-locking Soft Casters (21" & 24" chairs) -2 set	113		
Non-locking Hard Casters (21" & 24" chairs) -4 set	120		
Non-locking Hard Casters (21" & 24" chairs) -2 set	80		

Note: Soft & Hard casters are also available locking, clearly mark on the purchase order.






PRODUCT CODE KEY

Line	Series	Chair Type	Back Type	Size	Arm Type	
SOL	2	G	U	21	OPW	CLW
Solis	Chair	Guest Seating	Upholstered Back		Open Arm - Wood Arm	Closed Arm - Wood Arm
			M	24	OPU	CLU
			Mesh Back 21" & 24" Only		Open Arm Urethane Arm	Closed Arm - Urethane Arm
				30	OSA	CSA
					Open Arm - Solid Surface Arm	Closed Arm - Solid Surface Arm
				44		

SOLIS | REPLACEMENT COMPONENTS

DESCRIPTION/MODEL	COM			COL			FABRIC GRADES			LEATHER			Yds	Weight	Cube
	1	2	3	4	5	6	7	8	9						
	21" Replacement Guest Upholstered Backs SOL2-RBGU21	567	610	651	710	778	835	904	987	1071	1.5	14	2.7		
	21" Replacement Guest Mesh Backs SOL2-RBGM21	477										10	2.7		
	24" Replacement Guest Upholstered Backs SOL2-RBGU24	581	621	664	722	790	849	916	1002	1086	1.5	15	2.8		
	24" Replacement Guest Mesh Backs SOL2-RBGM24	497										11	2.8		
	30" Replacement Guest Upholstered Backs SOL2-RBGU30	632	679	727	795	871	938	1016	1111	1207	1.6	19	3.4		
	44" Replacement Guest Upholstered Backs SOL2-RBGU44	794	843	889	957	1034	1102	1179	1273	1371	1.6	28	4.8		
	21" Replacement Guest Upholstered Back Covers SOL2-RBCGU21	198	240	287	340	408	467	535	618	702	1.5	2	.8		
	24" Replacement Guest Upholstered Back Covers SOL2-RBCGU24	198	240	287	340	408	467	535	618	702	1.5	2.3	.8		
	30" Replacement Guest Upholstered Back Covers SOL2-RBCGU30	214	260	309	378	453	520	597	693	789	1.6	2.6	.8		
	44" Replacement Guest Upholstered Back Covers SOL2-RBCGU44	218	267	315	382	458	527	602	697	795	2.25	3.5	.8		
	Replacement Mesh Back Top Bar SOL2-RMBTB21	33										2.5	.5		
	SOL2-RMBTB24	34										3.0	.7		
	21" Replacement Seat SOL2-RS21	389	418	443	481	523	561	605	659	715	.9	9	2.7		
	24" Replacement Seat SOL2-RS24	409	436	464	501	543	583	626	679	733	.9	10	2.7		
	30" Replacement Seat SOL2-RS30	487	513	540	577	620	659	702	756	809	.9	12	3.4		
	44" Replacement Seat SOL2-RS44	628	662	694	740	793	840	892	958	1022	1.1	14	4.8		
	21" Replacement Seat Cover SOL2-RSC21	130	159	185	223	267	304	374	403	455	1.0	1.6	.8		
	24" Replacement Seat Cover SOL2-RSC24	134	160	189	227	270	306	350	405	458	1.0	1.7	.8		
	30" Replacement Seat Cover SOL2-RSC30	136	161	189	227	270	306	350	405	458	1.0	2	.8		
	44" Replacement Seat Cover SOL2-RSC44	152	186	218	265	318	363	416	483	547	1.1	2.5	.8		
	Replacement Splash Guard SOL2-RSG21	90										1	.3		
	SOL2-RSG24	110										2	.4		
	SOL2-RSG30	154										3	.5		
	SOL2-RSG44	166										4	.6		
	Replacement Closed Arm SOL2-RCA	207	218	231	247	267	283	303	327	350	0.4	6	.9		
	Replacement Arm Top - Urethane SOL2-RACU	70										1.5	.2		
	Replacement Arm Top - Beech SOL2-RACWB	213										1.0	.2		
	Replacement Arm Top - Maple SOL2-RACWM	229										1.0	.2		
	Replacement Arm Top - Solid Surface SOL2-RACSS				Grade A- White	Grade A- Color		Grade- B	Grade- C			1.0	.2		
				256	261		282	304			1.0	.2			


SOLIS | REPLACEMENT COMPONENTS

DESCRIPTION/MODEL	Price	Yds	Weight	Cube
	Replacement Side Frame - Start SOL2-RSFS	134	9	1.5
	Replacement Side Frame - Start - No Anti-Microbial SOL2-RSFSX	111	9	1.5
	Replacement Side Frame - End SOL2-RSFE	134	9	1.5
	Replacement Side Frame - End - No Anti-Microbial SOL2-RSFEX	111	9	1.5
	Replacement Side Frame - Start - 1 Glide, 1 Non-locking Caster SOL2-RSFSC	172	9.5	1.5
	Replacement Side Frame - Start - 1 Glide, 1 Non-locking Caster- No Anti-Microbial SOL2-RSFSCX	138	9.5	1.5
	Replacement Side Frame - End - 1 Glide, 1 Non-locking Caster SOL2-RSFEC	172	9.5	1.5
	Replacement Side Frame - End - 1 Glide, 1 Non-locking Caster- No Anti-Microbial SOL2-RSFECX	138	9.5	1.5
	Replacement Side Frame - Start - 2 Non-locking Casters SOL2-RSFSC2	149	10	1.5
	Replacement Side Frame - Start - 2 Non-locking Casters- No Anti-Microbial SOL2-RSFSC2X	145	10	1.5
	Replacement Side Frame - End - 2 Non-locking Casters SOL2-RSFEC2	149	10	1.5
	Replacement Side Frame - End - 2 Non-locking Casters- No Anti-Microbial SOL2-RSFEC2X	145	10	1.5
	Replacement Wood Side Rail Cover - Beech SOL2-RSRCB	180	1.0	.3
	Replacement Wood Side Rail Cover - Maple SOL2-RSRCM	231	1.0	.3
	Replacement Glide - Front SOL2-RGF	22	.5	.1
	Replacement Glide - Back SOL2-RGB	22	.5	.1
	Replacement Glide - Set of 4 SOL2-RGS4	24	2	.1
	Replacement Caster Glide - Front SOL2-RGFC	23	2	.1
	Replacement Caster Glide - Back SOL2-RGBC	23	2	.1
	Replacement Non-locking Caster - Hard Wheel SOL2 - RCH	30	1.5	.3
	Replacement Non-locking Caster - Soft Wheel SOL2 - RCS	33	1.5	.3
	Replacement Side Frame - Easy Access SOL2-RSFSEA	204	14	2.2
	Replacement Side Frame - Easy Access - No Anti-Microbial SOL2-RSFSEAX	191	14	2.2
	Replacement Step for Easy Access SOL2-RSTEP21	182	7	.8
	SOL2-RSTEP24	186	9	1.2
	SOL2-RSTEP21X	178	7	.8
	SOL2-RSTEP24X	183	9	1.2

LEED CI CREDITS



MATERIAL CONTENT:



PRE-CONSUMER
RECYCLED CONTENT = 17%

POST-CONSUMER
RECYCLE CONTENT = 22%

	CONTRIBUTES TO	
CREDIT 2.1 - 2.2	Construction Waste Management	1-2 point(s)
CREDIT 3.3	Resource Reuse	1 point
CREDIT 4.1	Recycled Content	1 point
CREDIT 4.2	Recycled Content	1 point
CREDIT 4.5	Low Emitting Materials, Systems & Seating	1 point
CREDIT 5.1	Regional Materials*	1 point
CREDIT 7	Certified Wood (MUST BE REQUESTED)	1 point(s)

*This credit is only applicable if in total 20% of the combined value of the procurement of construction materials and in the furniture are manufactured within a radius of 500 miles. This credit will apply if the installation of the finished product occurs within 500 miles of Kitchener, Ontario.

level® CERTIFICATION, AIR EMISSIONS AND FSC® CERTIFICATION



level® CERTIFICATION

BIFMA's e3 Furniture Sustainability Standard is a voluntary, multi-attribute standard that measures the degree of sustainability of furniture. This standard evaluates product and company environmental attributes and compliance systems in a wide range of elements which include Materials, Energy & Atmosphere, Human & Ecosystem Health and Social Responsibility. Solis products have earned level®, BIFMA's sustainability certification program for furniture, certification through third-party verification against the e3 standard.



AIR-EMISSIONS

All Solis products are supplied air-emissions certified. Contact customer service for information.

FSC®

In 2005, Krug received Forest Stewardship Council® (FSC®) Chain-of-Custody certification for our manufacturing facilities. The FSC® Chain-of-Custody tracks certified wood from seedling to final sale. It verifies that the material for our FSC® certified products only come from well-managed, FSC®-certified forests and other controlled sources. FSC® is dedicated to the promotion of responsible forest management worldwide helping to take care of forests for future generations. Solis and other Krug products can be specified with FSC® Certification. Contact customer service for further information, pricing and lead times.



Architects, designers, and building professionals can specify FSC®-certified products in order to achieve a point from the U.S. Green Building Council's Leadership in Energy and Environmental Design (LEED) Rating System.

SOLIS | PATIENT, DIMENSIONS & COM REQUIREMENTS

DIMENSIONS & COM. REQUIREMENTS

	Overall Width	Overall Depth	Overall Height	Seat Height	Height of Arms from Floor	Width Between Arms	Seat Depth	Shipping Weight	Cubes	COM Yardage Seat & Back	COM Yardage Seat	COM Yardage Back	COM Yardage Closed Arm Panel
UPHOLSTERED BACK													
21" Seat	25	28	43.75	18.5	26	20	20	54	21	2.1	0.9	2.0	0.8
24" Seat	28	28	43.75	18.5	26	23	20	58	23	2.1	0.9	2.0	0.8
30" Seat	34	28	43.75	18.5	26	29	20	64	28	3.1	0.9	2.2	0.8
MESH BACK													
21" Seat	25	28	43.75	18.5	26	20	20	50	21	-	0.9	-	0.8
24" Seat	28	28	43.75	18.5	26	23	20	53	23	-	0.9	-	0.8

COM - YARDAGE REQUIREMENTS

	Yardage Seat & Back	Yardage Seat	Yardage Back	Yardage Closed Arm Panel
21" & 24" - One Chair	2.1	0.9	2	0.8
21" & 24" - Two Chairs	4	1.3	3.1	1.2
21" & 24" - Three Chairs	6.1	2.1	4.2	1.6
30" - One Chair	3.1	0.9	2.2	0.8
30" - Two Chairs	6.2	1.8	4.4	1.2
30" - Three Chairs	9.3	2.6	6.6	1.6

Multiple yardage requirements can also be used for Patient Back Easy Access chairs and Patient Back Start, Center, End Multiple seating.

Note: Some vinyls, leathers & fabrics may not be suitable for application on Solis seating.

The approval process is as follows:

1. A sample of the COM. must be provided to Krug Customer Service prior to or at the time of order.
For Maharam, Momentum or CF Stinson, Krug will obtain the fabric sample.

2. The sample will be reviewed and the customer advised if the fabric is unsuitable.

3. The COM. fabric or leather will be inspected when received at the factory, to identify any further concerns with its suitability.

FEATURES:

For a complete list of features see [page 3](#).

SOLIS | PATIENT | UPHOLSTERED BACK



Solis Patient Chairs with Upholstered Backs are available in 21", 24" and 30" widths.

SOLIS | PATIENT | MESH BACK



Solis Patient Chairs with Mesh Backs are available in 21" and 24" widths only.






ORDERING NOTES: Complete Mesh backs (21" & 24") can be ordered and field replaced. The standard **Solis Frame Color** is Silver Metallic. Additional frame colors are available for an upcharge of **\$64 list** per arm frame pair, please see [page 63](#) for color selection and [page 3](#) for required ordering quantities. Silver metallic frames are available with an anti-microbial finish for an upcharge of **\$64 list** per arm frame pair or table.





Closed Arm Panels (per chair) - please add the following up charges for closed arm panels.

Fabric Grades	(COM) 1	2	(COL) 3	4	5	6	7	8	9
2 ARMS	418	448	477	531	588	643	699	757	869

[View Solis images | www.krug.ca](#)

SOLIS | PATIENT & OTTOMAN

DESCRIPTION/MODEL	Arm Type	COM		COL		FABRIC GRADES			LEATHER	
		1	2	3	4	5	6	7	8	9
	21" Open Arm, Mesh Back									
	SOL2-PM21OPU Urethane	1107	1139	1171	1239	1306	1372	1438	1504	1607
	SOL2-PM21OPW Beech	1231	1266	1298	1363	1431	1497	1563	1632	1732
	21" Open Arm, Upholstered Back									
	SOL2-PU21OPU Urethane	1163	1231	1304	1445	1584	1727	1863	2004	2285
	SOL2-PU21OPW Beech	1289	1358	1430	1569	1709	1853	1990	2132	2412
	24" Open Arm, Mesh Back									
	SOL2-PM24OPU Urethane	1143	1178	1212	1279	1345	1411	1479	1543	1645
	SOL2-PM24OPW Beech	1271	1306	1338	1404	1468	1537	1604	1669	1773
	24" Open Arm, Upholstered Back									
	SOL2-PU24OPU Urethane	1203	1275	1345	1484	1624	1765	1908	2048	2328
	SOL2-PU24OPW Beech	1331	1402	1468	1611	1752	1892	2033	2173	2457
	30" Open Arm, Upholstered Back									
	SOL2-PU30OPU Urethane	1494	1598	1702	1909	2117	2324	2531	2740	3155
	SOL2-PU30OPW Beech	1620	1727	1827	2034	2242	2451	2658	2864	3280

DESCRIPTION/MODEL	COM.		COL		FABRIC GRADES			LEATHER		W	D	H	Weight	Cubes	
	1	2	3	4	5	6	7	8	9						
	Ottoman														
	SOL5	532	555	573	618	661	702	744	786	873	18.25	18.25	13	12	5
Fabric Yardage Required: 1 ottoman = 0.7 yards 2 ottoman = 1 yards															
	Easy Clean Backrest Cover, Mesh Back														
	SOL2-BCM21	111	121	129	151	170	193	213	231	257	20	0.5	8	3	0.9
	SOL2-BCM24	111	121	129	151	170	193	213	231	257	23	0.5	8	3	0.9
	Easy Clean Backrest Cover, Upholstered Back														
	SOL2-BCU21	111	121	129	151	170	193	213	231	257	20	0.5	8	3	0.9
	SOL2-BCU24	111	121	129	151	170	193	213	231	257	23	0.5	8	3	0.9
	Adjustable Headrest														
	SOL2-HRM	173	190	205	231	255	278	301	326	372	15	3	6.75	3	0.9
	SOL2-HRU	173	190	205	231	255	278	301	326	372					
Adjustable headrest are one size and can be used on all Patient Chair models. Fabric Yardage Required: 1 headrest = 0.3 yards 2 headrest = 0.6 yards 3 headrest = 0.6 yards															

Solis Patient Option Upcharges

\$ List








\$ List

CAL 133 & Moisture Barrier (per yard)	64	Solid Surface Arm (per pair) - Gr A White	488
Removable Seat Cover (per seat)	90	Solid Surface Arm (per pair) - Gr A Color	505
21" & 24" - Removeable Back Covers (per back)	58	Solid Surface Arm (per pair) - Gr B	542
30" Removable Back Cover (per back)	90	Solid Surface Arm (per pair) - Gr C	586
21" & 24" Cleanable Under-seat Splashguard	40	Maple Arm upgrade per arm (add to beech price)	80
30" Cleanable Under-seat Splashguard	48	Beech Wood Side Rails Upgrade (per chair)	127
Non-locking Soft Casters (21" & 24" chairs) -4 set	184	Maple wood Side Rails Upgrade (per chair)	159
Non-locking Soft Casters (21" & 24" chairs) -2 set	113	Kinetic Back option (not available for 30" & 44")	120
Non-locking Hard Casters (21" & 24" chairs) -4 set	120	Non-Marring Glide	37
Non-locking Hard Casters (21" & 24" chairs) -2 set	80	Combination Upholstery - dual fabrics (per chair)	33
Note: Soft & Hard casters are also available locking, clearly mark on the purchase order.		Combination Upholstery - Three fabrics (per chair)	64

PRODUCT CODE KEY

Line	Series	Chair Type	Back Type	Size	Arm Type	
SOL Solis	2 Chair	P Patient Seating	U Upholstered Back	21	OPW Open Arm - Wood Arm	CLW Closed Arm - Wood Arm
			M Mesh Back 21" & 24" Only	24	OPU Open Arm Urethane Arm	CLU Closed Arm - Urethane Arm
				30	OSA Open Arm - Solid Surface Arm	CSA Closed Arm - Solid Surface Arm

SOLIS | REPLACEMENT COMPONENTS

Description	Model	COM		COL			FABRIC GRADES			LEATHER			Yardage	Weight	Cube
		1	2	3	4	5	6	7	8	9					
	21" Replacement Patient Upholstered Backs SOL2-RBPU21	673	732	793	877	973	1058	1152	1272	1393	2.0	21	3.8		
	21" Replacement Patient Mesh Backs SOL2-RBPM21	451										15	3.8		
	24" Replacement Patient Upholstered Backs SOL2-RBPU24	711	771	832	915	1012	1095	1192	1312	1433	2.0	21	3.8		
	24" Replacement Patient Mesh Backs SOL2-RBPM24	517										17	3.8		
	30" Replacement Patient Upholstered Backs SOL2-RBPU30	857	937	1015	1122	1247	1358	1483	1640	1794	2.6	24	4.8		
	21" Replacement Patient Upholstered Back Covers SOL2-RBCPU21	253	312	372	456	554	636	732	852	973	2.0	2.5	.8		
	24" Replacement Patient Upholstered Back Covers SOL2-RBCPU24	254	313	374	457	555	637	733	853	974	2.0	2.7	.8		
	30" Replacement Patient Upholstered Back Covers SOL2-RBCPU30	306	386	464	571	697	807	932	1088	1244	2.6	3	.8		
	Replacement Mesh Back Top Bar SOL2-RMBTB21	33										2.5	.5		
	SOL2-RMBTB24	34										3.0	.7		
	21" Replacement Seat SOL2-RS21	389	418	443	481	523	561	605	659	715	.9	9	2.7		
	24" Replacement Seat SOL2-RS24	409	436	464	501	543	583	626	679	733	.9	10	2.7		
	30" Replacement Seat SOL2-RS30	487	513	540	577	620	659	702	756	809	.9	12	3.4		
	44" Replacement Seat SOL2-RS44	628	662	694	740	793	840	892	958	1022	.9	14	4.8		
	21" Replacement Seat Cover SOL2-RSC21	130	159	185	223	267	304	374	403	455	1.0	1.6	.8		
	24" Replacement Seat Cover SOL2-RSC24	134	160	189	227	270	306	350	405	458	1.0	1.7	.8		
	30" Replacement Seat Cover SOL2-RSC30	136	161	189	227	270	306	350	405	458	1.0	2	.8		
	44" Replacement Seat Cover SOL2-RSC44	152	186	218	265	318	363	416	483	547	1.0	2.5	.8		
	Replacement Splash Guard SOL2-RSG21	90										1	.3		
	SOL2-RSG24	110										2	.4		
	SOL2-RSG30	154										3	.5		
	SOL2-RSG44	166										4	.6		
	Replacement Closed Arm SOL2-RCA	207	218	231	247	267	283	303	327	350	0.4	6	.9		

SIN 339113H - Hospital Geriatric Chairs & Lounge
SOLIS | REPLACEMENT COMPONENTS

DESCRIPTION/MODEL	Price	Weight	Cube	
	Replacement Side Frame - Start SOL2-RSFS	134	9 1.5	
	Replacement Side Frame - Start - No Anti-Microbial SOL2-RSFSX	111	9 1.5	
	Replacement Side Frame - End SOL2-RSFE	134	9 1.5	
	Replacement Side Frame - End - No Anti-Microbial SOL2-RSFEX	111	9 1.5	
	<hr/>			
		Replacement Side Frame - Start - 1 Glide, 1 Caster SOL2-RSFSC	172	9.5 1.5
Replacement Side Frame - Start - 1 Glide, 1 Caster- No Anti-Microbial SOL2-RSFSCX		138	9.5 1.5	
Replacement Side Frame - End - 1 Glide, 1 Caster SOL2-RSFEC		172	9.5 1.5	
Replacement Side Frame - End - 1 Glide, 1 Caster- No Anti-Microbial SOL2-RSFECX		138	9.5 1.5	
<hr/>				
		Replacement Side Frame - Start - 2 Caster SOL2-RSFSC2	149	10 1.5
	Replacement Side Frame - Start - 2 Caster- No Anti-Microbial SOL2-RSFSC2X	145	10 1.5	
	Replacement Side Frame - End - 2 Caster SOL2-RSFEC2	149	10 1.5	
	Replacement Side Frame - End - 2 Caster- No Anti-Microbial SOL2-RSFEC2X	145	10 1.5	
	<hr/>			
		Replacement Arm Cap - Urethane SOL2-RACU	70	1.0 .2
Replacement Arm Cap - Beech SOL2-RACWB		213	1.0 .2	
Replacement Arm Cap - Maple SOL2-RACWM		229	1.0 .2	
Replacement Arm Cap - Solid Surface SOL2-RACSS		Grade A- White 256 Grade A- Color 261 Grade- B 282 Grade- C 304	2	.2
<hr/>				
		Replacement Wood Side Rail Cover - Beech SOL2-RSRCB	180	1.0 .3
	Replacement Wood Side Rail Cover - Maple SOL2-RSRCM	231	1.0 .3	
<hr/>				
	Replacement Glide - Front SOL2-RGF	22	.5 .1	
	Replacement Glide - Back SOL2-RGB	22	.5 .1	
	Replacement Glide - Set of 4 SOL2-RGS4	24	2 .1	
	Replacement Caster Glide - Front SOL2-RGFC	23	2 .1	
	Replacement Caster Glide - Back SOL2-RGBC	23	2 .1	
	<hr/>			
		Replacement Caster - Hard Wheel SOL2 - RCH	30	1.5 .3
Replacement Caster - Soft Wheel SOL2 - RCS		33	1.5 .3	

SOLIS | MULTIPLE SEATING - GUEST BACKS

DIMENSIONS & COM. REQUIREMENTS - PRE-CONFIGURED UNITS

	Overall Width	Overall Depth	Overall Height	Seat Height	Height of Arms from Floor	Width Between Arms	Seat Depth	Shipping Weight	Cube	COM. Seat & Back Yardage	COM Fabric Seat Yardage	COM. Fabric Back Yardage	COM. Fabric Closed Arm Panel Yardage
MESH BACK													
PCGM21X2	47	28	34.5	18.5	26	20	20	90	30	-	1.3	-	1.2
PCGM21X3	69.5	28	34.5	18.5	26	20	20	126	44	-	2.1	-	1.6
PCGM24X2	53	28	34.5	18.5	26	23	20	96	34	-	1.3	-	1.2
PCGM24X3	78.5	28	34.5	18.5	26	23	20	135	50	-	2.1	-	1.6
UPHOLSTERED BACK													
PCGU21X2	47	28	34.5	18.5	26	20	20	94	30	3.1	1.3	2.3	1.2
PCGU21X3	69.5	28	34.5	18.5	26	20	20	132	44	4.7	2.1	3.1	1.6
PCGU24X2	53	28	34.5	18.5	26	23	20	102	34	3.1	1.3	2.3	1.2
PCGU24X3	78.5	28	34.5	18.5	26	23	20	144	50	4.7	2.1	3.1	1.6

DIMENSIONS & COM. REQUIREMENTS - START UNITS

	Overall Width	Overall Depth	Overall Height	Seat Height	Height of Arms from Floor	Width Between Arms	Seat Depth	Shipping Weight	Cube	COM. Seat & Back Yardage	COM Fabric Seat Yardage	COM. Fabric Back Yardage	COM. Fabric Closed Arm Panel (1 Arm) Yardage	COM. Fabric Closed Arm Panel (2 Arms) Yardage
MESH BACK														
SGM21	25	28	34.5	18.5	26	20	20	41	16	-	0.9	-	0.4	0.8
SGM24	28	28	34.5	18.5	26	23	20	44	18	-	0.9	-	0.4	0.8
UPHOLSTERED BACK														
SGU21	25	28	34.5	18.5	26	20	20	43	16	1.6	0.9	1.6	0.4	0.8
SGU24	28	28	34.5	18.5	26	23	20	47	18	1.6	0.9	1.6	0.4	0.8
SGU30	34	28	34.5	18.5	26	29	20	52	22	2.5	0.9	1.6	0.4	0.8
SGU44	48	28	34.5	18.5	26	43	20	66	31	3.2	1.1	2.5	0.4	0.8

DIMENSIONS & COM. REQUIREMENTS - CENTER UNITS

	Overall Width	Overall Depth	Overall Height	Seat Height	Height of Arms from Floor	Width Between Arms	Seat Depth	Shipping Weight	Cube	COM. Seat & Back Yardage	COM Fabric Seat Yardage	COM. Fabric Back Yardage	COM. Fabric Closed Arm Panel Yardage
MESH BACK													
CGM21	23	28	34.5	18.5	26	20	20	35	16	-	0.9	-	0.4
CGM24	26	28	34.5	18.5	26	23	20	38	18	-	0.9	-	0.4
UPHOLSTERED BACK													
CGU21	23	28	34.5	18.5	26	20	20	37	16	1.6	0.9	1.6	0.4
CGU24	26	28	34.5	18.5	26	23	20	41	19	1.6	0.9	1.6	0.4
CGU30	32	28	34.5	18.5	26	29	20	46	22	2.5	0.9	1.6	0.4
CGU44	46	28	34.5	18.5	26	43	20	60	31	3.2	1.1	2.5	0.4

DIMENSIONS & COM. REQUIREMENTS - END UNITS

	Overall Width	Overall Depth	Overall Height	Seat Height	Height of Arms from Floor	Width Between Arms	Seat Depth	Shipping Weight	Cube	COM. Seat & Back Yardage	COM Fabric Seat Yardage	COM. Fabric Back Yardage	COM. Fabric Closed Arm Panel Yardage
MESH BACK													
EGM21	23	28	34.5	18.5	26	20	20	35	16	-	0.9	-	0.4
EGM24	26	28	34.5	18.5	26	23	20	38	18	-	0.9	-	0.4
UPHOLSTERED BACK													
EGU21	23	28	34.5	18.5	26	20	20	37	16	1.6	0.9	1.6	0.4
EGU24	26	28	34.5	18.5	26	23	20	41	18	1.6	0.9	1.6	0.4
EGU30	32	28	34.5	18.5	26	29	20	46	22	2.5	0.9	1.6	0.4
EGU44	46	28	34.5	18.5	26	43	20	60	31	3.2	1.1	2.5	0.4

ORDERING NOTES:

When ordering multiple Start, Center, End units please refer to [page 5](#) for Yardage Requirements.

SOLIS | MULTIPLE SEATING - GUEST BACKS

DIMENSIONS & COM. REQUIREMENTS - FREESPAN WITH NO CENTER ARM

	Overall Width	Overall Depth	Overall Height	Seat Height	Height of Arms from Floor	Width Between Arms	Seat Depth	Shipping Weight	Cube	COM. Seat & Back Yardage	COM Fabric Seat Yardage	COM. Fabric Back Yardage	COM. Fabric Closed Arm Panel Yardage
MESH BACK													
PCFGM21X2A	46.5	28	34.5	18.5	26	41.5	20	85	30	-	1.3	-	0.8
PCFGM21X3A	68	28	34.5	18.5	26	63	20	114	44	-	2.1	-	0.8
PCFGM24X2A	52.25	28	34.5	18.5	26	47.5	20	92	34	-	1.3	-	0.8
PCFGM24X3A	77	28	34.5	18.5	26	72	20	124	50	-	2.1	-	0.8
UPHOLSTERED BACK													
PCFGU21X2A	46.5	28	34.5	18.5	26	41.5	20	89	30	3.1	1.3	2.3	0.8
PCFGU21X3A	68	28	34.5	18.5	26	63	20	120	44	4.7	2.1	3.1	0.8
PCFGU24X2A	52.25	28	34.5	18.5	26	47.5	20	96	34	3.1	1.3	2.3	0.8
PCFGU24X3A	77	28	34.5	18.5	26	72	20	131	50	4.7	2.1	3.1	0.8

DIMENSIONS & COM. REQUIREMENTS - FREESPAN WITH CENTER ARM

	Overall Width	Overall Depth	Overall Height	Seat Height	Height of Arms from Floor	Width Between Arms	Seat Depth	Shipping Weight	Cube	COM. Seat & Back Yardage	COM Fabric Seat Yardage	COM. Fabric Back Yardage
MESH BACK												
PCFGM21X2B	47.25	28	34.5	18.5	26	20	20	93	30	-	1.3	-
PCFGM21X3B	69.5	28	34.5	18.5	26	20	20	130	44	-	2.1	-
PCFGM24X2B	53.25	28	34.5	18.5	26	23	20	100	34	-	1.3	-
PCFGM24X3B	78.5	28	34.5	18.5	26	23	20	140	50	-	2.1	-
UPHOLSTERED BACK												
PCFGU21X2B	47.25	28	34.5	18.5	26	20	20	97	30	3.1	1.3	2.3
PCFGU21X3B	69.5	28	34.5	18.5	26	20	20	136	44	4.7	2.1	3.1
PCFGU24X2B	53.25	28	34.5	18.5	26	23	20	104	34	3.1	1.3	2.3
PCFGU24X3B	78.5	28	34.5	18.5	26	23	20	147	50	4.7	2.1	3.1
	COM. Fabric Closed Arm Panels (2 Arms)		COM Fabric Closed Arm Panels (3 Arms)				COM. Fabric Closed Arm Panels (4 Arms)					
PCFG21X2B	0.8		1.2				1.6					
PCFG21X3B	0.8		1.2				1.6					
PCFG24X2B	0.8		1.2				1.6					
PCFG24X3B	0.8		1.2				1.6					

Solis Pre-configured Guest Option Upcharges

\$ List

\$ List









CAL 133 & Moisture Barrier (per yard)	64	Maple Arm upgrade per arm (add to beech price)	80
Kinetic Back option (not available for 30" & 44")	120	Beech Wood Side Rails Upgrade (per chair)	127
Guest chair - Removable Seat Cover (per seat)	90	Solid Surface Arm (per pair) - Gr A White	488
21" & 24" - Removeable Back Covers (per back)	58	Solid Surface Arm (per pair) - Gr A Color	505
30" & 44" - Removeable Back Covers	90	Solid Surface Arm (per pair) - Gr B	542
Combination Upholstery - dual fabrics (per chair)	33	Solid Surface Arm (per pair) - Gr C	586
Combination Upholstery - Three fabrics (per chair)	64	Solid Surface Arm (per arm) - Gr A White	244
Beech Wood Side Rails Upgrade (per chair)	127	Solid Surface Arm (per arm) - Gr A Color	253
Maple wood Side Rails Upgrade (per chair)	159	Solid Surface Arm (per arm) - Gr B	271
21" & 24" Cleanable Under-seat Splashguard	40	Solid Surface Arm (per arm) - Gr C	293
30" Cleanable Under-seat Splashguard	48	Non-locking Soft Casters (21" & 24" chairs) -4 set	184
44" Cleanable Under-seat Splashguard	64	Non-locking Soft Casters (21" & 24" chairs) -2 set	113
Non-Marring Glide	37	Non-locking Hard Casters (21" & 24" chairs) -4 set	120
Additional features and options information see page 24.		Non-locking Hard Casters (21" & 24" chairs) -2 set	80

Note: Soft & Hard casters are also available locking, clearly mark on the purchase order.

Closed Arm Panels (per chair) - please add the following up charges for closed arm panels.

Fabric Grades	(COM) 1	2	(COL) 3	4	5	6	7	8	9
1 ARM	208	224	238	267	294	321	350	379	435
2 ARMS	418	448	477	531	588	643	699	757	869
3 ARMS	627	669	710	796	879	963	1048	1135	1304
4 ARMS	835	890	948	1061	1172	1285	1335	1510	1736

SOLIS | MULTIPLE SEATING - PRE-CONFIGURED GUEST UNITS

DESCRIPTION/MODEL	Arm Type	COM		COL			FABRIC GRADES			LEATHER	
		1	2	3	4	5	6	7	8	9	
	2 Seat - 21" Open Arm Pre-configured Guest Unit, Mesh Back										
	SOL2-PCGM21X2OPU	Urethane	1907	1971	2037	2170	2303	2436	2569	2701	2908
	SOL2-PCGM21X2OPW	Beech	2094	2163	2228	2360	2493	2628	2760	2891	3097
	2 Seat - 21" Open Arm Pre-configured Guest Unit, Upholstered Back										
	SOL2-PCGU21X2OPU	Urethane	2002	2110	2217	2432	2642	2859	3073	3289	3714
	SOL2-PCGU21X2OPW	Beech	2192	2301	2407	2621	2835	3052	3265	3479	3904
	3 Seat - 21" Open Arm Pre-configured Guest Unit, Mesh Back										
	SOL2-PCGM21X3OPU	Urethane	2735	2833	2933	3133	3330	3532	3731	3930	4237
	SOL2-PCGM21X3OPW	Beech	2987	3087	3186	3384	3582	3784	3982	4182	4488
	3 Seat - 21" Open Arm Pre-configured Guest Unit, Upholstered Back										
	SOL2-PCGU21X3OPU	Urethane	2874	3036	3194	3516	3839	4160	4480	4799	5443
	SOL2-PCGU21X3OPW	Beech	3129	3289	3449	3768	4089	4414	4734	5054	5695
	2 Seat - 24" Open Arm Pre-configured Guest Unit, Mesh Back										
	SOL2-PCGM24X2OPU	Urethane	1959	2026	2091	2223	2357	2489	2623	2756	2962
	SOL2-PCGM24X2OPW	Beech	2147	2215	2281	2415	2548	2681	2812	2946	3148
	2 Seat - 24" Open Arm Pre-configured Guest Unit, Upholstered Back										
	SOL2-PCGU24X2OPU	Urethane	2059	2166	2273	2487	2701	2916	3132	3345	3772
	SOL2-PCGU24X2OPW	Beech	2249	2356	2463	2678	2891	3104	3320	3535	3961
	3 Seat - 24" Open Arm Pre-configured Guest Unit, Mesh Back										
	SOL2-PCGM24X3OPU	Urethane	2818	2917	3016	3215	3414	3613	3814	4011	4319
	SOL2-PCGM24X3OPW	Beech	3070	3169	3269	3469	3668	3867	4066	4265	4573
	3 Seat - 24" Open Arm Pre-configured Guest Unit, Upholstered Back										
	SOL2-PCGU24X3OPU	Urethane	2963	3120	3279	3592	3906	4221	4534	4853	5479
	SOL2-PCGU24X3OPW	Beech	3215	3374	3533	3845	4160	4473	4788	5106	5734

ORDERING NOTES: A drawing showing the configuration of the multiple seating and tables is required with each purchase order.
 Complete Mesh backs (21" & 24") can be ordered and field replaced.

Solis Pre-configured Guest Option Upcharges	\$ List	\$ List
CAL 133 & Moisture Barrier (per yard)	64	Solid Surface Arm (per pair) - Gr A White 488
Kinetic Back option (not available for 30" & 44")	120	Solid Surface Arm (per pair) - Gr A Color 505
Guest chair - Removable Seat Cover (per seat)	90	Solid Surface Arm (per pair) - Gr B 542
21" & 24" - Removeable Back Covers (per back)	58	Solid Surface Arm (per pair) - Gr C 586
Combination Upholstery - dual fabrics (per chair)	33	Solid Surface Arm (per arm) - Gr A White 244
Combination Upholstery - Three fabrics (per chair)	64	Solid Surface Arm (per arm) - Gr A Color 253
Beech Wood Side Rails Upgrade (per chair)	127	Solid Surface Arm (per arm) - Gr B 271
Maple wood Side Rails Upgrade (per chair)	159	Solid Surface Arm (per arm) - Gr C 293
21" & 24" Cleanable Under-seat Splashguard	40	Non-locking Soft Casters (21" & 24" chairs) -4 set 184
Non-Marring Glide	37	Non-locking Soft Casters (21" & 24" chairs) -2 set 113
Maple Arm upgrade per arm (add to beech price)	80	Non-locking Hard Casters (21" & 24" chairs) -4 set 120
		Non-locking Hard Casters (21" & 24" chairs) -2 set 80


Additional features and options information see page 24, closed arm panels page 97.




Note: Soft & Hard casters are also available locking, clearly mark on the purchase order.



PRODUCT CODE KEY

Line	Series	Chair Type	Back Type	Size	Arm Type
SOL	2	PCG	U	21X2	OPW CLW
Solis	Chair	Pre-configured Guest Multiple Unit	Upholstered Back		Open Arm - Wood Arm Closed Arm Urethane Arm
			M	21X3	OPU CLU
			Mesh Back		Open Arm Urethane Arm Closed Arm - Wood Arm
				24X2	OSA CSA
					Open Arm - Solid Surface Arm Closed Arm - Solid Surface Arm
				24X3	

SOLIS | MULTIPLE SEATING - START, CENTER & END GUEST UNITS

DESCRIPTION/MODEL	Arm Type	COM		COL		FABRIC GRADES			LEATHER	
		1	2	3	4	5	6	7	8	9
START										
21" Open Arm Start Guest Unit, Mesh Back										
SOL2-SGM21OPU	Urethane	1012	1044	1080	1142	1209	1276	1342	1409	1512
SOL2-SGM21OPW	Beech	1138	1170	1203	1270	1336	1403	1467	1536	1639
										
21" Open Arm Start Guest Unit, Upholstered Back										
SOL2-SGU21OPU	Urethane	1063	1117	1170	1279	1384	1492	1598	1705	1920
SOL2-SGU21OPW	Beech	1191	1244	1297	1404	1510	1618	1727	1833	2046





										
24" Open Arm Start Guest Unit, Mesh Back										
SOL2-SGM24OPU	Urethane	1053	1086	1118	1185	1251	1316	1384	1451	1555
SOL2-SGM24OPW	Beech	1178	1212	1245	1311	1377	1445	1510	1578	1678
24" Open Arm Start Guest Unit, Upholstered Back										
SOL2-SGU24OPU	Urethane	1106	1158	1213	1317	1425	1534	1640	1747	1962
SOL2-SGU24OPW	Beech	1230	1284	1340	1446	1555	1662	1767	1872	2088
										
30" Open Arm Start Guest Unit, Upholstered Back										
SOL2-SGU30OPU	Urethane	1286	1372	1456	1622	1790	1957	2124	2294	2629
SOL2-SGU30OPW	Beech	1415	1497	1584	1748	1915	2085	2250	2419	2754
										
44" Open Arm Start Guest Unit, Upholstered Back										
SOL2-SGU44OPU	Urethane	1491	1572	1659	1822	1991	2160	2327	2493	2828
SOL2-SGU44OPW	Beech	1617	1699	1782	1949	2118	2283	2453	2620	2956

CENTER										
										
21" Open Arm Center Guest Unit, Mesh Back										
SOL2-CGM21OPU	Urethane	909	941	976	1039	1108	1172	1240	1307	1409
SOL2-CGM21OPW	Beech	973	1004	1037	1106	1170	1237	1304	1371	1473
21" Open Arm Center Guest Unit, Upholstered Back										
SOL2-CGU21OPU	Urethane	955	1008	1062	1169	1276	1383	1487	1597	1810
SOL2-CGU21OPW	Beech	1017	1068	1124	1231	1340	1446	1554	1662	1872
										
24" Open Arm Center Guest Unit, Mesh Back										
SOL2-CGM24OPU	Urethane	932	967	1001	1065	1134	1199	1266	1332	1434
SOL2-CGM24OPW	Beech	997	1031	1063	1128	1195	1263	1330	1394	1497
24" Open Arm Center Guest Unit, Upholstered Back										
SOL2-CGU24OPU	Urethane	983	1036	1090	1195	1304	1411	1518	1623	1839
SOL2-CGU24OPW	Beech	1045	1097	1153	1260	1369	1477	1583	1688	1902

PRODUCT CODE KEY

Line	Series	Chair Type	Back Type	Size	Arm Type
SOL	2	SG	U	21	OPW
Solis	Chair	Start Unit Guest Multiple Seating	Upholstered Back		Open Arm - Wood Arm
		CG	M	24	OPU
		Center Unit Guest Multiple Seating	Mesh Back 21" & 24" Only		Open Arm - Urethane Arm
		EG		30	OSA
		End Unit Guest Multiple Seating			Open Arm - Solid Surface Arm
				44	CSA
					Closed Arm - Solid Surface Arm
					COW
					Closed Start Arm / Open Center Arm - Wood Arm
					COU
					Closed Arm / Open Center Arm - Urethane Arm

SOLIS | MULTIPLE SEATING - CENTER & END GUEST UNITS

DESCRIPTION/MODEL	Arm Type	COM		COL		FABRIC GRADES			LEATHER	
		1	2	3	4	5	6	7	8	9
 30" Open Arm Center Guest Unit, Upholstered Back SOL2-CGU30OPU SOL2-CGU30OPW	Urethane	1147	1230	1314	1483	1647	1817	1985	2148	2486
	Beech	1212	1294	1377	1547	1713	1881	2048	2214	2549
	<hr/> 44" Open Arm Center Guest Unit, Upholstered Back SOL2-CGU44OPU SOL2-CGU44OPW									
Urethane	1341	1425	1509	1676	1844	2010	2177	2345	2681	
Beech	1404	1491	1570	1741	1908	2072	2241	2408	2743	
END  21" Open Arm End Guest Unit, Mesh Back SOL2-EGM21OPU SOL2-EGM21OPW	Urethane	909	941	976	1039	1108	1172	1240	1307	1409
	Beech	973	1004	1037	1106	1170	1237	1304	1371	1473
	<hr/> 21" Open Arm End Guest Unit, Upholstered Back SOL2-EGU21OPU SOL2-EGU21OPW									
Urethane	955	1008	1062	1169	1276	1383	1487	1597	1810	
Beech	1017	1068	1124	1231	1340	1446	1554	1662	1872	
 24" Open Arm End Guest Unit, Mesh Back SOL2-EGM24OPU SOL2-EGM24OPW	Urethane	932	967	1001	1065	1134	1199	1266	1332	1434
	Beech	997	1031	1063	1128	1195	1263	1330	1394	1497
	<hr/> 24" Open Arm End Guest Unit, Upholstered Back SOL2-EGU24OPU SOL2-EGU24OPW									
Urethane	983	1036	1090	1195	1304	1411	1518	1623	1839	
Beech	1045	1097	1153	1260	1369	1477	1583	1688	1902	
 30" Open Arm End Guest Unit, Upholstered Back SOL2-EGU30OPU SOL2-EGU30OPW	Urethane	1147	1230	1314	1483	1647	1817	1985	2148	2486
	Beech	1212	1294	1377	1547	1713	1881	2048	2214	2549
	<hr/> 44" Open Arm End Guest Unit, Upholstered Back SOL2-EGU44OPU SOL2-EGU44OPW									
Urethane	1341	1428	1509	1676	1844	2010	2177	2345	2681	
Beech	1404	1491	1570	1741	1908	2072	2241	2408	2743	









ORDERING NOTES:

The standard **Solis Frame Color** is Silver Metallic. Additional frame colors are available for an upcharge of **\$64 list** per arm frame pair, please see **page 63** for color selection and **page 3** for required ordering quantities. Silver metallic frames are available with an anti-microbial finish for an upcharge of **\$64 list** per arm frame pair or table.

PRODUCT CODE KEY

Line	Series	Chair Type	Back Type	Size	Arm Type	
SOL	2	SG	U	21	OPW	CLW
Solis	Chair	Start Unit Guest Multiple Seating	Upholstered Back		Open Arm -Wood Arm	Closed Arm - Wood Arm
		CG	M	24	OPU	CLU
		Center Unit Guest Multiple Seating	Mesh Back 21" & 24" Only		Open Arm-Urethane Arm	Closed Arm Urethane Arm
		EG		30	OSA	CSA
		End Unit Guest Multiple Seating			Open Arm - Solid Surface Arm	Closed Arm- Solid Surface Arm
				44		

SOLIS | PRE-CONFIGURED FREESPAN MULTIPLE SEATING GUEST UNIT WITHOUT CENTER ARM

DESCRIPTION/MODEL	Arm Type	COM		COL		FABRIC GRADES			LEATHER		
		1	2	3	4	5	6	7	8	9	
	21" Pre-Configured Freespan Guest Unit - Open Arm 2 Seat, Mesh Back										
	SOL2-PCFGM21X2AOPU	Urethane	1808	1855	1902	1997	2091	2188	2281	2377	2518
	SOL2-PCFGM21X2AOPW	Beech	1934	1981	2030	2124	2218	2313	2408	2503	2642
	21" Pre-Configured Freespan Guest Unit - Open Arm 2 Seat, Upholstered Back										
	SOL2-PCFGU21X2AOPU	Urethane	1902	2007	2114	2328	2542	2757	2970	3186	3613
	SOL2-PCFGU21X2AOPW	Beech	2030	2134	2241	2457	2669	2883	3097	3313	3741
	21" Pre-Configured Freespan Guest Unit - Open Arm 3 Seat, Mesh Back										
	SOL2-PCFGM21X3AOPU	Urethane	2527	2596	2669	2810	2954	3096	3238	3381	3594
	SOL2-PCFGM21X3AOPW	Beech	2654	2723	2794	2936	3080	3221	3364	3507	3718
	21" Pre-Configured Freespan Guest Unit - Open Arm 3 Seat, Upholstered Back										
	SOL2-PCFGU21X3AOPU	Urethane	2659	2819	2982	3301	3620	3941	4263	4584	5229
	SOL2-PCFGU21X3AOPW	Beech	2787	2946	3105	3428	3745	4068	4392	4710	5353
	24" Pre-Configured Freespan Guest Unit - Open Arm 2 Seat, Mesh Back										
	SOL2-PCFGM24X2AOPU	Urethane	1849	1896	1944	2037	2133	2228	2323	2418	2560
	SOL2-PCFGM24X2AOPW	Beech	1976	2023	2069	2165	2257	2355	2449	2543	2685
	24" Pre-Configured Freespan Guest Unit - Open Arm 2 Seat, Upholstered Back										
	SOL2-PCFGU24X2AOPU	Urethane	1944	2053	2158	2373	2587	2802	3014	3229	3656
	SOL2-PCFGU24X2AOPW	Beech	2069	2176	2282	2497	2714	2927	3141	3355	3784
	24" Pre-Configured Freespan Guest Unit - Open Arm 3 Seat, Mesh Back										
	SOL2-PCFGM24X3AOPU	Urethane	2589	2659	2732	2873	3014	3159	3299	3441	3655
	SOL2-PCFGM24X3AOPW	Beech	2715	2787	2857	2998	3141	3285	3427	3566	3783
	24" Pre-Configured Freespan Guest Unit - Open Arm 3 Seat, Upholstered Back										
	SOL2-PCFGU24X3AOPU	Urethane	2719	2882	3042	3364	3685	4007	4328	4646	5289
	SOL2-PCFGU24X3AOPW	Beech	2848	3009	3167	3490	3812	4133	4456	4774	5418

ORDERING NOTES: A drawing showing the configuration of the multiple seating and tables is required with each purchase order. Complete Mesh backs (21" & 24") can be ordered and field replaced.









Solis Pre-configured Guest Option Upcharges	\$ List	\$ List	
CAL 133 & Moisture Barrier (per yard)	64	Maple Arm upgrade per arm (add to beech price)	80
Kinetic Back option (not available for 30" & 44")	120	Solid Surface Arm (per pair) - Gr A White	488
Guest chair - Removable Seat Cover (per seat)	90	Solid Surface Arm (per pair) - Gr A Color	505
21" & 24" - Removeable Back Covers (per back)	58	Solid Surface Arm (per pair) - Gr B	542
Combination Upholstery - dual fabrics (per chair)	33	Solid Surface Arm (per pair) - Gr C	586
Combination Upholstery - Three fabrics (per chair)	64	Non-Marring Glide	37
Beech Wood Side Rails Upgrade (per chair)	127	Non-locking Soft Casters (21" & 24" chairs) -4 set	184
Maple wood Side Rails Upgrade (per chair)	159	Non-locking Soft Casters (21" & 24" chairs) -2 set	113
21" & 24" Cleanable Under-seat Splashguard	40	Non-locking Hard Casters (21" & 24" chairs) -4 set	120
		Non-locking Hard Casters (21" & 24" chairs) -2 set	80

Note: Soft & Hard casters are also available locking, clearly mark on the purchase order.

PRODUCT CODE KEY

Line	Series	Chair Type	Back Type	Size	Unit Style	Arm Type
SOL	2	PCFG	U	21X2	A	OPW
Solis	Chair	Pre-Configured Freespan Multiple Guest Unit	Upholstered Back		Unit with no Center Arm	Open Arm
			M	21X3	B	OPU
			Mesh Back		Unit with Center Arm	Open Arm Upholstered Arm
				24X2		CLW
						Closed Arm - Wood Arm
				24X3		CLU
						Closed Arm Upholstered Arm

SOLIS | PRE-CONFIGURED FREESPAN MULTIPLE SEATING GUEST UNIT WITH CENTER ARM

DESCRIPTION/MODEL	Arm Type	COM		COL		FABRIC GRADES			LEATHER		
		1	2	3	4	5	6	7	8	9	
	21" Pre-Configured Freespan Center Arm Guest Unit - Open Arm 2 Seat, Mesh Back										
	SOL2-PCFGM21X2BOPU	Urethane	1951	1999	2046	2140	2237	2329	2423	2520	2663
	SOL2-PCFGM21X2BOPW	Beech	2140	2190	2237	2329	2423	2520	2614	2712	2852
	21" Pre-Configured Freespan Center Arm Guest Unit - Open Arm 2 Seat, Upholstered Back										
	SOL2-PCFGU21X2BOPU	Urethane	2053	2160	2266	2480	2694	2908	3120	3336	3763
	SOL2-PCFGU21X2BOPW	Beech	2240	2347	2457	2669	2882	3097	3312	3528	3954
	21" Pre-Configured Freespan Center Arm Guest Unit - Open Arm 3 Seat, Mesh Back										
	SOL2-PCFGM21X3BOPU	Urethane	2748	2822	2893	3036	3179	3320	3461	3605	3818
	SOL2-PCFGM21X3BOPW	Beech	3004	3074	3145	3289	3430	3574	3714	3856	4070
	21" Pre-Configured Freespan Center Arm Guest Unit - Open Arm 3 Seat, Upholstered Back										
	SOL2-PCFGU21X3BOPU	Urethane	2894	3055	3215	3535	3856	4179	4499	4821	5464
	SOL2-PCFGU21X3BOPW	Beech	3146	3307	3469	3788	4111	4429	4752	5075	5717
	24" Pre-Configured Freespan Center Arm Guest Unit - Open Arm 2 Seat, Mesh Back										
	SOL2-PCFGM24X2BOPU	Urethane	1990	2037	2086	2180	2277	2370	2464	2560	2701
	SOL2-PCFGM24X2BOPW	Beech	2180	2228	2277	2370	2464	2560	2656	2747	2891
	24" Pre-Configured Freespan Center Arm Guest Unit - Open Arm 2 Seat, Upholstered Back										
	SOL2-PCFGU24X2BOPU	Urethane	2091	2201	2307	2522	2736	2949	3163	3379	3806
	SOL2-PCFGU24X2BOPW	Beech	2281	2390	2496	2713	2926	3140	3353	3566	3995
	24" Pre-Configured Freespan Center Arm Guest Unit - Open Arm 3 Seat, Mesh Back										
	SOL2-PCFGM24X3BOPU	Urethane	2812	2883	2956	3097	3239	3382	3522	3666	3880
	SOL2-PCFGM24X3BOPW	Beech	3067	3136	3208	3349	3491	3635	3776	3919	4132
	24" Pre-Configured Freespan Center Arm Guest Unit - Open Arm 3 Seat, Upholstered Back										
	SOL2-PCFGU24X3BOPU	Urethane	2958	3117	3279	3599	3920	4243	4562	4885	5527
	SOL2-PCFGU24X3BOPW	Beech	3210	3371	3533	3852	4173	4498	4815	5137	5781

Solis Pre-configured Guest Option Upcharges	\$ List	\$ List	
CAL 133 & Moisture Barrier (per yard)	64	Maple Arm upgrade per arm (add to beech price)	80
Kinetic Back option (not available for 30" & 44")	120	Solid Surface Arm (per pair) - Gr A White	488
Guest chair - Removable Seat Cover (per seat)	90	Solid Surface Arm (per pair) - Gr A Color	505
21" & 24" - Removeable Back Covers (per back)	58	Solid Surface Arm (per pair) - Gr B	542
Combination Upholstery - dual fabrics (per chair)	33	Solid Surface Arm (per pair) - Gr C	586
Combination Upholstery - Three fabrics (per chair)	64	Non-Marring Glide	37
Beech Wood Side Rails Upgrade (per chair)	127	Non-locking Soft Casters (21" & 24" chairs) -4 set	184
Maple wood Side Rails Upgrade (per chair)	159	Non-locking Soft Casters (21" & 24" chairs) -2 set	113
21" & 24" Cleanable Under-seat Splashguard	40	Non-locking Hard Casters (21" & 24" chairs) -4 set	120
		Non-locking Hard Casters (21" & 24" chairs) -2 set	80

Note: Soft & Hard casters are also available locking, clearly mark on the purchase order.

PRODUCT CODE KEY

Line	Series	Chair Type	Back Type	Size	Unit Style	Arm Type
SOL	2	PCFG	U	21X2	A	OPW
Solis	Chair	Pre-Configured Freespan Multiple Guest Unit	Upholstered Back		Unit with no Center Arm	Open Arm- Wood Arm
			M	21X3	B	OPU
			Mesh Back		Unit with Center Arm	Open Arm Urethane Arm
				24X2		CLW
						Closed Arm - Wood Arm
				24X3		CLU
						Closed Arm Urethane Arm

SOLIS | MULTIPLE SEATING - PATIENT BACKS**DIMENSIONS & COM. REQUIREMENTS - PRE-CONFIGURED UNITS**

	Overall Width	Overall Depth	Overall Height	Seat Height	Height of Arms from Floor	Width Between Arms	Seat Depth	Shipping Weight	Cube	COM. Seat & Back Yardage	COM Fabric Seat Yardage	COM. Fabric Back Yardage	COM. Fabric Closed Arm Panel Yardage
MESH BACK													
PCPM21X2	47	28	43.75	18.5	26	20	20	92	38	-	1.3	-	1.2
PCPM21X3	69.5	28	43.75	18.5	26	20	20	129	56	-	2.1	-	1.6
PCPM24X2	53	28	43.75	18.5	26	23	20	98	43	-	1.3	-	1.2
PCPM24X3	78.5	28	43.75	18.5	26	23	20	138	46	-	2.1	-	1.6
UPHOLSTERED BACK													
PCPU21X2	47	28	43.75	18.5	26	20	20	100	38	4.0	1.3	3.1	1.2
PCPU21X3	69.5	28	43.75	18.5	26	20	20	141	56	6.1	2.1	4.2	1.6
PCPU24X2	53	28	43.75	18.5	26	23	20	108	43	4.0	1.3	3.1	1.2
PCPU24X3	78.5	28	43.75	18.5	26	23	20	153	63	6.1	2.1	4.2	1.6

DIMENSIONS & COM. REQUIREMENTS - START UNITS

	Overall Width	Overall Depth	Overall Height	Seat Height	Height of Arms from Floor	Width Between Arms	Seat Depth	Shipping Weight	Cube	COM. Seat & Back Yardage	COM Fabric Seat Yardage	COM. Fabric Back Yardage	COM. Fabric Closed Arm Panel (1 Arm) Yardage	COM. Fabric Closed Arm Panel (2 Arms) Yardage
MESH BACK														
SPM21	25	28	43.75	18.5	26	20	20	42	21	-	0.9	-	0.4	0.8
SPM24	28	28	43.75	18.5	26	23	20	45	23	-	0.9	-	0.4	0.8
UPHOLSTERED BACK														
SPU21	25	28	43.75	18.5	26	20	20	46	21	2.1	0.9	2.0	0.4	0.8
SPU24	28	28	43.75	18.5	26	23	20	50	23	2.1	0.9	2.0	0.4	0.8
SPU30	34	28	43.75	18.5	26	29	20	56	28	3.1	0.9	2.2	0.4	0.8

DIMENSIONS & COM. REQUIREMENTS - CENTER UNITS

	Overall Width	Overall Depth	Overall Height	Seat Height	Height of Arms from Floor	Width Between Arms	Seat Depth	Shipping Weight	Cube	COM. Seat & Back Yardage	COM Fabric Seat Yardage	COM. Fabric Back Yardage	COM. Fabric Closed Arm Panel Yardage
MESH BACK													
CPM21	23	28	43.75	18.5	26	20	20	36	21	-	0.9	-	0.4
CPM24	26	28	43.75	18.5	26	23	20	39	23	-	0.9	-	0.4
UPHOLSTERED BACK													
CPU21	23	28	43.75	18.5	26	20	20	40	21	2.1	0.9	2.0	0.4
CPU24	26	28	43.75	18.5	26	23	20	44	23	2.1	0.9	2.0	0.4
CPU30	32	28	43.75	18.5	26	29	20	50	28	3.1	0.9	2.2	0.4

DIMENSIONS & COM. REQUIREMENTS - END UNITS

	Overall Width	Overall Depth	Overall Height	Seat Height	Height of Arms from Floor	Width Between Arms	Seat Depth	Shipping Weight	Cube	COM. Seat & Back Yardage	COM Fabric Seat Yardage	COM. Fabric Back Yardage	COM. Fabric Closed Arm Panel Yardage
MESH BACK													
EPM21	23	28	43.75	18.5	26	20	20	36	21	-	0.9	-	0.4
EPM24	26	28	43.75	18.5	26	23	20	38	23	-	0.9	-	0.4
UPHOLSTERED BACK													
EPU21	23	28	43.75	18.5	26	20	20	40	21	2.1	0.9	2.0	0.4
EPU24	26	28	43.75	18.5	26	23	20	44	23	2.1	0.9	2.0	0.4
EPU30	32	28	43.75	18.5	26	29	20	50	28	3.1	0.9	2.2	0.4

ORDERING NOTES:Multiple yardage requirements for Patient back Start, Center and End units, please refer to [page 10](#).

SOLIS | MULTIPLE SEATING - PATIENT BACKS

DIMENSIONS & COM. REQUIREMENTS - FREESPAN WITH NO CENTER ARM

	Overall Width	Overall Depth	Overall Height	Seat Height	Height of Arms from Floor	Width Between Arms	Seat Depth	Shipping Weight	Cube	COM. Seat & Back Yardage	COM Fabric Seat Yardage	COM. Fabric Back Yardage	COM. Fabric Closed Arm Panel Yardage
MESH BACK													
PCFPM21X2A	46.5	28	43.75	18.5	26	41.5	20	87	38	-	1.3	-	0.8
PCFPM21X3A	68	28	43.75	18.5	26	63	20	118	56	-	2.1	-	0.8
PCFPM24X2A	52.25	28	43.75	18.5	26	47.5	20	94	43	-	1.3	-	0.8
PCFPM24X3A	77	28	43.75	18.5	26	72	20	128	63	-	2.1	-	0.8
UPHOLSTERED BACK													
PCFPU21X2A	46.5	28	43.75	18.5	26	41.5	20	95	38	4.0	1.3	3.1	0.8
PCFPU21X3A	68	28	43.75	18.5	26	63	20	129	56	6.1	2.1	4.2	0.8
PCFPU24X2A	52.25	28	43.75	18.5	26	47.5	20	103	43	4.0	1.3	3.1	0.8
PCFPU24X3A	77	28	43.75	18.5	26	72	20	141	63	6.1	2.1	4.2	0.8

DIMENSIONS & COM. REQUIREMENTS - FREESPAN WITH CENTER ARM

	Overall Width	Overall Depth	Overall Height	Seat Height	Height of Arms from Floor	Width Between Arms	Seat Depth	Shipping Weight	Cube	COM. Seat & Back Yardage	COM Fabric Seat Yardage	COM. Fabric Back Yardage
MESH BACK												
PCFPM21X2B	47.25	28	43.75	18.5	26	20	20	96	38	-	1.3	-
PCFPM21X3B	69.5	28	43.75	18.5	26	20	20	134	56	-	2.1	-
PCFPM24X2B	53.25	28	43.75	18.5	26	23	20	102	43	-	1.3	-
PCFPM24X3B	78.5	28	43.75	18.5	26	23	20	144	63	-	2.1	-
UPHOLSTERED BACK3.4												
PCFPU21X2B	47.25	28	43.75	18.5	26	20	20	103	38	4.0	1.3	3.4
PCFPU21X3B	69.5	28	43.75	18.5	26	20	20	145	56	6.1	2.1	5.4
PCFPU24X2B	53.25	28	43.75	18.5	26	23	20	111	43	4.0	1.3	3.4
PCFPU24X3B	78.5	28	43.75	18.5	26	23	20	157	63	6.1	2.1	5.4

	COM. Fabric Closed Arm Panels (2 Arms)	COM Fabric Closed Arm Panels (3 Arms)	COM. Fabric Closed Arm Panels (4 Arms)
PCFP21X2B	0.8	1.2	
PCFP21X3B	0.8		1.6
PCFP24X2B	0.8	1.2	
PCFP24X3B	0.8		1.6

ORDERING NOTES: A drawing showing the configuration of the multiple seating and tables is required with each purchase order. Complete Mesh backs (21" & 24") can be ordered and field replaced.









Solis Pre-configured Patient Option Upcharges	\$ List	\$ List
CAL 133 & Moisture Barrier (per yard)	64	Maple Arm upgrade per arm (add to beech price) 80
Kinetic Back option (not available for 30" & 44")	120	Beech Wood Side Rails Upgrade (per chair) 127
Patient chair - Removable Seat Cover (per seat)	90	Solid Surface Arm (per pair) - Gr A White 488
21" & 24" - Removeable Back Covers (per back)	61	Solid Surface Arm (per pair) - Gr A Color 505
30" & 44" - Removeable Back Covers	94	Solid Surface Arm (per pair) - Gr B 542
Combination Upholstery - dual fabrics (per chair)	33	Solid Surface Arm (per pair) - Gr C 586
Combination Upholstery - Three fabrics (per chair)	64	Non-Marring Glide 37
Beech Wood Side Rails Upgrade (per chair)	127	Non-locking Soft Casters (21" & 24" chairs) -4 set 184
Maple wood Side Rails Upgrade (per chair)	159	Non-locking Soft Casters (21" & 24" chairs) -2 set 113
21" & 24" Cleanable Under-seat Splashguard	40	Non-locking Hard Casters (21" & 24" chairs) -4 set 120
30" Cleanable Under-seat Splashguard	48	Non-locking Hard Casters (21" & 24" chairs) -2 set 80
44" Cleanable Under-seat Splashguard	64	Note: Soft & Hard casters are also available locking, clearly mark on the purchase order.

Additional features and options information see page 24.

Closed Arm Panels (per chair) - please add the following up charges for closed arm panels.

Fabric Grades	(COM) 1	2	(COL) 3	4	5	6	7	8	9
1 ARM	208	224	238	267	294	321	350	379	435
2 ARMS	418	448	477	531	588	643	699	757	869
3 ARMS	627	669	710	796	879	963	1048	1135	1304
4 ARMS	835	890	948	1061	1172	1285	1335	1510	1736

SOLIS | MULTIPLE SEATING - PRE-CONFIGURED PATIENT UNITS

DESCRIPTION/MODEL	Arm Type	COM		COL		FABRIC GRADES			LEATHER		
		1	2	3	4	5	6	7	8	9	
	2 Seat - 21" Open Arm Pre-configured Patient Unit, Mesh Back										
	SOL2-PCPM21X2OPU	Urethane	2104	2169	2237	2369	2502	2635	2767	2899	3104
	SOL2-PCPM21X2OPW	Beech	2294	2359	2423	2559	2692	2823	2957	3090	3294
	2 Seat - 21" Open Arm Pre-configured Patient Unit, Upholstered Back										
	SOL2-PCPU21X2OPU	Urethane	2211	2345	2480	2745	3014	3283	3547	3816	4352
	SOL2-PCPU21X2OPW	Beech	2401	2533	2669	2934	3206	3471	3739	4006	4540
	3 Seat - 21" Open Arm Pre-configured Patient Unit, Mesh Back										
	SOL2-PCPM21X3OPU	Urethane	3043	3144	3244	3444	3642	3843	4040	4239	4547
	SOL2-PCPM21X3OPW	Beech	3297	3403	3507	3697	3895	4093	4292	4491	4799
	3 Seat - 21" Open Arm Pre-configured Patient Unit, Upholstered Back										
	SOL2-PCPU21X3OPU	Urethane	3203	3408	3609	4020	4426	4861	5242	5650	6466
	SOL2-PCPU21X3OPW	Beech	3455	3661	3865	4271	4679	5113	5495	5904	6718
	2 Seat - 24" Open Arm Urethane Cap Pre-configured Patient Unit, Mesh Back										
	SOL2-PCPM24X2OPU	Urethane	2132	2196	2265	2396	2530	2663	2794	2928	3134
	SOL2-PCPM24X2OPW	Beech	2321	2387	2453	2587	2718	2852	2986	3117	3322
	2 Seat - 24" Open Arm Pre-configured Patient Unit, Upholstered Back										
	SOL2-PCPU24X2OPU	Urethane	2240	2376	2508	2778	3043	3313	3579	3847	4381
	SOL2-PCPU24X2OPW	Beech	2431	2564	2698	2966	3236	3501	3768	4038	4571
	3 Seat - 24" Open Arm Pre-configured Patient Unit, Mesh Back										
	SOL2-PCPM24X3OPU	Urethane	3102	3203	3301	3499	3699	3898	4098	4295	4606
	SOL2-PCPM24X3OPW	Beech	3355	3455	3554	3753	3953	4152	4350	4548	4859
	3 Seat - 24" Open Arm Pre-configured Patient Unit, Upholstered Back										
	SOL2-PCPU24X3OPU	Urethane	3260	3465	3669	4077	4486	4891	5302	5710	6527
	SOL2-PCPU24X3OPW	Beech	3513	3717	3921	4331	4738	5145	5554	5964	6780

ORDERING NOTES: A drawing showing the configuration of the multiple seating and tables is required with each purchase order. Complete Mesh backs (21" & 24") can be ordered and field replaced.

Solis Pre-configured Patient Option Upcharges	\$ List	\$ List	
CAL 133 & Moisture Barrier (per yard)	64	Beech Wood Side Rails Upgrade (per chair)	127
Kinetic Back option (not available for 30" & 44")	120	Solid Surface Arm (per pair) - Gr A White	488
Patient chair - Removable Seat Cover (per seat)	90	Solid Surface Arm (per pair) - Gr A Color	505
21" & 24" - Removeable Back Covers (per back)	61	Solid Surface Arm (per pair) - Gr B	542
Combination Upholstery - dual fabrics (per chair)	33	Solid Surface Arm (per pair) - Gr C	586
Combination Upholstery - Three fabrics (per chair)	64	Solid Surface Arm (per arm) - Gr A White	244
Beech Wood Side Rails Upgrade (per chair)	127	Solid Surface Arm (per arm) - Gr A Color	253
Maple wood Side Rails Upgrade (per chair)	159	Solid Surface Arm (per arm) - Gr B	271
21" & 24" Cleanable Under-seat Splashguard	40	Solid Surface Arm (per arm) - Gr C	293
Non-Marring Glide	37	Non-locking Soft Casters (21" & 24" chairs) -4 set	184
Maple Arm upgrade per arm (add to beech price)	80	Non-locking Soft Casters (21" & 24" chairs) -2 set	113
		Non-locking Hard Casters (21" & 24" chairs) -4 set	120
		Non-locking Hard Casters (21" & 24" chairs) -2 set	80











Additional features and options information see page 24, closed arm panel upcharges page 104.

Note: Soft & Hard casters are also available locking, clearly mark on the purchase order.

PRODUCT CODE KEY

Line	Series	Chair Type	Back Type	Size	Arm Type
SOL	2	PCP	U	21X2	OPW
Solis	Chair	Pre-configured Multiple Unit Patient	Upholstered Back		Open Arm - Wood Arm
			M	21X3	OPU
			Mesh Back		Open Arm Urethane Arm
				24X2	CLW
					Closed Arm - Wood Arm
				24X3	CLU
					Closed Arm Urethane Arm

SOLIS | MULTIPLE SEATING - PATIENT START & CENTER UNITS






DESCRIPTION/MODEL	Arm Type	COM		COL		FABRIC GRADES			LEATHER		
		1	2	3	4	5	6	7	8	9	
	21" Open Arm Start Patient Unit, Mesh Back										
	SOL2-SPM21OPU	Urethane	1107	1139	1171	1239	1306	1372	1438	1504	1607
	SOL2-SPM21OPW	Beech	1231	1266	1298	1363	1431	1497	1563	1632	1732
	21" Open Arm Start Patient Unit, Upholstered Back										
	SOL2-SPU21OPU	Urethane	1163	1231	1304	1445	1584	1727	1863	2004	2285
	SOL2-SPU21OPW	Beech	1289	1358	1430	1569	1709	1853	1990	2132	2412
	24" Open Arm Start Patient Unit, Mesh Back										
	SOL2-SPM24OPU	Urethane	1143	1178	1212	1279	1345	1411	1479	1543	1645
	SOL2-SPM24OPW	Beech	1271	1306	1338	1404	1468	1537	1604	1669	1773
	24" Open Arm Start Patient Unit, Upholstered Back										
	SOL2-SPU24OPU	Urethane	1203	1275	1345	1484	1624	1765	1908	2048	2328
	SOL2-SPU24OPW	Beech	1331	1402	1468	1611	1752	1892	2033	2173	2457
	30" Open Arm Start Patient Unit, Upholstered Back										
	SOL2-SPU30OPU	Urethane	1494	1598	1702	1909	2117	2323	2531	2740	3155
	SOL2-SPU30OPW	Beech	1620	1727	1827	2034	2242	2451	2658	2864	3280
	CENTER 21" Open Arm Center Patient Unit, Mesh Back										
	SOL2-CPM21OPU	Urethane	1003	1036	1067	1137	1241	1268	1335	1402	1504
	SOL2-CPM21OPW	Beech	1065	1097	1134	1199	1266	1332	1398	1464	1567
	21" Open Arm Center Patient Unit, Upholstered Back										
	SOL2-CPU21OPU	Urethane	1054	1124	1194	1335	1478	1615	1756	1897	2177
	SOL2-CPU21OPW	Beech	1117	1190	1257	1398	1538	1677	1819	1960	2241
	24" Open Arm Urethane Cap Center Patient Unit, Mesh Back										
	SOL2-CPM24OPU	Urethane	1030	1062	1094	1162	1228	1294	1359	1425	1529
	SOL2-CPM24OPW	Beech	1092	1124	1158	1224	1290	1357	1422	1491	1592
	24" Open Arm Center Patient Unit, Upholstered Back										
	SOL2-CPU24OPU	Urethane	1082	1152	1222	1361	1503	1643	1782	1924	2206
	SOL2-CPU24OPW	Beech	1142	1215	1284	1425	1565	1706	1845	1988	2269
	30" Open Arm Center Patient Unit, Upholstered Back										
	SOL2-CPU30OPU	Urethane	1355	1459	1560	1769	1976	2182	2390	2601	3013
	SOL2-CPU30OPW	Beech	1417	1522	1623	1833	2037	2244	2453	2663	3076

ORDERING NOTES: A drawing showing the configuration of the multiple seating and tables is required with each purchase order. Additional features and options information see page 24, closed arm panel upcharges page 104.

PRODUCT CODE KEY

Line	Series	Chair Type	Back Type	Size	Arm Type
SOL	2	SP	U	21	OPW
Solis	Chair	Start Unit Patient Multiple Seating	Upholstered Back		Open Arm - Wood Arm
		CP	M	24	OPU
		Center Unit Patient Multiple Seating	Mesh Back 21" & 24" Only		Open Arm Urethane Arm
		EP		30	CLW
		End Unit Patient Multiple Seating			Closed Arm - Wood Arm
				44	CLU
					Closed Arm Urethane Arm
					COW
					Closed Start Arm/Open Center Arm Wood Arm
					COU
					Closed Start Arm/Open Center Arm with Urethane Arm

SOLIS | MULTIPLE SEATING - PATIENT END UNITS

DESCRIPTION/MODEL	Arm Type	COM		COL		FABRIC GRADES			LEATHER	
		1	2	3	4	5	6	7	8	9
 21" Open Arm End Patient Unit, Mesh Back SOL2-EPM21OPU SOL2-EPM21OPW	Urethane	1003	1036	1067	1137	1202	1268	1335	1402	1504
	Beech	1065	1097	1134	1199	1266	1332	1398	1464	1567
	21" Open Arm End Patient Unit, Upholstered Back									
 SOL2-EPU21OPU SOL2-EPU21OPW	Urethane	1054	1124	1194	1335	1478	1615	1756	1897	2177
	Beech	1117	1190	1257	1398	1538	1677	1819	1960	2241
	24" Open Arm End Patient Unit, Mesh Back									
 SOL2-EPM24OPU SOL2-EPM24OPW	Urethane	1030	1062	1094	1162	1228	1294	1359	1425	1529
	Beech	1092	1124	1158	1224	1290	1357	1422	1491	1592
	24" Open Arm End Patient Unit, Upholstered Back									
 SOL2-EPU24OPU SOL2-EPU24OPW	Urethane	1082	1152	1222	1361	1503	1643	1782	1924	2206
	Beech	1142	1215	1284	1425	1565	1706	1846	1988	2269
	30" Open Arm End Patient Unit, Upholstered Back									
 SOL2-EPU30OPU SOL2-EPU30OPW	Urethane	1355	1459	1560	1769	1976	2182	2390	2601	3013
	Beech	1417	1522	1623	1833	2037	2244	2453	2663	3076

ORDERING NOTES: A drawing showing the configuration of the multiple seating and tables is required with each purchase order. Complete Mesh backs (21" & 24") can be ordered and field replaced.

Solis Pre-configured Patient Option Upcharges	\$ List	\$ List	
CAL 133 & Moisture Barrier (per yard)	64	Beech Wood Side Rails Upgrade (per chair)	127
Kinetic Back option (not available for 30" & 44")	120	Solid Surface Arm (per pair) - Gr A White	488
Patient chair - Removable Seat Cover (per seat)	90	Solid Surface Arm (per pair) - Gr A Color	505
21" & 24" - Removeable Back Covers (per back)	61	Solid Surface Arm (per pair) - Gr B	542
30" & 44" - Removeable Back Covers	94	Solid Surface Arm (per pair) - Gr C	586
Combination Upholstery - dual fabrics (per chair)	33	Solid Surface Arm (per arm) - Gr A White	244
Combination Upholstery - Three fabrics (per chair)	64	Solid Surface Arm (per arm) - Gr A Color	253
Beech Wood Side Rails Upgrade (per chair)	127	Solid Surface Arm (per arm) - Gr B	271
Maple wood Side Rails Upgrade (per chair)	159	Solid Surface Arm (per arm) - Gr C	293
21" & 24" Cleanable Under-seat Splashguard	40	Non-locking Soft Casters (21" & 24" chairs) -4 set	184
30" Cleanable Under-seat Splashguard	48	Non-locking Soft Casters (21" & 24" chairs) -2 set	113
44" Cleanable Under-seat Splashguard	64	Non-locking Hard Casters (21" & 24" chairs) -4 set	120
Non-Marring Glide	37	Non-locking Hard Casters (21" & 24" chairs) -2 set	80
Maple Arm upgrade per arm (add to beech price)	80	Note: Soft & Hard casters are also available locking, clearly mark on the purchase order.	

Additional features and options information see page 24.









Closed Arm Panels (per chair) - please add the following up charges for closed arm panels.

Fabric Grades	(COM) 1	2	(COL) 3	4	5	6	7	8	9
1 ARM	208	224	238	267	294	321	350	379	435

PRODUCT CODE KEY

Line	Series	Chair Type	Back Type	Size	Arm Type
SOL	2	SP	U	21	OPW
Solis	Chair	Start Unit Patient Multiple Seating	Upholstered Back		Open Arm - Wood Arm
		CP	M	24	OPU
		Center Unit Patient Multiple Seating	Mesh Back 21" & 24" Only		Open Arm Urethane Arm
		EP		30	CLW
		End Unit Patient Multiple Seating			Closed Arm - Wood Arm
					CLU
					Closed Arm Urethane Arm

SOLIS | PRE-CONFIGURED FREESPAN MULTIPLE SEATING PATIENT UNIT WITHOUT CENTER ARM

DESCRIPTION/MODEL	Arm Type	COM		COL		FABRIC GRADES			LEATHER		
		1	2	3	4	5	6	7	8	9	
	21" Pre-Configured Freespan Patient Unit - Open Arm 2 Seat, Mesh Back										
	SOL2-PCFPM21X2AOPU	Urethane	1997	2045	2091	2188	2281	2377	2471	2566	2710
	SOL2-PCFPM21X2AOPW	Beech	2124	2170	2218	2313	2408	2503	2596	2694	2835
	21" Pre-Configured Freespan Patient Unit - Open Arm 2 Seat, Upholstered Back										
	SOL2-PCFPU21X2AOPU	Urethane	2100	2239	2382	2661	2943	3222	3505	3786	4348
	SOL2-PCFPU21X2AOPW	Beech	2227	2364	2507	2788	3069	3349	3631	3914	4473
	21" Pre-Configured Freespan Patient Unit - Open Arm 3 Seat, Mesh Back										
	SOL2-PCFPM21X3AOPU	Urethane	2808	2881	2952	3095	3237	3379	3520	3663	3876
	SOL2-PCFPM21X3AOPW	Beech	2935	3008	3078	3220	3363	3505	3646	3789	4004
	21" Pre-Configured Freespan Patient Unit - Open Arm 3 Seat, Upholstered Back										
	SOL2-PCFPU21X3AOPU	Urethane	2957	3166	3379	3798	4221	4641	5063	5485	6328
	SOL2-PCFPU21X3AOPW	Beech	3082	3294	3505	3929	4348	4767	5190	5612	6455
	24" Pre-Configured Freespan Patient Unit - Open Arm 2 Seat, Mesh Back										
	SOL2-PCFPM24X2AOPU	Urethane	2034	2084	2131	2223	2319	2415	2508	2606	2745
	SOL2-PCFPM24X2AOPW	Beech	2163	2210	2255	2352	2447	2541	2636	2732	2873
	24" Pre-Configured Freespan Patient Unit - Open Arm Urethane Cap 2 Seat, Upholstered Back										
	SOL2-PCFPU24X2AOPU	Urethane	2140	2281	2421	2703	2986	3266	3545	3827	4392
	SOL2-PCFPU24X2AOPW	Beech	2268	2408	2549	2829	3112	3390	3671	3954	4515
	24" Pre-Configured Freespan Patient Unit - Open Arm 3 Seat, Mesh Back										
	SOL2-PCFPM24X3AOPU	Urethane	2870	2942	3011	3155	3295	3437	3580	3721	3935
	SOL2-PCFPM24X3AOPW	Beech	2995	3068	3137	3280	3424	3564	3708	3864	4063
	24" Pre-Configured Freespan Patient Unit - Open Arm 3 Seat, Upholstered Back										
	SOL2-PCFPU24X3AOPU	Urethane	3021	3231	3439	3862	4286	4707	5125	5548	6390
	SOL2-PCFPU24X3AOPW	Beech	3145	3356	3565	3988	4411	4833	5255	5675	6518









ORDERING NOTES: A drawing showing the configuration of the multiple seating and tables is required with each purchase order. Complete Mesh backs (21" & 24") can be ordered and field replaced.

Solis Pre-configured Patient Option Upcharges	\$ List	\$ List
CAL 133 & Moisture Barrier (per yard)	64	Maple Arm upgrade per arm (add to beech price)
Kinetic Back option (not available for 30" & 44")	120	Beech Wood Side Rails Upgrade (per chair)
Patient chair - Removable Seat Cover (per seat)	90	Solid Surface Arm (per pair) - Gr A White
21" & 24" - Removeable Back Covers (per back)	61	Solid Surface Arm (per pair) - Gr A Color
Combination Upholstery - dual fabrics (per chair)	33	Solid Surface Arm (per pair) - Gr B
Combination Upholstery - Three fabrics (per chair)	64	Solid Surface Arm (per pair) - Gr C
Beech Wood Side Rails Upgrade (per chair)	127	Non-Marring Glide
Maple wood Side Rails Upgrade (per chair)	159	Non-locking Soft Casters (21" & 24" chairs) -4 set
21" & 24" Cleanable Under-seat Splashguard	40	Non-locking Soft Casters (21" & 24" chairs) -2 set
		Non-locking Hard Casters (21" & 24" chairs) -4 set
		Non-locking Hard Casters (21" & 24" chairs) -2 set
		Note: Soft & Hard casters are also available locking, clearly mark on the purchase order.

PRODUCT CODE KEY

Line	Series	Chair Type	Back Type	Size	Unit Style	Arm Type
SOL	2	PCFP	U	21X2	A	OPW
Solis	Chair	Pre-configured Freespan Multiple Patient Unit	Upholstered Back		Unit with no Center Arm	Open Arm - Wood Arm
			M	21X3	B	OPU
			Mesh Back		Unit with Center Arm	Open Arm Urethane Arm
				24X2		CLW
						Closed Arm -Wood Arm
				24X3		CLU
						Closed Arm Urethane Arm

SOLIS | PRE-CONFIGURED FREESPAN MULTIPLE SEATING PATIENT UNIT WITH CENTER ARM

DESCRIPTION/MODEL	Arm Type	COM		COL			FABRIC GRADES			LEATHER	
		1	2	3	4	5	6	7	8	9	
	21" Pre-Configured Freespan Center Arm Patient Unit - Open Arm 2 Seat, Mesh Back										
	SOL2-PCFPM21X2BOPU	Urethane	2139	2188	2236	2328	2422	2518	2612	2710	2851
	SOL2-PCFPM21X2BOPW	Beech	2328	2377	2422	2518	2612	2710	2804	2898	3039
	21" Pre-Configured Freespan Center Arm Patient Unit - Open Arm 2 Seat, Upholstered Back										
	SOL2-PCFPU21X2BOPU	Urethane	2250	2388	2531	2810	3092	3374	3654	3935	4499
	SOL2-PCFPU21X2BOPW	Beech	2440	2579	2719	3001	3283	3563	3844	4128	4686
	21" Pre-Configured Freespan Center Arm Patient Unit - Open Arm 3 Seat, Mesh Back										
	SOL2-PCFPM21X3BOPU	Urethane	3036	3105	3179	3320	3461	3605	3745	3890	4103
	SOL2-PCFPM21X3BOPW	Beech	3289	3358	3430	3574	3714	3856	3999	4142	4354
	21" Pre-Configured Freespan Center Arm Patient Unit - Open Arm 3 Seat, Upholstered Back										
	SOL2-PCFPU21X3BOPU	Urethane	3192	3404	3613	4037	4457	4878	5300	5721	6565
	SOL2-PCFPU21X3BOPW	Beech	3445	3656	3867	4289	4709	5132	5553	5973	6817
	24" Pre-Configured Freespan Center Arm Patient Unit - Open Arm 2 Seat, Mesh Back										
	SOL2-PCFPM24X2BOPU	Urethane	2177	2227	2273	2369	2463	2559	2654	2746	2890
	SOL2-PCFPM24X2BOPW	Beech	2369	2417	2463	2559	2654	2746	2844	2936	3080
	24" Pre-Configured Freespan Center Arm Patient Unit - Open Arm 2 Seat, Upholstered Back										
	SOL2-PCFPU24X2BOPU	Urethane	2293	2432	2571	2853	3135	3414	3698	3979	4539
	SOL2-PCFPU24X2BOPW	Beech	2481	2621	2763	3042	3324	3605	3888	4169	4730
	24" Pre-Configured Freespan Center Arm Patient Unit - Open Arm 3 Seat, Mesh Back										
	SOL2-PCFPM24X3BOPU	Urethane	3096	3165	3238	3381	3521	3665	3809	3950	4162
	SOL2-PCFPM24X3BOPW	Beech	3348	3420	3490	3634	3774	3918	4060	4203	4416
	24" Pre-Configured Freespan Center Arm Patient Unit - Open Arm 3 Seat, Upholstered Back										
	SOL2-PCFPU24X3BOPU	Urethane	3257	3468	3678	4099	4521	4942	5363	5784	6627
	SOL2-PCFPU24X3BOPW	Beech	3510	3718	3931	4352	4774	5194	5614	6035	6879

ORDERING NOTES: A drawing showing the configuration of the multiple seating and tables is required with each purchase order. Complete Mesh backs (21" & 24") can be ordered and field replaced.

Solis Pre-configured Patient Option Upcharges	\$ List		\$ List
CAL 133 & Moisture Barrier (per yard)	64	Beech Wood Side Rails Upgrade (per chair)	127
Kinetic Back option (not available for 30" & 44")	120	Solid Surface Arm (per pair) - Gr A White	488
Patient chair - Removable Seat Cover (per seat)	90	Solid Surface Arm (per pair) - Gr A Color	505
21" & 24" - Removeable Back Covers (per back)	61	Solid Surface Arm (per pair) - Gr B	542
Combination Upholstery - dual fabrics (per chair)	33	Solid Surface Arm (per pair) - Gr C	586
Combination Upholstery - Three fabrics (per chair)	64	Solid Surface Arm (per arm) - Gr A White	244
Beech Wood Side Rails Upgrade (per chair)	127	Solid Surface Arm (per arm) - Gr A Color	253
Maple wood Side Rails Upgrade (per chair)	159	Solid Surface Arm (per arm) - Gr B	271
21" & 24" Cleanable Under-seat Splashguard	40	Solid Surface Arm (per arm) - Gr C	293
Non-Marring Glide	37	Non-locking Soft Casters (21" & 24" chairs) -4 set	184
Maple Arm upgrade per arm (add to beech price)	80	Non-locking Soft Casters (21" & 24" chairs) -2 set	113
		Non-locking Hard Casters (21" & 24" chairs) -4 set	120
		Non-locking Hard Casters (21" & 24" chairs) -2 set	80






Additional features and options information see page 24, closed arm panel upcharges page 104.

Note: Soft & Hard casters are also available locking, clearly mark on the purchase order.






PRODUCT CODE KEY

Line	Series	Chair Type	Back Type	Size	Unit Style	Arm Type
SOL	2	PCFP	U	21X2	A	OPW
Solis	Chair	Pre-configured Freespan Multiple Patient Unit	Upholstered Back		Unit with no Center Arm	Open Arm - Wood Arm
			M	21X3	B	OPU
			Mesh Back		Unit with Center Arm	Open Arm Urethane Arm
				24X2		CLW
						Closed Arm -Wood Arm
				24X3		CLU
						Closed Arm Urethane Arm


SOLIS | REPLACEMENT COMPONENTS - MULTIPLE SEATING


Description	Model	COM		COL	FABRIC GRADES			LEATHER			Yardage	Weight	Cube
		1	2	3	4	5	6	7	8	9			
	21" Replacement Guest Upholstered Backs SOL2-RBGU21	567	610	651	710	778	835	904	987	1071	1.5	14	2.7
	21" Replacement Guest Mesh Backs SOL2-RBGM21	477										10	2.7
	24" Replacement Guest Upholstered Backs SOL2-RBGU24	581	621	664	722	790	849	916	1002	1086	1.5	15	2.8
	24" Replacement Guest Mesh Backs SOL2-RBGM24	497										11	2.8
	30" Replacement Guest Upholstered Backs SOL2-RBGU30	632	679	727	795	871	938	1016	1111	1207	1.6	19	3.4
	44" Replacement Guest Upholstered Backs SOL2-RBGU44	794	843	889	957	1034	1102	1179	1273	1371	2.25	28	4.8
	21" Replacement Guest Upholstered Back Cover SOL2-RBCGU21	198	240	287	340	408	467	535	618	702	1.5	2	.8
	24" Replacement Guest Upholstered Back Cover SOL2-RBCGU24	198	240	282	340	408	467	535	618	702	1.5	2.3	.8
	30" Replacement Guest Upholstered Back Cover SOL2-RBCGU30	214	260	309	378	453	520	597	693	789	1.6	2.6	.8
	44" Replacement Guest Upholstered Back Cover SOL2-RBCGU44	218	267	315	382	458	527	602	697	795	2.25	3.5	.8
	21" Replacement Patient Upholstered Backs SOL2-RBPU21	673	732	793	877	973	1058	1152	1272	1393	2.0	21	3.8
	21" Replacement Patient Mesh Backs SOL2-RBPM21	451										15	3.8
	24" Replacement Patient Upholstered Backs SOL2-RBPU24	711	771	832	915	1012	1095	1192	1312	1433	2.0	21	3.8
	24" Replacement Patient Mesh Backs SOL2-RBPM24	517										17	3.8
	30" Replacement Patient Upholstered Backs SOL2-RBPU30	857	937	1015	1122	1247	1358	1483	1640	1794	2.2	24	4.8
	21" Replacement Patient Upholstered Back Cover SOL2-RBCPU21	253	312	372	456	554	636	732	852	973	2.0	2.5	.8
	24" Replacement Patient Upholstered Back Cover SOL2-RBCPU24	254	313	374	457	555	637	733	853	974	2.0	2.7	.8
	30" Replacement Patient Upholstered Back Cover SOL2-RBCPU30	306	386	464	571	697	807	932	1088	1244	2.2	3	.8
	Replacement Mesh Back Top Bar SOL2-RMBTB21	33									2.5	.5	
	SOL2-RMBTB24	34									3.0	.7	


SOLIS | REPLACEMENT COMPONENTS - MULTIPLE SEATING

Description	Model	COM		COL	FABRIC GRADES			LEATHER			Yardage	Weight	Cube	
		1	2	3	4	5	6	7	8	9				
	21" Replacement Seat SOL2-RS21	389	418	443	481	523	561	605	659	715	.9	9	2.7	
	24" Replacement Seat SOL2-RS24	409	436	464	501	543	583	626	679	733	.9	10	2.7	
	30" Replacement Seat SOL2-RS30	487	513	540	577	620	659	702	756	809	.9	12	3.4	
	44" Replacement Seat SOL2-RS44	628	662	694	740	793	840	892	958	1022	1.1	14	4.8	
	21" Replacement Seat Cover SOL2-RSC21	130	159	185	223	267	304	374	403	455	1.0	1.6	.8	
	24" Replacement Seat Cover SOL2-RSC24	134	160	189	227	270	306	350	405	458	1.0	1.7	.8	
	30" Replacement Seat Cover SOL2-RSC30	136	161	189	227	270	306	350	405	458	1.0	2	.8	
	44" Replacement Seat Cover SOL2-RSC44	152	186	218	265	318	363	416	483	547	1.1	2.5	.8	
FREESPAN 	21" Replacement Freespan Seat - A Center SOL2-RS21A-C	396	423	451	488	532	567	612	665	720	0.9	9	2.7	
	21" Replacement Freespan Seat - A Left Facing SOL2-RS21A-L	392	420	448	486	530	564	610	663	718	0.9	9	2.7	
	21" Replacement Freespan Seat - A Right Facing SOL2-RS21A-R	392	420	448	486	530	564	610	663	718	0.9	9	2.7	
	21" Replacement Freespan Seat - B SOL2-RS21B	392	420	448	486	530	564	610	663	718	0.9	9	2.7	
	24" Replacement Freespan Seat - A Center SOL2-RS24A-C	415	443	469	509	552	589	633	687	740	0.9	9	2.7	
	24" Replacement Freespan Seat - A Left Facing SOL2-RS24A-L	412	441	467	507	547	586	630	685	738	0.9	9	2.7	
	24" Replacement Freespan Seat - A Right Facing SOL2-RS24A-R	412	441	467	507	547	586	630	685	738	0.9	9	2.7	
	24" Replacement Freespan Seat - B SOL2-RS24B	412	441	467	507	547	586	630	685	738	0.9	9	2.7	
		21" Replacement Freespan Seat Cover - A Center SOL2-RSC21A-C	130	159	185	223	267	304	347	403	455	0.9	9	2.7
		21" Replacement Freespan Seat Cover- A Left Facing SOL2-RSC21A-L	130	159	185	223	267	304	347	403	455	0.9	9	2.7
21" Replacement Freespan Seat Cover- A Right Facing SOL2-RSC21A-R		130	159	185	223	267	304	347	403	455	0.9	9	2.7	
21" Replacement Freespan Seat Cover- B SOL2-RSC21B		130	159	185	223	267	304	347	403	455	0.9	9	2.7	
24" Replacement Freespan Seat Cover- A Center SOL2-RSC24A-C		134	160	186	224	268	304	348	404	456	0.9	9	2.7	
24" Replacement Freespan Seat Cover- A Left Facing SOL2-RSC24A-L		134	160	186	224	268	304	348	404	456	0.9	9	2.7	
24" Replacement Freespan Seat Cover- A Right Facing SOL2-RSC24A-R		134	160	186	224	268	304	348	404	456	0.9	9	2.7	
24" Replacement Freespan Seat Cover- B SOL2-RSC24B		134	160	186	224	268	304	348	404	456	0.9	9	2.7	
	Replacement Splash Guard SOL2-RSG21	90										1	.3	
	SOL2-RSG24	110										2	.4	
	SOL2-RSG30	154										3	.5	
	SOL2-RSG44	166										4	.6	


SOLIS | REPLACEMENT COMPONENTS - MULTIPLE SEATING


Description	Model	COM		COL			FABRIC GRADES			LEATHER			Yardage	Weight	Cube
		1	2	3	4	5	6	7	8	9					
	Replacement Closed Arm SOL2-RCA	207	218	231	247	267	283	303	327	350	0.4	6	.9		


Description	Model	Price	Weight	Cubes
	Replacement Side Frame - Interim SOL2-RSFIB	129	7	1.2
	Replacement Side Frame - Interim - No Anti-Microbial SOL2-RSFIBX	118	7	1.2

	Replacement Side Frame - Start SOL2-RSFS	134	9	1.5
	Replacement Side Frame - Start - No Anti-Microbial SOL2-RSFSX	111	9	1.5
	Replacement Side Frame - Center SOL2-RSFC	134	9	1.5
	Replacement Side Frame - Center - No Anti-Microbial SOL2-RSFCX	111	9	1.5
	Replacement Side Frame - End SOL2-RSFE	134	9	1.5
	Replacement Side Frame - End - No Anti-Microbial SOL2-RSFEX	111	9	1.5








	Replacement Side Frame - Start - 1 Glide, 1 Caster SOL2-RSFSC	172	9.5	1.5
	Replacement Side Frame - Start - 1 Glide, 1 Caster- No Anti-Microbial SOL2-RSFSCX	138	9.5	1.5
	Replacement Side Frame - End - 1 Glide, 1 Caster SOL2-RSFEC	172	9.5	1.5
	Replacement Side Frame - End - 1 Glide, 1 Caster- No Anti-Microbial SOL2-RSFECX	138	9.5	1.5

	Replacement Side Frame - Start - 2 Caster SOL2-RSFSC2	149	10	1.5
	Replacement Side Frame - Start - 2 Caster- No Anti-Microbial SOL2-RSFSC2X	145	10	1.5
	Replacement Side Frame - End - 2 Caster SOL2-RSFEC2	149	10	1.5
	Replacement Side Frame - End - 2 Caster- No Anti-Microbial SOL2-RSFEC2X	145	10	1.5

	Replacement Wood Side Rail Cover - Beech SOL2-RSRCB	180	1.0	.3
	Replacement Wood Side Rail Cover - Maple SOL2-RSRCM	231		

	Replacement Arm Cap - Urethane SOL2-RACU	70	1.5	.2			
	Replacement Arm Cap - Beech SOL2-RACWB	213	1.0	.2			
	Replacement Arm Cap - Maple SOL2-RACWM	229	1.0	.2			
		Grade	Grade	Grade- B	Grade- C		
		A- White	A- Color				
	Replacement Arm Cap - Solid Surface SOL2-RACSS	256	261	282	304	2	.2


SIN 339113H - Hospital Geriatric Chairs & Lounge
SOLIS | REPLACEMENT COMPONENTS

Description	Model	Price	Weight	Cubes
	Replacement Link/Ganging Brackets - Table to Chair SOL2-RLKB1	68	2.0	.2
	Replacement Link/Ganging Brackets - Chair to Chair SOL2-RLKB2	51	2.0	.2
	Replacement Link/Ganging Brackets - Chair to Chair (set of 10) SOL2-RLKB3	159	1.0	.2
	Replacement Glide - Front SOL2-RGF	22	.5	.1
	Replacement Glide - Back SOL2-RGB	22	.5	.1
	Replacement Glide - Easy Access - Front SOL2-RGFEA	29	.5	.1
	Replacement Glide - Set of 4 SOL2-RGS4	24	2	.1
	Replacement Caster Glide - Front SOL2-RGFC	23	2	.1
	Replacement Caster Glide - Back SOL2-RGBC	23	2	.1
	Replacement Caster - Hard Wheel SOL2 - RCH	30	1.5	.3
	Replacement Caster - Soft Wheel SOL2 - RCS	33	1.5	.3
	Replacement Stretcher SOL2-RSTRETCHER21	182	1.0	.3
	SOL2-RSTRETCHER24	186	1.5	.4
	SOL2-RSTRETCHER21X	178	1.0	.5
	SOL2-RSTRETCHER24X	183	1.5	.6

LEED CI CREDITS



MATERIAL CONTENT:



PRE-CONSUMER
 RECYCLED CONTENT = 15.28%

POST-CONSUMER
 RECYCLED CONTENT = 21.71%

Up to 45.76% of this Solis product is recyclable at the end of its useful life.

CONTRIBUTES TO

CREDIT 2.1 - 2.2	Construction Waste Management	1-2 point(s)
CREDIT 3.3	Resource Reuse	1 point
CREDIT 4.1	Recycled Content	1 point
CREDIT 4.2	Recycled Content	1 point
CREDIT 4.5	Low Emitting Materials, Systems & Seating	1 point
CREDIT 5.1	Regional Materials*	1 point
CREDIT 7	Certified Wood (MUST BE REQUESTED)	1 point(s)

*This credit is only applicable if in total 20% of the combined value of the procurement of construction materials and in the furniture are manufactured within a radius of 500 miles. This credit will apply if the installation of the finished product occurs within 500 miles of Kitchener, Ontario.

level® CERTIFICATION, AIR EMISSIONS AND FSC® CERTIFICATION



level® CERTIFICATION

BIFMA's e3 Furniture Sustainability Standard is a voluntary, multi-attribute standard that measures the degree of sustainability of furniture. This standard evaluates product and company environmental attributes and compliance systems in a wide range of elements which include Materials, Energy & Atmosphere, Human & Ecosystem Health and Social Responsibility. Solis products have earned level®, BIFMA's sustainability certification program for furniture, certification through third-party verification against the e3 standard.



AIR-EMISSIONS

All Solis products are supplied air-emissions certified. Contact customer service for information.

FSC®





In 2005, Krug received Forest Stewardship Council® (FSC®) Chain-of-Custody certification for our manufacturing facilities. The FSC® Chain-of-Custody tracks certified wood from seedling to final sale. It verifies that the material for our FSC® certified products only come from well-managed, FSC®-certified forests and other controlled sources. FSC® is dedicated to the promotion of responsible forest management worldwide helping to take care of forests for future generations. Solis and other Krug products can be specified with FSC® Certification. Contact customer service for further information, pricing and lead times.

Architects, designers, and building professionals can specify FSC®-certified products in order to achieve a point from the US. Green Building Council's Leadership in Energy and Environmental Design (LEED) Rating System.

SOLIS | EASY ACCESS CHAIR

DIMENSIONS & COM. REQUIREMENTS

	Overall Width	Overall Depth	Overall Height	Seat Height	Height of Arms from Floor	Width Between Arms	Seat Depth	Shipping Weight	Cube	COM Yardage Seat & Back	COM Yardage Seat	COM Yardage Back
UPHOLSTERED GUEST BACK												
21" Seat	25	30.75	40.5	24.5	32	20	20	51	16	1.6	0.9	1.6
24" Seat	28	30.75	40.5	24.5	32	23	20	55	18	1.6	0.9	1.6
MESH GUEST BACK												
21" Seat	25	30.75	40.5	24.5	32	20	20	49	16	-	0.9	-
24" Seat	28	30.75	40.5	24.5	32	23	20	52	18	-	0.9	-
UPHOLSTERED PATIENT BACK												
21" Seat	25	30.75	49.75	24.5	32	20	20	54	21	2.1	0.9	2.0
24" Seat	28	30.75	49.75	24.5	32	23	20	58	23	2.1	0.9	2.0
MESH PATIENT BACK												
21" Seat	25	30.75	49.75	24.5	32	20	20	50	21	-	0.9	-
24" Seat	28	30.75	49.75	24.5	32	23	20	53	23	-	0.9	-
Footrest height (All Models) 7.25"												

DESCRIPTION/MODEL	Arm Type	COM.		COL			FABRIC GRADES			LEATHER	
		1	2	3	4	5	6	7	8	9	
	21" Guest, Open Arm, Mesh Back										
	SOL2-HGM21OPU Urethane	1460	1493	1527	1592	1661	1727	1791	1857	1960	
	SOL2-HGM21OPW Beech	1587	1619	1653	1717	1786	1853	1918	1985	2087	
	21" Guest, Open Arm, Upholstered Back										
SOL2-HGU21OPU Urethane	1537	1592	1646	1758	1867	1979	2088	2196	2419		
SOL2-HGU21OPW Beech	1664	1717	1774	1884	1993	2105	2215	2324	2545		
	24" Guest, Open Arm, Mesh Back										
	SOL2-HGM24OPU Urethane	1491	1524	1557	1622	1689	1755	1821	1886	1990	
	SOL2-HGM24OPW Beech	1617	1647	1683	1748	1816	1882	1947	2016	2117	
	24" Guest, Open Arm, Upholstered Back										
SOL2-HGU24OPU Urethane	1568	1624	1680	1792	1908	2019	2131	2241	2466		
SOL2-HGU24OPW Beech	1695	1752	1808	1920	2033	2145	2255	2369	2594		
	21" Patient, Open Arm, Mesh Back										
	SOL2-HPM21OPU Urethane	1569	1604	1638	1703	1771	1836	1902	1968	2070	
	SOL2-HPM21OPW Beech	1697	1730	1764	1832	1896	1962	2030	2094	2196	
	21" Patient, Open Arm, Upholstered Back										
SOL2-HPU21OPU Urethane	1653	1728	1801	1947	2092	2241	2388	2539	2833		
SOL2-HPU21OPW Beech	1778	1854	1926	2073	2219	2369	2516	2665	2959		
	24" Patient, Open Arm, Mesh Back										
	SOL2-HPM24OPU Urethane	1617	1647	1683	1748	1816	1882	1947	2016	2117	
	SOL2-HPM24OPW Beech	1744	1776	1809	1878	1942	2007	2073	2140	2242	
	24" Patient, Open Arm, Upholstered Back										
SOL2-HPU24OPU Urethane	1702	1777	1854	2004	2158	2308	2460	2612	2917		
SOL2-HPU24OPW Beech	1827	1905	1980	2132	2282	2434	2587	2741	3042		

Solis Guest Option Upcharges

	\$ List		\$ List
CAL 133 & Moisture Barrier (per yard)	64	Solid Surface Arm (per pair) - Gr A White	488
Guest chair - Removable Seat Cover (per seat)	90	Solid Surface Arm (per pair) - Gr A Color	505
21" & 24" - Removeable Back Covers	58	Solid Surface Arm (per pair) - Gr B	542
21" & 24" Cleanable Under-seat Splashguard	40	Solid Surface Arm (per pair) - Gr C	586
Kinetic Back option	120	Maple Arm upgrade per arm (add to beech price)	80
Combination upholstery - Dual	33	Beech Wood Side Rails Upgrade (per chair)	127
Non-Marring Glide	36	Maple wood Side Rails Upgrade (per chair)	159

See page 3 for Features and Options information.

PRODUCT CODE KEY


Line	Series	Chair Type	Style	Back Type	Size	Arm Type
SOL	2	H	G	U	21	OPW
Solis	Chair	Easy Access	Guest	Upholstered Back		Open Arm - Wood Cap
			P	M	24	OPU
			Patient	Mesh		Open Arm Urethane Arm Cap

SOLIS BEHAVIORAL HEALTH | ENVIRONMENTAL SUMMARY

LEED CI CREDITS



MATERIAL CONTENT:



CONTRIBUTES TO

CREDIT	CONTRIBUTES TO	POINTS
CREDIT 2.1 - 2.2	Construction Waste Management	1-2 point(s)
CREDIT 3.3	Resource Reuse	1 point
CREDIT 4.1	Recycled Content	1 point
CREDIT 4.2	Recycled Content	1 point
CREDIT 4.5	Low Emitting Materials, (PLEASE ENQUIRE) Composite Wood & Laminate Adhesives	1 point
CREDIT 5.1	Regional Materials*	1 point
CREDIT 7	Certified Wood (PLEASE ENQUIRE)	1 point

* This credit is only applicable if in total 20% of the combined value of the procurement of construction materials and in the furniture are manufactured within a radius of 500 miles. This credit will apply if the installation of the finished product occurs within 500 miles of Toronto, Ontario.

level® CERTIFICATION, AIR EMISSIONS AND FSC® CERTIFICATION



level® CERTIFICATION

BIFMA's e3 Furniture Sustainability Standard is a voluntary, multi-attribute standard that measures the degree of sustainability of furniture. This standard evaluates product and company environmental attributes and compliance systems in a wide range of elements which include Materials, Energy & Atmosphere, Human & Ecosystem Health and Social Responsibility. Solis products have earned level®, BIFMA's sustainability certification program for furniture, certification through third-party verification against the e3 standard.



AIR-EMISSIONS

All Solis products are supplied air-emissions certified. Contact customer service for information.

FSC®

In 2005, Krug received Forest Stewardship Council® (FSC®) Chain-of-Custody certification for our manufacturing facilities. The FSC® Chain-of-Custody tracks certified wood from seedling to final sale. It verifies that the material for our FSC® certified products only come from well-managed, FSC®-certified forests and other controlled sources. FSC® is dedicated to the promotion of responsible forest management worldwide helping to take care of forests for future generations. Solis and other Krug products can be specified with FSC® Certification. Contact customer service for further information, pricing and lead times.



Architects, designers, and building professionals can specify FSC®-certified products in order to achieve a point from the U.S. Green Building Council's Leadership in Energy and Environmental Design (LEED) Rating System.

SOLIS BEHAVIORAL HEALTH | FEATURES



CLEAN OUT

All Solis seating models have a built-in clean out feature: a space at the back of the seat that allows dirt, debris and liquids to fall to the floor for easy clean up and maintenance - designed so that it does not detract from the comfort or appearance of the product.



STEEL SEAT FRAME

The structural seat frame is made from welded steel with a powder-coated finish that allows Solis to well exceed ANSI/BIFMA standards.




FLEX BACK

The ergonomically-designed back has a slight flexing action, which significantly enhances comfort.




WALL SAVER

The angle of the back and the rear legs are designed to keep the back away from the wall, to prevent wear and damage to both the chairs and to the walls of the facility. Patient and Guest chairs with mesh backs are excluded as they do not have the wall saver feature.



HIGH DENSITY FOAM

Solis features dual density foam that is soft on the outside for comfort, dense on the inside for high durability. The seat and back foam features a compound curvature that supports healthy sitting postures, while also designed to ease ingress and egress.



SECURED WOODEN ARM

Solis Wood Arm caps are fastened to the side frames with tamper resistant security screws. Wood arms are available in either beech or maple hardwood and in 22 Krug standard finishes. Maple arm caps are available for an up-charge of **\$77 list** per arm using beech pricing.



URETHANE ARM

Solis secured urethane arms are durable, comfortable, and long lasting. Urethane arms are available in three colors options; Black, Grey and Taupe.

TAMPER RESISTANT HARDWARE

All screws used on the Solis Behavioral Health units have been replaced with tamper resistant security screws.

GANGING

All Solis Freestanding chairs can be ganged using a ganging bracket. The powder-coated metal plate is fastened to the underside of the steel side rails using the pre-existing holes in the frame.

SECURED GLIDES

Solis Behavioral Health chairs have their glides secured in place to prevent their removal and damage.

BOTTOM STAPLE COVER/SHIELD

Solis Behavioral Health chairs come standard with a black painted plywood cover underneath the seat. This cover is designed to prevent access to the upholstery staples of the seat and to prevent the hiding of objects underneath the seat. The cover is also designed to allow for regular ganging hardware and proper seat ventilation. The cover is secured to the unit with tamper resistant security screws.

BACK STAPLE COVER STRIP

The Solis Behavioral Health back upholstery has been altered to allow a staple cover strip to be attached; this will prevent access to the upholstery staples. The cover strip is nylon coated galvanized steel with vinyl coated ends to prevent any sharp edges. The back cover strip is fastened to the unit with tamper resistant security screws.

TUBULAR STEEL CHAIR FRAME

The overall aesthetic frame of the chair is built from structural steel tubing, both elliptical and rectangular for exceptional strength and appealing design. The frame is electro welded and polished joints for ease of cleaning and a one piece look. Available in eight powder-coated finishes. Silver Metallic is offered as Krug's standard finish. For all metal finishes other than Silver Metallic, there is a minimum quantity of 30 units per color and are available for an upcharge of **\$64 list** per seat/table. Microban anti-microbial finish is standard, with no upcharge, when frame finishes other than Silver Metallic is ordered. Solis Silver Metallic frames are available with an anti-microbial finish for an upcharge of **\$64 list** per chair or table. Upcharges for quantities less than 30 units per color, per order can be obtained through Customer Service.

FINISH DURABILITY

The Krug Enduraguard finish, a proprietary catalyzed varnish formulation, has been repeatedly shown, through independent laboratory testing, to be the industry leader in durability and abrasion resistance. The Krug finish looks better longer than competitors, and is uniquely suited to the demands of healthcare environments.

LATEX-FREE

Krug products are made with latex-free materials, to prevent the allergic reaction that latex causes in some people.

WEIGHT CAPACITIES

Weight capacities are as follows:
Guest & Patient Chairs (21" & 24") - **500 lbs**
Plus Chairs (30" & 44") - **750 lbs**

SOLIS BEHAVIORAL HEALTH | OPTIONS




SLED BASE

The Solis side frames legs have the option to be tied front to back with a steel rail, this will strengthen the frames and eliminate the option of having legs.



KINETIC BACK OPTION

This optional feature provides the chair back with a very pleasant and comfortable rocking motion, which can significantly enhance long-term sitting for patients and guests alike. The durable spring-loaded mechanism provides a range of motion of 20 degrees, and can be field-installed or replaced. It's available on any Solis chair back - Guest, Patient and Multiple Seating - with the exception of the 30" and 44" sizes.



CLOSED ARM

Solis closed arm has an upholstered arm panel built into the side frame. It is between the middle rail on the side frame and the top of the arm.



FULLY CLOSED ARM (SLEIGH BASE ONLY)

The fully closed arm includes the regular closed arm, but also adds a second upholstered arm panel between the middle rail on the side frame and the sleigh base bottom. This feature is only available when the sleigh base option is selected.

FLOOR ANCHOR BRACKETS (SLEIGH BASE ONLY)

Floor mounting brackets are supplied to be secured to the bottom of the Solis sleigh base with tamper resistant security screws. The hardware to attach the brackets to the floor is not provided by Krug.

WEIGHTED SHIELD

In place of the Bottom Staple Cover, a weighted black coated steel version is also available. This steel shield is designed to add enough weight for the product to be a minimum of 80 lbs. The shield is also designed to allow standard ganging hardware as well as proper seat ventilation. This is all achieved while also covering/preventing all access to the upholstery staples under the seat. The Weighted Shield is fastened with tamper-resistant security screws.

COMBINATION UPHOLSTERY OPTION

When combination upholstery is specified with fabric of the same grade or COM, an upcharge for dual fabrics is **\$33 list** per unit and **\$64 list** per unit for three fabrics will be applied. When graded in combination upholstery is selected, use the highest grade upholstery selected or to obtain a quote for blended grading contact Customer Service (please provide the fabrics specified and location of where each fabric is to be applied on the product).

ANTI-MICROBIAL FINISH

Solis Silver Metallic frames are available with an anti-microbial finish for an upcharge of **\$64 list** per chair or table.

CAL133 & MOISTURE BARRIER

California Technical Bulletin 133 is a flammability test for seating. Krug offers a compliance method, in combination with non-flammable upholstery covers, may enable products to meet certification requirements for this test. This process at the same time also provides the products with a Moisture Barrier - a treatment that helps to prevent the passage of liquids and moisture to inside of the upholstered components - thereby conferring sanitary and anti-infection benefits. So when CAL 133 is specified, the product also automatically has a Moisture Barrier, and when a Moisture Barrier is specified, the product also features the compliance method and low flammability features of CAL 133.

The application of this up-charge and the compliance method does not mean that the specific configuration of product and upholstery cover are tested and officially certified as being CAL133 compliant. If the official certification is required, Krug will provide this (through an independent certified testing laboratory) at a charge of \$917 per item, plus the cost of the product to be tested. Lead time for certification testing is typically 4-8 weeks. Krug assumes no responsibility for the testing of our products in combination with upholstery covers, or for the results of any testing conducted. Some specific configurations of products and upholstery have already been tested. Please contact Customer Service for additional information. CAL 133 and Moisture Barrier is available for **\$64 list** per yard.

REMOVABLE COVERS & REPLACEMENT COMPONENTS

Optional Removeable seat and back covers can be quickly installed on Solis products that were originally ordered with the Removeable cover option. Replacement seat and back covers can also be installed on Solis products that were not originally ordered with the Removeable cover option, with some simple staple removal on the original seats and backs. Complete Mesh backs can be ordered and field replaced.

NO SPRING SEATS

The springs in the seat have been removed and replaced with a solid plywood seat pan. Additional foam has also been added in place of the springs for comfort.

TAMPER-RESISTANT SPLASHGUARD

All Solis seating models are available with a coated steel moisture barrier that covers and enclosed the underside of the seat (while still allowing air transfer and ventilation in and out of the seat cushion). The Splashguard replaces the Bottom Staple Cover on the underside of the seat. It is designed to still allowing ganging and has folded metal edges to prevent any sharp edges. The splashguard is fastened with tamper resistant security screws.

SOLIS BEHAVIORAL HEALTH | GUEST - DIMENSIONS & COM REQUIREMENTS

DIMENSIONS



	Overall Width	Overall Depth	Overall Height	Seat Height	Height of Arms from Floor	Width Between Arms	Seat Depth	Base Shipping Weight	Cubes
21" Seat	25	28	34.5	18.5	26	20	20	51	16
24" Seat	28	28	34.5	18.5	26	23	20	55	18
30" Seat	34	28	34.5	18.5	26	29	20	60	22
44" Seat	48	28	34.5	18.5	26	43	20	74	31

COM - YARDAGE REQUIREMENTS


	Yardage Seat & Back	Yardage Seat	Yardage Back	Yardage Closed Upper Arm Panel	Yardage Fully Closed Arm Panel (Upper & Lower)
21" & 24" - One Chair	1.6	0.9	1.6	0.8	1.6
21" & 24" - Two Chairs	3.1	1.3	1.6	1.2	2.4
21" & 24" - Three Chairs	4.7	2.1	3.7	1.6	3.2
30" Plus - One Chair	2.5	0.9	1.6	1.6	3.2
30" Plus - Two Chairs	5	1.8	3.2	1.2	2.4
30" Plus - Three Chairs	7.5	2.7	4.8	1.6	3.2
44" Plus - One Chair	2.5	0.9	2.3	0.8	1.6
44" Plus - Two Chairs	5	1.8	3.9	1.2	2.4
44" Plus - Three Chairs	7.5	2.7	5.5	1.6	3.2

Closed Arm Panels (per chair) - please add the following up charges for closed arm panels.







Fabric Grades	(COM) 1	2	(COL) 3	4	5	6	7	Leather 8	9	COM
Closed Arm Panel (1 arm)	208	224	238	267	294	321	350	379	435	0.4
Closed Arm Panels (2 arms)	418	448	477	531	588	643	699	757	869	0.8



Fully Closed Arm (1 arm)	339	365	391	436	483	529	576	627	707	1.5
Fully Closed Arm (2 arms)	677	730	782	872	967	1054	1151	1253	1412	3



SOLIS BEHAVIORAL HEALTH | GUEST

DESCRIPTION/MODEL	COM		COL		FABRIC GRADES			LEATHER			
	1	2	3	4	5	6	7	8	9		
	21" Open Arm, Mesh Back										
	SOL2-GBHM21OPU	Urethane	1119	1151	1181	1245	1309	1372	1434	1499	1596
	SOL2-GBHM21OPW	Beech	1240	1271	1304	1367	1429	1492	1556	1619	1716
	21" Open Arm, Upholstered Back										
	SOL2-GBHU21OPU	Urethane	1169	1220	1271	1373	1477	1578	1678	1779	1985
	SOL2-GBHU21OPW	Beech	1289	1340	1391	1493	1594	1697	1801	1899	2106
	24" Open Arm, Mesh Back										
	SOL2-GBHM24OPU	Urethane	1161	1192	1223	1285	1349	1414	1478	1538	1638
	SOL2-GBHM24OPW	Beech	1281	1311	1342	1405	1468	1534	1596	1661	1756
	24" Open Arm, Upholstered Back										
	SOL2-GBHU24OPU	Urethane	1209	1262	1312	1415	1515	1619	1719	1821	2028
	SOL2-GBHU24OPW	Beech	1331	1381	1433	1535	1638	1818	1840	1942	2146
	30" Open Arm, Upholstered Back										
	SOL2-GBHU30OPU	Urethane	1443	1522	1604	1761	1922	2083	2239	2401	2718
	SOL2-GBHU30OPW	Beech	1563	1642	1724	1882	2042	2201	2359	2522	2839
	44" Open Arm, Upholstered Back										
	SOL2-GBHUH44OPU	Urethane	1606	1686	1765	1923	2085	2241	2405	2562	2880
	SOL2-GBHUH44OPW	Beech	1727	1806	1884	2043	2205	2361	2524	2682	2999

ORDERING NOTES: Solis Behavioral Health guest chairs are standard with; secured glides, secured Arms, Bottom Staple shield/Cover, Non-Accessible Staples (Bottom of back) and Tamper- Resistant Hardware.

Solis Guest Option Upcharges	\$ List	\$ List
CAL 133 & Moisture Barrier (per yard)	64	30" & 44" - Removable Back Cover (per back)
Guest chair - Removable Seat Cover	80	Kinetic Back option
21" & 24" - Removeable Back Cover	58	Maple Arm upgrade per arm (add to beech price)
Combination Upholstery - dual fabrics	33	Non-Marring Glide
Combination Upholstery -Three fabrics	64	

Solis Behavioral Health Option Upcharges	\$ List	\$ List
Plywood Seat / No Springs	121	Weight Shield (to min 80lbs) - 21" Uph.
Sled Base	265	Weight Shield (to min 80lbs) - 21" Mesh
Anchor to Floor (Sleigh base only)	359	Weight Shield (to min 80lbs) - 24" Uph.
21" Tamper- Resistant Splashguard	157	Weight Shield (to min 80lbs) - 24" Mesh
24" Tamper- Resistant Splashguard	165	Weight Shield (to min 80lbs) - 30" Uph.
30" Tamper- Resistant Splashguard	340	Weight Shield (to min 80lbs) - 44" Uph.
44" Tamper- Resistant Splashguard	363	

Solis Behavioral Health guest chairs have the option of Closed or Fully Closed arms, change the last 3 letters of the model number to the required arm type from the Product Code Key below and add the upcharge on page 423.

PRODUCT CODE KEY

Line	Series	Chair Type	Back Type	Size	Arm Type
SOL	2	GBH	U	21	OPU
Solis	Chair	Guest Seating	Upholstered Back		Open Arm - Urethane
		PBH	M	24	OPW
		Patient Seating	Mesh Back 21" & 24" Only		Open Arm - Wood
				30	CLW
					Closed Arm - Wood
				44	CLU
					Closed Arm - Urethane
					FCW
					Fully Closed Arm - Wood
					FCU
					Fully Closed Arm - Urethane

SOLIS BEHAVIORAL HEALTH | PATIENT -DIMENSIONS & COM REQUIREMENTS

DIMENSIONS

	Overall Width	Overall Depth	Overall Height	Seat Height	Height of Arms from Floor	Width Between Arms	Seat Depth	Base Shipping Weight	Cubes
UPHOLSTERED BACK									
21" Seat	25	28	43.75	18.5	26	20	20	54	21
24" Seat	28	28	43.75	18.5	26	23	20	58	23
30" Seat	34	28	43.75	18.5	26	29	20	64	28

COM - YARDAGE REQUIREMENTS

	Yardage Seat & Back	Yardage Seat	Yardage Back	Yardage-Closed Upper Arm Panel	Yardage-Fully Closed Arm Panel (Upper & Lower)
21" & 24" - One Chair	2.1	0.9	2	0.8	1.6
21" & 24" -Two Chairs	4	1.3	3.4	1.2	2.4
21" & 24" - Three Chairs	6.1	2.1	5.4	1.6	3.2
30" Plus - One Chair	3.1	0.9	2.2	0.8	1.6
30" Plus - Two Chairs	6.2	1.8	4.4	1.2	2.4
30" Plus - Three Chairs	9.3	2.7	6.6	1.6	3.2

ORDERING NOTES:


COMBINATION UPHOLSTERY OPTION

When combination upholstery is specified with fabric of the same grade or COM, an upcharge for dual fabrics is **\$33 list** per unit and **\$64 list** per unit for three fabrics will be applied. When graded in combination upholstery is selected, use the highest grade upholstery selected or to obtain a quote for blended grading contact Customer Service (please provide the fabrics specified and location of where each fabric is to be applied on the product). Complete Mesh backs (21" & 24") can be ordered and field replaced.


The standard **Solis Frame Color** is Silver Metallic. Additional frame colors are available for an upcharge of **\$64 list** per arm frame pair, please see **page 24** for color selection and required ordering quantities. Silver metallic frames are available with an anti-microbial finish for an upcharge of **\$64 list** per arm frame pair or table.

Closed Arm Panels (per chair) - please add the following up charges for closed arm panels.




Fabric Grades	(COM) 1	(COM) 2	(COL) 3	4	5	6	7	Leather 8	9	COM
Closed Arm Panel (1 arm)	208	224	238	267	294	321	350	379	435	0.4
Closed Arm Panels (2 arms)	418	448	477	531	588	643	699	757	869	0.8



Fully Closed Arm (1 arm)	339	365	391	436	483	529	576	627	707	1.5
Fully Closed Arm (2 arms)	677	730	782	872	967	1054	1151	1253	1412	3



SOLIS BEHAVIORAL HEALTH | PATIENT

DESCRIPTION/MODEL	COM		COL			FABRIC GRADES			LEATHER		
	1	2	3	4	5	6	7	8	9		
	21" Open Arm, Mesh Back										
	SOL2-PBHM21OPU	Urethane	1164	1241	1272	1335	1398	1461	1526	1589	1688
	SOL2-PBHM21OPW	Beech	1331	1360	1393	1456	1519	1583	1644	1709	1808
	21" Open Arm, Upholstered Back										
	SOL2-PBHU21OPU	Urethane	1265	1331	1396	1533	1664	1801	1932	2064	2333
	SOL2-PBHU21OPW	Beech	1384	1451	1518	1653	1782	1921	2054	2186	2453
	24" Open Arm, Mesh Back										
	SOL2-PBHM24OPU	Urethane	1247	1281	1311	1374	1439	1503	1565	1629	1727
	SOL2-PBHM24OPW	Beech	1370	1401	1431	1494	1559	1622	1686	1748	1845
	24" Open Arm, Upholstered Back										
	SOL2-PBHU24OPU	Urethane	1305	1372	1439	1570	1705	1839	1974	2108	2377
	SOL2-PBHU24OPW	Beech	1423	1492	1559	1692	1825	1959	2092	2229	2496
	30" Open Arm, Upholstered Back										
	SOL2-PBHU30OPU	Urethane	1640	1741	1837	2033	2234	2431	2629	2824	3220
	SOL2-PBHU30OPW	Beech	1760	1860	1957	2155	2354	2552	2746	2946	3342

Solis Guest Option Upcharges	\$ List	\$ List	
CAL 133 & Moisture Barrier (per yard)	64	30" - Removable Back Cover (per back)	80
Guest chair - Removable Seat Cover	80	Kinetic Back option	120
21" & 24" - Removeable Back Cover	58	Maple Arm upgrade per arm (add to beech price)	80
Combination Upholstery - dual fabrics	33	Non-Marring Glide	37
Combination Upholstery -Three fabrics	64		

Solis Behavioral Health Option Upcharges	\$ List	\$ List	
Plywood Seat / No Springs	121	Weight Shield (to min 80lbs) - 21" Uph.	408
Sled Base	265	Weight Shield (to min 80lbs) - 21" Mesh	486
Anchor to Floor (Sleigh base only)	359	Weight Shield (to min 80lbs) - 24" Uph.	337
21" Tamper- Resistant Splashguard	157	Weight Shield (to min 80lbs) - 24" Mesh	412
24" Tamper- Resistant Splashguard	165	Weight Shield (to min 80lbs) - 30" Uph.	180
30" Tamper- Resistant Splashguard	340		

Solis Behavioral Health guest chairs have the option of Closed or Fully Closed arms, change the last 3 letters of the model number to the required arm type from the Product Code Key below and add the upcharge on page 425.

PRODUCT CODE KEY

Line	Series	Chair Type	Back Type	Size	Arm Type
SOL	2	GBH	U	21	OPU
Solis	Chair	Guest Seating	Upholstered Back		Open Arm - Urethane
		PBH	M	24	OPW
		Patient Seating	Mesh Back 21" & 24" Only		Open Arm - Wood
				30	CLW
					Closed Arm - Wood
				44	CLU
					Closed Arm - Urethane
					FCW
					Fully Closed Arm - Wood
					FCU
					Fully Closed Arm - Urethane

SOLIS BEHAVIORAL HEALTH | MULTIPLE SEATING - GUEST

DIMENSIONS & COM. REQUIREMENTS - START UNITS

	Overall Width	Overall Depth	Overall Height	Seat Height	Height of Arms from Floor	Width Between Arms	Seat Depth	Shipping Weight	Cube	COM. Seat & Back Yardage	COM. Fabric Seat Yardage	COM. Fabric Back Yardage	COM. Fabric Closed Arm Panel (1 Arm) Yardage	COM. Fabric Closed Arm Panel (2 Arms) Yardage
MESH BACK														
SGM21	25	28	34.5	18.5	26	20	20	41	16	-	0.9	-	0.4	0.8
SGM24	28	28	34.5	18.5	26	23	20	44	18	-	0.9	-	0.4	0.8
UPHOLSTERED BACK														
SGU21	25	28	34.5	18.5	26	20	20	43	16	1.6	0.9	1.6	0.4	0.8
SGU24	28	28	34.5	18.5	26	23	20	47	18	1.6	0.9	1.6	0.4	0.8
SGU30	34	28	34.5	18.5	26	29	20	52	22	2.5	0.9	2.5	0.4	0.8
SGU44	48	28	34.5	18.5	26	43	20	66	31	2.5	0.9	2.5	0.4	0.8

DIMENSIONS & COM. REQUIREMENTS - CENTER UNITS

	Overall Width	Overall Depth	Overall Height	Seat Height	Height of Arms from Floor	Width Between Arms	Seat Depth	Shipping Weight	Cube	COM. Seat & Back Yardage	COM. Fabric Seat Yardage	COM. Fabric Back Yardage	COM. Fabric Closed Arm Panel Yardage	
MESH BACK														
CGM21	23	28	34.5	18.5	26	20	20	35	16	-	0.9	-	0.4	
CGM24	26	28	34.5	18.5	26	23	20	38	18	-	0.9	-	0.4	
UPHOLSTERED BACK														
CGU21	23	28	34.5	18.5	26	20	20	37	16	1.6	0.9	1.6	0.4	
CGU24	26	28	34.5	18.5	26	23	20	41	19	1.6	0.9	1.6	0.4	
CGU30	32	28	34.5	18.5	26	29	20	46	22	2.5	0.9	2.5	0.4	
CGU44	46	28	34.5	18.5	26	43	20	60	31	2.5	0.9	2.5	0.4	

DIMENSIONS & COM. REQUIREMENTS - END UNITS

	Overall Width	Overall Depth	Overall Height	Seat Height	Height of Arms from Floor	Width Between Arms	Seat Depth	Shipping Weight	Cube	COM. Seat & Back Yardage	COM. Fabric Seat Yardage	COM. Fabric Back Yardage	COM. Fabric Closed Arm Panel Yardage	
MESH BACK														
EGM21	23	28	34.5	18.5	26	20	20	35	16	-	0.9	-	0.4	
EGM24	26	28	34.5	18.5	26	23	20	38	18	-	0.9	-	0.4	
UPHOLSTERED BACK														
EGU21	23	28	34.5	18.5	26	20	20	37	16	1.6	0.9	1.6	0.4	
EGU24	26	28	34.5	18.5	26	23	20	41	18	1.6	0.9	1.6	0.4	
EGU30	32	28	34.5	18.5	26	29	20	46	22	2.5	0.9	2.5	0.4	
EGU44	46	28	34.5	18.5	26	43	20	60	31	2.5	0.9	2.5	0.4	











ORDERING NOTES:

When ordering multiple Start, Center, End units please refer to [page 5](#) for Yardage Requirements.

Closed Arm Panels (per chair) - please add the following up charges for closed arm panels.

Fabric Grades	(COM) 1	(COL) 2	(COL) 3	(COL) 4	(COL) 5	(COL) 6	(COL) 7	(COL) 8	(COL) 9	Leather 8	Leather 9	COM
Closed Arm Panel (1 arm)	208	224	238	267	294	321	350	379	435	0.4		
Closed Arm Panels (2 arms)	418	448	477	531	588	643	699	757	869	0.8		
Fully Closed Arm (1 arm)	339	365	391	436	483	529	576	627	707	1.5		
Fully Closed Arm (2 arms)	677	730	782	872	967	1054	1151	1253	1412	3		

SOLIS BEHAVIORAL HEALTH | START, CENTER & END GUEST UNITS









DESCRIPTION/MODEL	COM		COL		FABRIC GRADES			LEATHER			
	1	2	3	4	5	6	7	8	9		
START											
	21" Open Arm Start Guest Unit, Mesh Back										
	SOL2-SGBHM21OPU	Urethane	1119	1151	1181	1245	1309	1372	1434	1499	1596
	SOL2-SGBHM21OPW	Beech	1240	1271	1304	1367	1429	1492	1556	1619	1716
	21" Open Arm Start Guest Unit, Upholstered Back										
	SOL2-SGBHU21OPU	Urethane	1169	1220	1271	1373	1477	1578	1678	1779	1985
	SOL2-SGBHU21OPW	Beech	1289	1340	1391	1493	1594	1697	1801	1899	2106
<hr/>											
	24" Open Arm Start Guest Unit, Mesh Back										
	SOL2-SGBHM24OPU	Urethane	1161	1192	1223	1285	1349	1414	1478	1538	1638
	SOL2-SGBHM24OPW	Beech	1281	1311	1342	1405	1468	1534	1596	1661	1756
	24" Open Arm Start Guest Unit, Upholstered Back										
	SOL2-SGBHU24OPU	Urethane	1209	1262	1312	1415	1515	1619	1685	1821	2028
	SOL2-SGBHU24OPW	Beech	1331	1381	1433	1535	1638	1818	1840	1942	2146
<hr/>											
	30" Open Arm Start Guest Unit, Upholstered Back										
	SOL2-SGBHU30OPU	Urethane	1443	1522	1604	1761	1922	2083	2239	2401	2718
	SOL2-SGBHU30OPW	Beech	1563	1642	1724	1882	2042	2201	2359	2522	2839
<hr/>											
	44" Open Arm Start Guest Unit, Upholstered Back										
	SOL2-SGBHU44OPU	Urethane	1606	1686	1765	1923	2085	2241	2405	2562	2880
	SOL2-SGBHU44OPW	Beech	1727	1806	1884	2043	2205	2361	2524	2682	2999
<hr/>											
CENTER											
	21" Open Arm Center Guest Unit, Mesh Back										
	SOL2-CGBHM21OPU	Urethane	1021	1054	1086	1147	1210	1273	1336	1401	1499
	SOL2-CGBHM21OPW	Beech	1083	1114	1143	1207	1271	1334	1396	1460	1559
	21" Open Arm Center Guest Unit, Upholstered Back										
	SOL2-CGBHU21OPU	Urethane	1064	1117	1168	1270	1372	1474	1572	1677	1881
	SOL2-CGBHU21OPW	Beech	1124	1177	1228	1331	1431	1534	1634	1738	1941
<hr/>											
	24" Open Arm Center Guest Unit, Mesh Back										
	SOL2-CGBHM24OPU	Urethane	1046	1081	1110	1172	1237	1302	1361	1425	1524
	SOL2-CGBHM24OPW	Beech	1108	1139	1170	1232	1297	1359	1422	1485	1584
	24" Open Arm Center Guest Unit, Upholstered Back										
	SOL2-CGBHU24OPU	Urethane	1093	1143	1195	1297	1398	1503	1604	1704	1909
	SOL2-CGBHU24OPW	Beech	1153	1205	1254	1357	1459	1562	1664	1765	1968

Solis Behavioral Health guest chairs have the option of Closed or Fully Closed arms, change the last 3 letters of the model number to the required arm type from the Product Code Key below and add the upcharge on page 39.

PRODUCT CODE KEY

Line	Series	Chair Type	Back Type	Size	Arm Type
SOL	2	SG	U	21	OPW
Solis	Chair	Start Unit Guest Multiple Seating	Upholstered Back		Open Arm - Wood Arm
		CG	M	24	OPU
		Center Unit Guest Multiple Seating	Mesh Back 21" & 24" Only		Open Arm Urethane Arm
		EG		30	CLW
		End Unit Guest Multiple Seating			Closed Arm - Wood
				44	CLU
					Closed Arm - Urethane
					FCW
					Fully Closed Arm - Wood
					FCU
					Fully Closed Arm - Urethane

SOLIS BEHAVIORAL HEALTH | CENTER & END GUEST UNITS

DESCRIPTION/MODEL	COM		COL			FABRIC GRADES			LEATHER		
	1	2	3	4	5	6	7	8	9		
 30" Open Arm Center Guest Unit, Upholstered Back	SOL2-CGBHU30OPU	Urethane	1310	1389	1467	1631	1788	1946	2107	2265	2585
	SOL2-CGBHU30OPW	Beech	1371	1449	1529	1690	1846	2006	2167	2324	2642
	<hr/>										
 44" Open Arm Center Guest Unit, Upholstered Back	SOL2-CGBHU44OPU	Urethane	1463	1545	1617	1781	1942	2103	2263	2419	2740
	SOL2-CGBHU44OPW	Beech	1524	1606	1685	1842	2002	2163	2322	2480	2800
	<hr/>										
END  21" Open Arm End Guest Unit, Mesh Back	SOL2-EGBHM21OPU	Urethane	1021	1054	1086	1147	1210	1273	1336	1401	1499
	SOL2-EGBHM21OPW	Beech	1083	1114	1143	1207	1271	1334	1396	1460	1559
	<hr/>										
 21" Open Arm End Guest Unit, Upholstered Back	SOL2-EGBHU21OPU	Urethane	1064	1117	1168	1270	1372	1474	1572	1677	1881
	SOL2-EGBHU21OPW	Beech	1124	1177	1228	1331	1431	1534	1634	1738	1941
	<hr/>										
 24" Open Arm End Guest Unit, Mesh Back	SOL2-EGBHM24OPU	Urethane	1046	1081	1110	1172	1237	1302	1361	1425	1524
	SOL2-EGBHM24OPW	Beech	1108	1139	1170	1232	1297	1359	1422	1485	1584
	<hr/>										
 24" Open Arm End Guest Unit, Upholstered Back	SOL2-EGBHU24OPU	Urethane	1093	1143	1195	1297	1398	1503	1604	1704	1909
	SOL2-EGBHU24OPW	Beech	1153	1205	1254	1357	1459	1562	1664	1765	1968
	<hr/>										
 30" Open Arm End Guest Unit, Upholstered Back	SOL2-EGBHU30OPU	Urethane	1310	1389	1467	1631	1788	1946	2107	2265	2585
	SOL2-EGBHU30OPW	Beech	1371	1449	1529	1690	1846	2006	2167	2324	2642
	<hr/>										
 44" Open Arm End Guest Unit, Upholstered Back	SOL2-EGBHU44OPU	Urethane	1463	1545	1617	1781	1942	2103	2263	2419	2740
	SOL2-EGBHU44OPW	Beech	1524	1606	1685	1842	2002	2163	2322	2480	2800

ORDERING NOTES:

The standard **Solis Frame Color** is Silver Metallic. Additional frame colors are available for an upcharge of **\$64 list** per arm frame pair, please see page 24 for color selection and required ordering quantities. Silver metallic frames are available with an anti-microbial finish for an upcharge of **\$64 list** per arm frame pair or table.

Solis Behavioral Health guest chairs have the option of Closed or Fully Closed arms, change the last 3 letters of the model number to the required arm type from the Product Code Key below and add the upcharge on page 427.

PRODUCT CODE KEY

Line	Series	Chair Type	Back Type	Size	Arm Type
SOL	2	SG	U	21	OPW
Solis	Chair	Start Unit Guest Multiple Seating	Upholstered Back		Open Arm - Wood Arm
		CG	M	24	OPU
		Center Unit Guest Multiple Seating	Mesh Back 21" & 24" Only		Open Arm Urethane Arm
		EG		30	CLW
		End Unit Guest Multiple Seating			Closed Arm - Wood
				44	CLU
					Closed Arm - Urethane
					FCW
					Fully Closed Arm - Wood
					FCU
					Fully Closed Arm - Urethane

SOLIS BEHAVIORAL HEALTH | MULTIPLE SEATING - PATIENT BACKS

DIMENSIONS & COM. REQUIREMENTS - START UNITS

	Overall Width	Overall Depth	Overall Height	Seat Height	Height of Arms from Floor	Width Between Arms	Seat Depth	Shipping Weight	Cube	COM. Seat & Back Yardage	COM. Fabric Seat Yardage	COM. Fabric Back Yardage	COM. Fabric Closed Arm Panel (1 Arm) Yardage	COM. Fabric Closed Arm Panel (2 Arms) Yardage
MESH BACK														
SPM21	25	28	43.75	18.5	26	20	20	42	21	-	0.9	-	0.4	0.8
SPM24	28	28	43.75	18.5	26	23	20	45	23	-	0.9	-	0.4	0.8
UPHOLSTERED BACK														
SPU21	25	28	43.75	18.5	26	20	20	46	21	2.1	0.9	2.0	0.4	0.8
SPU24	28	28	43.75	18.5	26	23	20	50	23	2.1	0.9	2.0	0.4	0.8
SPU30	34	28	43.75	18.5	26	29	20	56	28	3.1	0.9	2.2	0.4	0.8

DIMENSIONS & COM. REQUIREMENTS - CENTER UNITS

	Overall Width	Overall Depth	Overall Height	Seat Height	Height of Arms from Floor	Width Between Arms	Seat Depth	Shipping Weight	Cube	COM. Seat & Back Yardage	COM. Fabric Seat Yardage	COM. Fabric Back Yardage	COM. Fabric Closed Arm Panel Yardage
MESH BACK													
CPM21	23	28	43.75	18.5	26	20	20	36	21	-	0.9	-	0.4
CPM24	26	28	43.75	18.5	26	23	20	39	23	-	0.9	-	0.4
UPHOLSTERED BACK													
CPU21	23	28	43.75	18.5	26	20	20	40	21	2.1	0.9	2.0	0.4
CPU24	26	28	43.75	18.5	26	23	20	44	23	2.1	0.9	2.0	0.4
CPU30	32	28	43.75	18.5	26	29	20	50	28	3.1	0.9	2.2	0.4

DIMENSIONS & COM. REQUIREMENTS - END UNITS

	Overall Width	Overall Depth	Overall Height	Seat Height	Height of Arms from Floor	Width Between Arms	Seat Depth	Shipping Weight	Cube	COM. Seat & Back Yardage	COM. Fabric Seat Yardage	COM. Fabric Back Yardage	COM. Fabric Closed Arm Panel Yardage
MESH BACK													
EPM21	23	28	43.75	18.5	26	20	20	36	21	-	0.9	-	0.4
EPM24	26	28	43.75	18.5	26	23	20	38	23	-	0.9	-	0.4
UPHOLSTERED BACK													
EPU21	23	28	43.75	18.5	26	20	20	40	21	2.1	0.9	2.0	0.4
EPU24	26	28	43.75	18.5	26	23	20	44	23	2.1	0.9	2.0	0.4
EPU30	32	28	43.75	18.5	26	29	20	50	28	3.1	0.9	2.2	0.4







ORDERING NOTES:

Multiple yardage requirements for Patient back Start, Center and End units, please refer to [page 10](#).

Closed Arm Panels (per chair) - please add the following up charges for closed arm panels.

Fabric Grades	(COM) 1	2	(COL) 3	4	5	6	7	Leather 8	9	COM
Closed Arm Panel (1 arm)	208	224	238	267	294	321	350	379	435	0.4
Closed Arm Panels (2 arms)	418	448	477	531	588	643	699	757	869	0.8
Fully Closed Arm (1 arm)	627	669	710	796	879	963	1048	1135	1304	1.5
Fully Closed Arm (2 arms)	835	890	948	1061	1172	1285	1335	1510	1736	3

SOLIS BEHAVIORAL HEALTH | START & CENTER PATIENT UNITS






DESCRIPTION/MODEL	COM		COL			FABRIC GRADES			LEATHER		
	1	2	3	4	5	6	7	8	9		
 <p>START</p> <p>21" Open Arm Start Patient Unit, Mesh Back</p> <p>SOL2-SPBHM21OPU Urethane</p> <p>SOL2-SPBHM21OPW Beech</p> <p>21" Open Arm Start Patient Unit, Upholstered Back</p> <p>SOL2-SPBHU21OPU Urethane</p> <p>SOL2-SPBHU21OPW Beech</p>	1164	1241	1272	1335	1398	1461	1526	1589	1688		
	1331	1360	1393	1456	1519	1583	1644	1709	1808		
	1265	1331	1396	1533	1664	1801	1932	2064	2333		
	1384	1451	1518	1653	1782	1921	2054	2186	2453		
	<hr/>										
	 <p>24" Open Arm Start Patient Unit, Mesh Back</p> <p>SOL2-SPBHM24OPU Urethane</p> <p>SOL2-SPBHM24OPW Beech</p> <p>24" Open Arm Start Patient Unit, Upholstered Back</p> <p>SOL2-SPBHU24OPU Urethane</p> <p>SOL2-SPBHU24OPW Beech</p>	1247	1281	1311	1374	1439	1503	1565	1629	1727	
1370		1401	1431	1494	1559	1622	1686	1748	1845		
1305		1372	1439	1570	1705	1839	1974	2108	2377		
1423		1492	1559	1692	1825	1959	2092	2229	2496		
<hr/>											
 <p>30" Open Arm Start Patient Unit, Upholstered Back</p> <p>SOL2-SPBHU30OPU Urethane</p> <p>SOL2-SPBHU30OPW Beech</p>		1640	1741	1837	2033	2234	2431	2629	2824	3220	
	1760	1860	1957	2155	2354	2552	2746	2946	3342		
	<hr/>										
	<p>CENTER</p>  <p>21" Open Arm Center Patient Unit, Mesh Back</p> <p>SOL2-CPBHM21OPU Urethane</p> <p>SOL2-CPBHM21OPW Beech</p> <p>21" Open Arm Center Patient Unit, Upholstered Back</p> <p>SOL2-CPBHU21OPU Urethane</p> <p>SOL2-CPBHU21OPW Beech</p>	1111	1142	1173	1239	1303	1363	1428	1491	1589	
		1171	1203	1236	1298	1360	1423	1487	1552	1647	
		1161	1228	1294	1428	1562	1693	1832	1964	2232	
1220		1288	1355	1487	1622	1753	1890	2024	2293		
<hr/>											
 <p>24" Open Arm Urethane Cap Center Patient Unit, Mesh Back</p> <p>SOL2-CPBHM24OPU Urethane</p> <p>SOL2-CPBHM24OPW Beech</p> <p>24" Open Arm Center Patient Unit, Upholstered Back</p> <p>SOL2-CPBHU24OPU Urethane</p> <p>SOL2-CPBHU24OPW Beech</p>		1138	1169	1201	1265	1328	1390	1453	1515	1613	
	1198	1229	1262	1323	1387	1451	1513	1578	1672		
	1187	1253	1319	1456	1589	1723	1856	1990	2257		
	1246	1314	1381	1515	1647	1781	1915	2053	2319		
	<hr/>										
	 <p>30" Open Arm Center Patient Unit, Upholstered Back</p> <p>SOL2-CPBHU30OPU Urethane</p> <p>SOL2-CPBHU30OPW Beech</p>	1506	1606	1703	1899	2096	2295	2493	2692	3087	
1566		1666	1764	1960	2158	2355	2554	2751	3145		

Solis Behavioral Health guest chairs have the option of Closed or Fully Closed arms, change the last 3 letters of the model number to the required arm type from the Product Code Key below and add the upcharge on page 44.

PRODUCT CODE KEY

Line	Series	Chair Type	Back Type	Size	Arm Type
SOL	2	SG	U	21	OPW
Solis	Chair	Start Unit Guest Multiple Seating	Upholstered Back		Open Arm - Wood Arm
		CG	M	24	OPU
		Center Unit Guest Multiple Seating	Mesh Back 21" & 24" Only		Open Arm Urethane Arm
		EG		30	CLW
		End Unit Guest Multiple Seating			Closed Arm - Wood
				44	CLU
					Closed Arm - Urethane
					FCW
					Fully Closed Arm - Wood
					FCU
					Fully Closed Arm - Urethane

SOLIS BEHAVIORAL HEALTH | END PATIENT UNITS

DESCRIPTION/MODEL	COM		COL			FABRIC GRADES				LEATHER	
	1	2	3	4	5	6	7	8	9		
 21" Open Arm End Unit, Mesh Back SOL2-EPBHM21OPU Urethane SOL2-EPBHM21OPW Beech	1111	1142	1173	1239	1303	1363	1428	1491	1589		
	1171	1203	1236	1298	1360	1423	1487	1552	1647		
 21" Open Arm End Unit, Upholstered Back SOL2-EPBHU21OPU Urethane SOL2-EPBHU21OPW Beech	1161	1228	1294	1428	1562	1693	1832	1964	2232		
	1220	1288	1355	1487	1622	1753	1890	2024	2293		
 24" Open Arm Urethane Cap End Unit, Mesh Back SOL2-EPBHM24OPU Urethane SOL2-EPBHM24OPW Beech	1138	1169	1201	1265	1328	1390	1453	1515	1613		
	1198	1229	1262	1323	1387	1451	1513	1578	1672		
 24" Open Arm End Unit, Upholstered Back SOL2-EPBHU24OPU Urethane SOL2-EPBHU24OPW Beech	1187	1253	1319	1456	1589	1723	1856	1990	2257		
	1246	1314	1381	1515	1647	1781	1915	2053	2319		
 30" Open Arm End Unit, Upholstered Back SOL2-EPBHU30OPU Urethane SOL2-EPBHU30OPW Beech	1506	1606	1703	1899	2096	2295	2493	2692	3087		
	1566	1666	1764	1960	2158	2355	2554	2751	3145		

ORDERING NOTES:

Complete Mesh backs (21" & 24") can be ordered and field replaced.

The standard **Solis Frame Color** is Silver Metallic. Additional frame colors are available for an upcharge of **\$64 list** per arm frame pair, please see **page 24** for color selection and required ordering quantities. Silver metallic frames are available with an anti-microbial finish for an upcharge of **\$64 list** per arm frame pair or table.

Solis Option Upcharges	\$ List	\$ List
CAL 133 & Moisture Barrier (per yard)	64	Non-Marring Glide
Removable Seat Cover (per seat)	80	Kinetic Back option
21" & 24" - Removeable Back Covers (per back)	58	Maple Arm upgrade per arm (add to beech price)
30" - Removable Back Cover (per back)	80	
Combination Upholstery - dual fabrics	33	
Combination Upholstery -Three fabrics	64	

Solis Behavioral Health Option Upcharges \$ List





Plywood Seat / No Springs	121	Weight Shield (to min 80lbs) - 21" Uph.	408
Sled Base	265	Weight Shield (to min 80lbs) - 21" Mesh	486
Anchor to Floor (Sleigh base only)	359	Weight Shield (to min 80lbs) - 24" Uph.	337
21" Tamper- Resistant Splashguard	157	Weight Shield (to min 80lbs) - 24" Mesh	412
24" Tamper- Resistant Splashguard	165	Weight Shield (to min 80lbs) - 30" Uph.	180
30" Tamper- Resistant Splashguard	340		

Solis Behavioral Health guest chairs have the option of Closed or Fully Closed arms, change the last 3 letters of the model number to the required arm type from the Product Code Key below and add the upcharge on page 430.






PRODUCT CODE KEY

Line	Series	Chair Type	Back Type	Size	Arm Type
SOL	2	SG	U	21	OPW
Solis	Chair	Start Unit Guest Multiple Seating	Upholstered Back		Open Arm -Wood Arm
		CG	M	24	OPU
		Center Unit Guest Multiple Seating	Mesh Back 21" & 24" Only		Open Arm Urethane Arm
		EG		30	CLW
		End Unit Guest Multiple Seating			Closed Arm - Wood
				44	CLU
					Closed Arm - Urethane
					FCW
					Fully Closed Arm - Wood
					FCU
					Fully Closed Arm - Urethane


SOLIS BEHAVIORAL HEALTH | REPLACEMENT COMPONENTS

Description	Model	COM		COL			FABRIC GRADES			LEATHER			Yardage	Weight	Cube	
		1	2	3	4	5	6	7	8	9						
Guest 	21" Replacement Behavioral Health Guest Upholstered Backs															
	SOL2-RBBHGU21	508	555	598	665	740	807	883	977	1067	1.5	14	2.7			
	21" Replacement Behavioral Health Guest Mesh Backs															
	SOL2-RBBHGM21	441											10	2.7		
	24" Replacement Behavioral Health Guest Upholstered Backs															
	SOL2-RBBHGU24	529	571	620	687	763	829	904	995	1089	1.5	15	2.8			
	24" Replacement Behavioral Health Guest Mesh Backs															
	SOL2-RBBHGM24	468											11	2.8		
	30" Replacement Behavioral Health Guest Upholstered Backs															
	SOL2-RBBHGU30	597	652	705	780	905	940	1027	1135	1241	1.6	19	3.4			
	44" Replacement Behavioral Health Guest Upholstered Backs															
	SOL2-RBBHGU44	774	824	879	956	1039	1117	1202	1309	1416	2.25	28	4.8			
Patient 	21" Replacement Behavioral Health Patient Upholstered Backs															
	SOL2-RBBHPU21	628	695	764	856	961	1059	1165	1298	1433	2.0	21	3.8			
	21" Replacement Behavioral Health Patient Mesh Backs															
	SOL2-RBBHPM21	478											15	3.8		
	24" Replacement Behavioral Health Patient Upholstered Backs															
	SOL2-RBBHPU24	662	729	796	889	997	1090	1198	1334	1466	2.0	21	3.8			
	24" Replacement Behavioral Health Patient Mesh Backs															
	SOL2-RBBHPM24	508											17	3.8		
	30" Replacement Behavioral Health Patient Upholstered Backs															
	SOL2-RBBHPU30	834	921	1009	1131	1270	1391	1533	1706	1881	2.2	24	4.8			
	Guest 	21" Replacement Behavioral Health Guest Upholstered Back Cover														
		SOL2-RBCBHGU21	155	202	246	313	389	455	531	624	717	1.5	2	.8		
21" Replacement Behavioral Health Guest Mesh Back Cover																
SOL2-RBCBHGM21		191											2	.8		
24" Replacement Behavioral Health Guest Upholstered Back Cover																
SOL2-RBCBHGU24		155	202	247	313	389	455	532	624	720	1.5	2.3	.8			
24" Replacement Behavioral Health Guest Mesh Back Cover																
SOL2-RBCBHGM24		232											2.3	.8		
30" Replacement Behavioral Health Guest Upholstered Back Cover																
SOL2-RBCBHGU30		169	224	274	350	435	512	597	717	811	1.6	2.6	.8			
44" Replacement Behavioral Health Guest Upholstered Back Cover																
SOL2-RBCBHGU44		178	232	284	362	448	518	606	715	821	2.25	3.5	.8			
Patient 	21" Replacement Behavioral Health Patient Upholstered Back Cover															
	SOL2-RBCBHPU21	199	267	334	427	535	628	735	870	1003	2.0	2.5	.8			
	21" Replacement Behavioral Health Patient Mesh Back Cover															
	SOL2-RBCBHPM21	212											2.5	.8		
	24" Replacement Behavioral Health Patient Upholstered Back Cover															
	SOL2-RBCBHPU24	201	267	334	427	536	628	735	870	1003	2.0	2.7	.8			
	24" Replacement Behavioral Health Patient Mesh Back Cover															
	SOL2-RBCBHPM24	250											2.7	.8		
	30" Replacement Behavioral Health Patient Upholstered Back Cover															
	SOL2-RBCBHPU30	244	333	420	541	679	804	941	1117	1290	2.2	3	.8			

SOLIS BEHAVIORAL HEALTH | REPLACEMENT COMPONENTS

Description	Model	COM			COL			FABRIC GRADES			LEATHER			Yardage	Weight	Cube
		1	2	3	4	5	6	7	8	9						
 Seat	21" Replacement Behavioral Health Seat SOL2-RSBH21	321	352	382	424	473	514	562	624	686	.9	9	2.7			
	24" Replacement Behavioral Health Seat SOL2-RSBH24	358	388	418	458	510	548	598	659	720	.9	10	2.7			
	30" Replacement Behavioral Health Seat SOL2-RSBH30	405	434	464	509	546	597	644	705	765	.9	12	3.4			
	44" Replacement Behavioral Health Seat SOL2-RSBH44	538	576	613	665	723	777	834	909	983	.9	14	4.8			
 No Spring Seat	21" Replacement Behavioral Health No Spring Seat SOL2-RSBH21NS	443	473	502	543	592	634	685	744	806	.9	9	2.7			
	24" Replacement Behavioral Health No Spring Seat SOL2-RSBH24NS	479	510	538	582	628	670	720	780	840	.9	10	2.7			
	30" Replacement Behavioral Health No Spring Seat SOL2-RSBH30NS	522	556	585	627	667	717	765	824	886	.9	12	3.4			
	44" Replacement Behavioral Health No Spring Seat SOL2-RSBH44NS	659	696	732	784	844	895	955	1030	1103	.9	12	3.4			
 Seat Covers	21" Replacement Behavioral Health Seat Cover SOL2-RSBHC21	108	138	169	210	259	301	348	409	470	1.0	1.6	.8			
	24" Replacement Behavioral Health Seat Cover SOL2-RSBHC24	111	140	170	212	260	302	350	410	471	1.0	1.7	.8			
	30" Replacement Guest, Patient & Easy Access Seat Cover SOL2-RSBHC30	119	141	179	223	270	312	362	422	481	1.0	2	.8			
	44" Replacement Behavioral Health Seat Cover SOL2-RSBHC44	140	178	213	267	326	376	434	510	583	1.0	2.5	.8			
 Replacement Closed Arm Replacement Lower Closed Arm Panel	SOL2-RCA	195	207	220	238	259	276	297	321	345	.8	6	.9			
	SOL2-RCAB	137	151	163	182	202	218	240	265	291	.8	6	.9			
 Bottom Staple Cover/Shield Weighted Shield Tamper-Resistant Splashguard	SOL2-RBC21	82										2	0.8			
	SOL2-RBC24	85										2.3	0.8			
	SOL2-RBC30	95										2.6	0.8			
	SOL2-RBC44	105										3.5	0.8			
	SOL2-RWSU21	408										25	1			
	SOL2-RWSM21	486										25	1			
	SOL2-RWSU24	337										25	1			
	SOL2-RWSM24	412										25	1			
	SOL2-RWSU30	180										31	1			
	SOL2-RWSU44	171										44	1			
SOL2-RSGBH21	259										1	.3				
SOL2-RSGBH24	269										2	.4				
SOL2-RSGBH30	464										3	.5				
SOL2-RSGBH44	502										4	.6				

SOLIS BEHAVIORAL HEALTH | REPLACEMENT FRAMES

Description	Model	Price	Weight	Cubes
	Tamper- Resistant Side Frame Assembly - Start		9	1.5
	SOL2-RSFABHS - Urethane	178		
	- Beech	357		
	Tamper- Resistant Side Frame Assembly - Center		9	1.5
	SOL2-RSFABHC - Urethane	178		
	- Beech	357		
	Tamper- Resistant Side Frame Assembly - End		9	1.5
	SOL2-RSFABHE - Urethane	178		
	- Beech	357		
	Sleigh Base Side Frame Assembly - Start		9	1.5
SOL2-RSFABHSSB - Urethane	585			
- Beech	764			
Sleigh Base Side Frame Assembly - Center		9	1.5	
SOL2-RSFABHCSB - Urethane	585			
- Beech	764			
Sleigh Base Side Frame Assembly - End		9	1.5	
SOL2-RSFABHESB - Urethane	585			
- Beech	764			
Sleigh Base Fully Closed Side Frame - Start		9	1.5	
SOL2-RSFABHSFC - Urethane	585			
- Beech	764			
Sleigh Base Fully Closed Side Frame - Center		9	1.5	
SOL2-RSFABHCFC - Urethane	585			
- Beech	764			
Sleigh Base Fully Closed Side Frame - End		9	1.5	
SOL2-RSFABHEFC - Urethane	585			
- Beech	764			


Maple arm side frames are available for an upcharge of \$74 list per arm, please see [page 63](#) for finish selection.

Tamper- Resist Tool Kit		143		
SOL2-BHTK				

LEED CI CREDITS



MATERIAL CONTENT:



PRE-CONSUMER
 RECYCLED CONTENT = 54.33%

POST-CONSUMER
 RECYCLED CONTENT = 16.83%

CONTRIBUTES TO

CREDIT 2.1 - 2.2	Construction Waste Management	1-2 point(s)
CREDIT 3.3	Resource Reuse	1 point
CREDIT 4.1	Recycled Content	1 point
CREDIT 4.2	Recycled Content	1 point
CREDIT 4.5	Low Emitting Materials, Systems & Seating	1 point
CREDIT 5.1	Regional Materials*	1 point
CREDIT 7	Certified Wood (MUST BE REQUESTED)	1 point(s)

*This credit is only applicable if in total 20% of the combined value of the procurement of construction materials and in the furniture are manufactured within a radius of 500 miles. This credit will apply if the installation of the finished product occurs within 500 miles of Kitchener, Ontario.

level® CERTIFICATION, AIR EMISSIONS AND FSC® CERTIFICATION



level® CERTIFICATION

BIFMA's e3 Furniture Sustainability Standard is a voluntary, multi-attribute standard that measures the degree of sustainability of furniture. This standard evaluates product and company environmental attributes and compliance systems in a wide range of elements which include Materials, Energy & Atmosphere, Human & Ecosystem Health and Social Responsibility. Solis products have earned level®, BIFMA's sustainability certification program for furniture, certification through third-party verification against the e3 standard.



AIR-EMISSIONS

All Solis products are supplied air-emissions certified. Contact customer service for information.

FSC®

In 2005, Krug received Forest Stewardship Council® (FSC®) Chain-of-Custody certification for our manufacturing facilities. The FSC® Chain-of-Custody tracks certified wood from seedling to final sale. It verifies that the material for our FSC® certified products only come from well-managed, FSC®-certified forests and other controlled sources. FSC® is dedicated to the promotion of responsible forest management worldwide helping to take care of forests for future generations. Solis and other Krug products can be specified with FSC® Certification. Contact customer service for further information, pricing and lead times.

Architects, designers, and building professionals can specify FSC®-certified products in order to achieve a point from the US. Green Building Council's Leadership in Energy and Environmental Design (LEED) Rating System.

STANDARD FINISHES

Solid Beech & Maple edges with Veneer tops. For a complete list of standard wood finishes, please see **page 62**. Solis tables are available in 22 standard finishes.

LAMINATE AND POLYMER EDGE

Solis tables are available in laminates with wood or laminates with Polymer edge. See **page 62** for laminate information.

METAL FINISHES

Silver Metallic Standard - No Upcharge
 Silver Metallic frames are available with an anti-microbial finish for an upcharge of **\$64 list** per arm frame pair or table. Additional Frame Finishes are available for an upcharge of **\$64 list** per seat/ table.
 Available colors are: • White • Parchment • Sand • Taupe • Warm Grey • Cool Grey • Black

For all metal finishes other than Silver Metallic Standard, there is a minimum order quantity of 30 units per color. The anti-microbial finish is included in the additional finish up-charge. Upcharges for order quantities less than 30 units per color or custom metal finishes, please contact Customer Service to obtain a quote.

[View Solis images | www.krug.ca](http://www.krug.ca)

ORDERING NOTES:

Linking tables can be ordered in conjunction with any of the Krug Solis Multiple Seating. Linking tables are connected to the Multiple Seating via U-Shaped brackets. The design of the tables for Solis Multiple Seating allows for any table to be very easily added or moved to a new position within the configuration - or completely replaced - after the product has been first installed. The attachment of the tables is designed so that they can be readily be taken out of the configuration without any defacing of the adjoining seat frames.


Linking tables also feature a universal, non-handed design:

They can be moved to reverse position in almost every configuration, providing a high level of flexibility for reconfiguring.








Please note Solis Plastic Laminate Linking Tables are not available on *KrugExpress*.

Wood Tops with Wood Edges are available on *KrugExpress* but with a minimum order requirement of 5 tables per order.

A drawing showing the configuration of the multiple seating and tables are required with each purchase order.



SOLIS | LINKING TABLES

DESCRIPTION/MODEL	Beech	Maple	Laminate with Wood Edge	Laminate with Polymer Edge	W	D	Weight	Cubes
 <p>Center Square Table SOL4-LKI-22-22</p>	617	647	752	591	22	22	18	1.5
 <p>End Square Table SOL4-LKE-22-22</p>	658	693	803	634	22	22	20	1.5
 <p>Curvilinear Connector Table 45° with flat edge SOL4-LKCRF45</p>	598	630	730	591	27.5	27.5	21	2.2
 <p>Curvilinear Connector Table 45° SOL4-LKCRR45</p>	628	662	766	622	27.5	27.5	21	2.2
 <p>Curvilinear Connector Table 90° SOL4-LKCR90</p>	708	746	866	706	30	30	27	2.2
 <p>Curvilinear Connector Table 90° with flat edge SOL4-LKCRF90</p>	699	738	852	695	30	30	29	2.2
 <p>Rectilinear Corner Connector Table 90° SOL4-LKCSF90</p>	785	829	958	739	30	30	32	2.2

ORDERING NOTES:

Linking tables can be ordered in conjunction with any of the Solis Multiple Seating. Linking tables are connected to the Multiple Seating via U-Shaped brackets.









Rectilinear Corner Connector table 90° include a support leg in the outer corner.

When specifying Linking Tables please ensure that each unit has legs on either side of the table.

Please note Solis Plastic Laminate Linking Tables are not available on *KrugExpress*. Wood Tops with Wood Edges are available on *KrugExpress* but with a minimum order requirement of 5 tables per order.

A drawing showing the configuration of the multiple seating and tables is required with each purchase order.

SIN 339113H - Hospital Geriatric Chairs & Lounge
SOLIS | FREE STANDING TABLES

DESCRIPTION/MODEL	Beech	Maple	Laminate with Wood Edge	Laminate with Polymer Edge	W	D	H	Weight	Cubes
 Square Tables SOL4-22-22-16	583	613	708	552	22	22	16	26	5
 SOL4-42-22-16	809	852	988	759	42	22	16	46	9
 SOL4-22-22-21	588	618	716	558	22	22	21	28	7
<hr/>									
 Circular Tables SOL4-18D-16	515	542	630	491	18 Diameter	-	16	20	3
 SOL4-18D-21	532	560	648	508	18 Diameter	-	21	22	4
 SOL4-24D-16	544	576	666	530	24 Diameter	-	16	32	5
 SOL4-24D-21	588	618	716	568	24 Diameter	-	21	35	7
 SOL4-36D-16	830	873	1011	844	36 Diameter	-	16	43	12

GENERAL INFORMATION

Terms and Conditions

Net 30 days on approved credit. A late payment charge of 1% per month will be applied on overdue invoices. This charge will be pro-rated to the number of days past 30 days that the invoice is overdue. All applicable sales taxes are extra. Distribution of this price list does not in itself constitute an offer to sell. Orders can be received only from authorized Krug dealers. Acceptance of any order and terms of sale may be established at the discretion of Krug. Deposits are required on orders received from new accounts as well as on large or special orders. Krug reserves the right to discontinue designs, or to change designs, construction, prices, or materials without notice.

Contact Information

Phone: 1.888.578.KRUG (5784) | Fax: 1.519.748.5177

Purchase Order Fax: 1.888.236.4783

Purchase Order E-mail: orders@krug.ca

Web: www.krug.ca E-mail: solutions@krug.ca

Customer Service Hours

Please note customer service hours are:

8:30 am to 5:00 pm est

Customer Satisfaction

It is the primary goal of Krug and our staff to ensure the complete satisfaction of our customers with our products and performance. If a problem arises with a Krug product after the expiration of the limited warranty period, Krug will exercise its best efforts to achieve the satisfaction of the customer in a manner that is fair to all concerned.

Order Acknowledgments

Each order will be acknowledged via e-mail or fax. This acknowledgment is the final agreement between Krug and the customer, superseding all previous communications regarding the purchase order. Where there is a discrepancy on a purchase order between a product code and a description, Krug will make every effort to resolve the discrepancy, but will be ruled by the product code ordered. Please check all acknowledgments for accuracy, and advise Krug of any discrepancies with a purchase order.

Order Cancellation

Krug reserves the right to not accept or allow cancellation of orders. All products are manufactured on a custom-made, make-to-order basis, and the purchasing, engineering and production of orders begins shortly after order placement - and the customer purchase order is a contract that authorizes Krug to manufacture the products. Acceptance of order cancellation (or partial cancellation) is solely at the discretion of Krug, and is dependent on the extent to which engineering, purchasing and manufacturing has been initiated by the time cancellation is requested. No order cancellations (partial or otherwise) are allowable more than 4 weeks from date of order placement (as order production is unable to be terminated by that point), and full payment of the acknowledged order value is required for any orders cancelled after 4 weeks. Cancellations may be allowable in less than 4 weeks after order placement, depending on the extent to which manufacturing has been initiated. An acceptance of order cancellation requires that the purchaser agrees to make payment for all costs incurred to the point of acceptance of cancellation. Cancellation charges include all costs for purchase of dedicated material and components, engineering costs for non-standard products, and all costs for manufacturing completed to that point, as well as a \$367 net charge for processing of the original order and for processing of cancellation invoicing.

Pricing

Krug endeavors to ensure that all prices in this price list reflect accurately our current prices. However, errors do occur and will be rectified through notices to the field. Krug reserves the right to acknowledge pricing that may be different from the price list.

Storage Charges

Krug reserves the right to assess a nominal storage charge if a customer does not accept shipment of an order within a week of the ship date.

Warranty

Krug warrants the construction and the finish of all our products to be free from defects in materials and workmanship for the lifetime of their use. This warranty is applicable to products in use by their original purchaser. This warranty does not apply to components not manufactured by Krug including textiles, which are subject to the specific warranties of those manufacturers, if any. Textiles (fabric, leather, vinyl, or any other covering material) suppliers do not guarantee their products for durability and color fastness, and nor does Krug. Casters, mechanical and electrical components have a warranty of five years from the date of purchase. The Krug warranty does not apply to COM-specified materials, damage caused by a carrier other than Krug, or variation in wood finishes due to natural wood color variation. Krug cannot be held responsible for variations in fabric dye lots from order to order. All fabric is carefully inspected when it is received, but a degree of variation in color should be expected. Repairs or replacement of any defect covered under this warranty by Krug will be made, at our option and method, at no charge to the original purchaser during the warranty period. Krug's judgement is final and binding with respect to the nature or cause of defects or damage, and the necessity or manner of repair or replacement.

This warranty does not apply to defects or damage resulting from:

- normal wear and tear occurring with the use of the product
- negligence, misuse, excessive use, alteration, improper cleaning or repair
- substitution or use of incorrect or unauthorized components or material
- handling or installation that is incorrect, or that causes damage or defect
- damage incurred by a freight carrier other than Krug
- wearing of finishes and fabrics, and normal variations in materials (including dye lot variations)
- properties of natural materials, including wood and leather
- exposure to environments with uncontrolled temperature and humidity (products must be transported, stored and used in climate-controlled conditions)

Note, specific warranties for components and materials not manufactured by Krug:

Jordan Sleepers Heavy-Duty Mechanism, made with heavy gauge steel and minimal moving parts - is backed by a 5-year warranty on the mechanism itself, in addition to the lifetime warranty on the rest of the product. If it does become damaged or degraded, the mechanism can be field-replaced.

Juno and Trevisa Overbed Tables have a 2-year warranty.

Blanket Wrapping

Krug will blanket wrap larger seating orders at customer's request. Please indicate on your purchase order and contact Customer Service.

Export Packaging

Krug is pleased to provide the option for export packaging on all our products, to provide additional protection from damage. For shipments overseas, a quote for export packaging can be provided, based on the products to be ordered and the delivery destination - please contact Customer Service or Bids & Specification Support for more information and a quotation. KRUG is not responsible for shipment damage occurring on overseas shipments

Export Packaging is STRONGLY RECOMMENDED for:

- (A) all shipments outside of the lower 48 states and Canada.
- (B) all shipments that will be held in storage for an extended period prior to installation.

Important: Please note that Krug will not be responsible for damage claims on product shipped or stored in the above conditions but where export packaging has not been utilized.

Dimensions

Dimensions are in inches and approximate, and subject to change without notice. Contact Customer Service if dimensions are critical.

GENERAL INFORMATION

Freight Terms and Conditions

1. All product is shipped FOB the Krug factory. Freight is either pre-paid to the destination or not pre-paid, depending on established customer specific freight terms.

2. Docks at the selected delivery location must be equipped to handle a 53' trailer. If a dock is inadequate for delivery by Krug, Krug will re-deliver to another local location and any additional costs will be charged to the customer.

3. For all deliveries, it is understood that Krug or its agent is making a dock delivery only (equipped to handle a 53' trailer), and any further work of truck unloading, delivery beyond the dock, installation, and removal of packaging is not authorized or paid for by Krug.

4. Drop shipments to the installation site, and timed deliveries, are available on larger shipments (full truckloads or slightly less) at no additional charge. Drop shipments or timed deliveries for smaller shipments may not be available, or if available will require a surcharge. Deliveries on an after hours basis, or on weekends, or any other special requirements, may be subject to a surcharge. Location and contact information, and the requested time of delivery, is required at least one week prior to the acknowledged shipment date. If this information is not provided one week in advance, or if the location or time of the drop shipment is changed less than one week in advance, a surcharge may be applied, and/or the drop shipment may not be scheduled. For deliveries requested Monday to Thursday after 5:00 pm, please apply a surcharge of \$262/shipment. For deliveries requested Monday to Friday before 7:00 am, please apply a surcharge of \$262/shipment. For deliveries requested Friday (after 3:00 pm) or weekends, please apply a surcharge of \$525/shipment. (local times).

5. For all deliveries - whether to the Customer location or drop shipment - any circumstances that result in the delay of our carrier (including unsuitable receiving facilities, or facilities not open or available), service charges will be applied at the rate of \$125/hour. Where re-delivery is necessary because of these circumstances, the full cost of re-delivery will be charged. If Less Than Truck Load is delivering, one hour is allocated to unload. Any additional time required to unload after the first hour is \$125/hour. If a Truck Load is delivering the order, three hours is allocated to unload. Any additional time required to unload is \$125/hour. Direct deliveries to site for large orders are possible, (must exceed \$60,000 net), and accommodate 48 - 53' trailers. Krug is responsible for delivery to the approved delivery address. If an address change is required, this must be authorized by Krug 5 business days prior to ship date. Any additional delivery costs incurred after this time will be charged to the customer.

Product Strength and Durability Testing

All Krug products have been thoroughly tested, and exceed the testing requirements of ANSI/BIFMA seating standard. Specific test results and documentation are available on request.



Installation Support

For assistance please contact Technical Support at 1-888-578-5784 x216 or e-mail installationhelp@krug.ca and you will be directed to the appropriate installation support person.

Damaged Shipments

All Krug product is well engineered, carefully inspected, and expertly loaded onto our trucks at our Distribution Center. If you receive any damaged freight, we ask that you do not refuse the shipment. Krug is not responsible for damage to goods that occurs in transit or

storage. It is the purchaser and/or receiver's responsibility to examine the goods upon receipt and to notify Krug of any damages, overages or shortages. Any discrepancies should be noted on the Bill of Lading. The delivering carrier will not accept responsibility for shortages or damages if signed "clear". Notification of concealed damage claims must be made to Krug Distribution within 5 days of delivery, along with digital pictures if available. All product and packaging must be available for inspection. Krug liability ceases after 5 business days and Krug will not be responsible for concealed damages if shipments are left unopened. Krug is not responsible for the condition of product that is stored or installed in an environment where temperature and humidity are not controlled.

Field Product Report Authorization

Krug's written authorization, in the form of an FPR number, must be obtained prior to incurring charges of any kind if Krug is expected to pay these charges. This includes authorization for returns, field repairs and replacements, post field repairs, installation and delivery charges. Krug reserves the right to have its representative inspect product related to any request for such authorizations, prior to that authorization being provided. Deductions from invoices paid for any charges to Krug, without prior written authorization in the form of an FPR, will not be accepted. Digital photographs may be required to complete the FPR process.

Returns

No merchandise may be returned without Krug's prior written consent. In the event of an authorized return, a Field Product Report (FPR) number will be issued, and a restocking charge will apply. Return transportation charges must be prepaid. Unauthorized returns will not be accepted and will be returned freight collect. All merchandise being returned must be properly packaged in its original or comparable replacement packaging to ensure protection of the product during handling and transportation. Returns on orders duplicated by the customer must be received in their original packaging to be accepted. Product being returned where Krug has authorized its liability for replacement or repair will be thoroughly inspected on its return, and the results compared to the reason for the return stated on the FPR. Any discrepancies, such as additional damage, signs of usage, missing parts, etc., will result in an adjustment to the amount of credit issued.

Custom Capabilities

Over 15% of our orders involve some type of custom work, and we invite our customers to make use of our extensive capabilities.

These include:

- 1) Dimensional customization of standard size products
- 2) Custom finishes
- 3) For larger orders, completely custom-designed products, as well as non-standard wood species can be specified.

Custom orders may require additional production lead times. Contact Engineering at the e-mail address engquotes@krug.ca.

Care and Maintenance Leather

Leather is a natural product and requires very little care during use. Most stains can be removed with a clean dry cloth. For stubborn spots and stains, use a mild non-detergent cleaner, rinse well and let air dry naturally. Do not use saddle soap, cleaning solvents, furniture polish, oils, varnish, abrasive cleaners, soaps or ammonia waters.

Fabric Upholstery

Professional upholstery cleaning is recommended.

Flammability Standards for Krug Textiles - Upholstery Program

- Passes State of California Technical Bulletin CAL 117-2013


KRUG TEXTILES - UPHOLSTERY FABRICS



Krug Textiles - Stocked Fabric Program

Grade 1


ARLO



308 MIDNIGHT



306 PETROL



908 CHARCOAL



93 SEAL



601 PEARL



84 NUTMEG



62 OATMEAL



90 LIMESTONE

FRANKLIN



47 CAMEL



3009 MIDNIGHT



67 FAWN



97 CINDER



94 METAL



909 BLACK



9004 CHARCOAL




308 PETROL



108 ORCHID

COMRADE



309 MIDNIGHT



84 TEAK




63 LINEN



24 ALPINE



905 IRON



601 SNOW



57 MARIGOLD



31 DUCK EGG

FELICITY



601 IVORY



305 SKY



603 TAUPE



93 COAL



405 HENNA



64 PUTTY



62 FAWN



36 BLUEBERRY

Krug Textiles - Stocked Fabric Program

Grade 2

GRADDY



25 CAPER




31 SKY




604 FLAX



901 CHAR



93 GRAY



34 SLATE



84 TEAK



98 NICKLE


YATES




84 BIRCH




44 CLAY



87 TAUPE



25 JUNIPER



305 INDIGO



109 CRANBERRY



803 TOAST



92 ZINC



91 SILVER



908 CHARCOAL

MCCOY



608 TUNDRA



601 CREME



908 CHARCOAL




62 COPPER



108 CORDOVAN



32 ROBIN'S EGG




94 MERCURY



84 BARK


ORIS




908 DOMINO



604 BARK



601 CREAM



306 DELFT




902 ZINC



305 MIDNIGHT



64 PUTTY



205 CHARTREUSE


KRUG TEXTILES - UPHOLSTERY FABRICS




Krug Textiles - Stocked Fabric Program

Grade 3


MORITZ




205 SPEARMINT



61 OYSTER




306 CADET




104 MULBERRY



31 AEGEAN



9008 CHARCOAL




82 CLAY



304 CAPRI

LORENZO



306 INDIGO



24 ALPINE




64 LINEN



91 FLANNEL




32 MIST



601 CREAM



106 HENNA



604 STUCCO

BISCOTTI



302 CAPRI



45 SPICE



61 DESERT



91 GRANITE

INTRIGUE



601 OYSTER



27 OLIVE



4003 OCHRE



908 CHARCOAL



3009 MIDNIGHT



805 PECAN



608 STUCCO




605 STRAW

Krug Textiles - Faux Leather Program - Grade 2



Krug Textiles - Leather Program - Grade 8

Please contact Customer Service for specific information on leathers, available colors and lead times.



Krug Textiles - Cut fabric NET price per yard

Grade 1	\$22
Grade 2	\$34
Grade 3	\$46

LATEX FREE

Krug products are made with latex-free materials to prevent the allergic reaction that latex causes in some people.

CUSTOMER'S OWN MATERIAL - C.O.M.

Customer's Own Material (COM/COL)

COM/COL must be received three weeks prior to the acknowledged ship date. Orders with COM/COL not received by the required deadline will be delayed. A description of the upholstery cover, including supplier name, pattern name, upholstery cover name and color number must be included with the purchase order.

COM/COL testing requires 3 business days and samples are to be directed to Customer Service. The customer has the option of providing the sample COM/COL before, at time of order, or once the sample COM/COL is received. If the customer does not send a sample for approval in advance of sending actual material, Krug will not be responsible for the cost of any upholstery cover or other material that it determines to be unsuitable for the product or our process.

When the COM/COL upholstery cover is received at Krug, it must be clearly identified with the upholstery cover name and color, and tagged with name of the Krug customer and purchase order number. Krug will inspect all COM/COL upholstery covers when received to determine if it will be suitable for upholstery. Where Krug feels that the upholstery cover or leather specified will compromise the quality or integrity of our products, customers will be contacted to direct these concerns. Further, Krug reserves the right to refuse to accept and use any COM upholstery covers or leathers that will compromise our products in any way that is unacceptable to Krug. Krug cannot assume responsibility for the durability or tailoring quality of customer's own material.

Yardage specified in this price guide is approximate. In the case of multiple product orders, multiply the number of items by the COM yardage specified to determine upholstery cover required, unless otherwise indicated. Additional yardage may be needed if the material is less than 54" wide, or patterned or striped and requires matching. All COMs are cut "up the roll" unless otherwise stated by the customer. All striped upholstery covers will be applied vertically unless otherwise stated by the customer and after approval by Krug. Krug will not be responsible for directional or positional problems with its application of COM material, unless it has been provided with explicit instructions by the customer. Special instructions should be sent to Krug Customer Service, including a sample (or photocopy) of the upholstery cover. Krug is not responsible for instructions sent with the upholstery cover rolls, or for the method of upholstery if no instructions have been provided.

Price increases and freight charges to COM/COL acquired on the customer's behalf will be passed onto the customer.

Application of Directional Upholstery cover

Some COM upholstery covers will be considered directional by Krug even though they are not considered directional by the supplier. All COMs are automatically cut "up the roll" unless otherwise stated by the customer (please see below).



Standard-Cut
"up the roll"



Non-Standard-Cut
across the roll "railroad"

COM/COL Shipping Procedures

For seating COM/COL upholstery covers, please send upholstery covers to:

Krug Inc.
111 Ahrens Street
Kitchener, Ontario
Canada N2H 4C2

Attention: RECEIVER

COM/COL orders cannot be scheduled into production until the upholstery cover has arrived and inspection is complete.

All packages must be clearly marked

"For Customs Clearance by Willson International Custom Brokers".

According to the North American Free Trade Agreement (NAFTA), goods shipped between the United States and Canada can qualify for exemption from all duties, or for a reduction in duties, if the goods can be proven to originate in either the United States, Canada or Mexico.

Canada Customs requires that a [NAFTA Certificate of Origin](#) and a [Commercial Invoice](#) be completed and sent with the upholstery cover shipment. The Commercial Invoice must clearly state the description of the upholstery cover, the selling price, the make-up or content, and the purchaser. The absence of these two documents will delay the shipments at the U.S./Canada border, thereby potentially delaying the customer order. If the total value of the shipment is less than \$1200 U.S., Customs will accept a Low Value Statement of Origin in place of the NAFTA Certificate of Origin. The Low Value Statement must be signed by a representative of the exporting company. This statement may either be included on the commercial invoice or attached to the invoice. Krug is happy to answer any questions or concerns about COM/COL shipping procedures and the required documents.

CAL 133 & Moisture Barrier

California Technical Bulletin 133 is a flammability test for seating. Krug offers a compliance method which, in combination with non-flammable upholstery covers, may enable the products to meet certification requirements for this test. This process at the same time also provides the products with a Moisture Barrier - a treatment that helps to prevent the passage of liquids and moisture to inside of upholstered components - thereby conferring sanitary and anti-infection benefits. So when CAL 133 is specified, the product also automatically has a Moisture Barrier, and when a Moisture Barrier is specified, the product also features the compliance method and low flammability features of CAL 133.

The application of this upcharge and the compliance method does not mean that the specific configuration of product and upholstery cover are tested and officially certified as being CAL 133 compliant. If official certification is required, Krug will provide this (through an independent certified testing laboratory) at a charge of \$917 per item, plus the cost of the product to be tested. Lead time for certification testing is typically 4-8 weeks. Krug assumes no responsibility for the testing of our products in combination with upholstery covers, or for the results of any testing conducted. Some specific configurations of product and upholstery have already been tested. Please contact Customer Service for additional information.

C.O.L. Yardage

To calculate C.O.L. yardage required, please use the following conversions based on COM yardage: Leather must be ordered in square footage.

- 17 square feet in a yard
- Approx. 3 yards in a hide
- Approx. 51 square feet in a hide
- Please use grade 3 pricing for COL

Upholstery Cover Yardage Calculation

To calculate yardage required for COM and other non-standard upholstery cover orders, please contact Krug Customer Service at 1.888.578.5784. Unless otherwise stated, upholstery cover rolls are assumed to be a minimum 54" wide. Please use the guide below to calculate the percentage of extra upholstery cover required to cover large repeats. The repeat is calculated by adding both the vertical and horizontal measurements together and then referring to the chart below for extra yardage required.

FABRIC	2"-14"		15"-19"		20"-27"		28"-36"	
	Plain	Repeat	Repeat	Repeat	Repeat	Repeat	Repeat	
54	0%	10%	15%	20%	25%			
53-50	16%	20%	25%	30%	35%			
48	16%	25%	30%	35%	40%			
45	40%	50%	55%	60%	65%			
36	50%	60%	65%	70%	75%			

GRADED-IN UPHOLSTERY PROGRAMS

Krug has partnered with several textile brands to grade in their offerings, designed to provide a wide range of upholstery selections for our seating products.

Upholstery pricing and availability is subject to change without notice. We grade this upholstery according to the pricing of the fabric suppliers - when their pricing changes, the Krug grade may change.

When placing an order, a Krug customer must specify the complete upholstery number, along with the appropriate Krug model number and finish. Krug will supply the complete product at the prices listed. Orders specifying graded-in upholstery cannot be cancelled once the upholstery has been ordered.

Upholstery Grades

To determine the price of a product for graded-in upholstery, use the reference lists located on Krug's website under - Products - Textiles, to view the upholstery grade (1-9). Krug is not responsible for the discontinuation of this upholstery. Please contact Customer Service for information on upholstery not listed.

When two upholstery selections are specified for use on seating, the higher grade upholstery price will apply to the order.

High Performance upholstery; Polyurethane, Vinyl or Crypton, is particularly suitable for healthcare and other intensive-use environments.

Upholstery Samples

If you require additional samples or memos for presentation, please contact fabric supplier directly.

Flammability Standards

- Tunnel Test Surface Ratings Class A rating
- Class 1 UFAC
- Passes State of California Technical Bulletin CAL 117-2013

Please contact fabric supplier directly for further flammability information pertaining to specific upholstery.

Special Conditions

Acknowledgments will give the estimated delivery date of the finished product. Some upholstery is imported, and availability may affect estimated delivery time. For large projects, please contact fabric supplier directly for availability of yardage.

KRUG EXPRESS PROGRAM

PROGRAM DETAILS

KrugExpress orders are ready to ship by the date acknowledged. Delivery and shipping schedules may result in actual shipping of orders at a later date. Statutory holidays and scheduled factory vacations may add to acknowledged lead times of *KrugExpress* orders. Unless otherwise specified on the order, the customer's standard method of shipping Krug products will be utilized.

Available factory capacity for *KrugExpress* is filled by orders received on a "first come, first serve" basis. If the normal *KrugExpress* lead time is not available for your order because available capacity has been filled, you will be immediately advised of the earliest available ready-to-ship date. Please consult your Customer Service representative in advance if you wish to confirm the specific lead time availability for a *KrugExpress* order.

Orders must be received by midnight of a given day for that day to be considered the official day the order is received. Order lead times are acknowledged from the date the order is received, but not including the date the order is received.

KrugExpress orders must be "clean" when received in order to be considered officially received on a given day, and lead times will be acknowledged from the date orders are determined to be "clean".

Changes to *KrugExpress* orders are not allowed under any circumstances.

Orders for product on *KrugExpress* must clearly state: "*KrugExpress*".

COM and graded-in upholstery is available on Krug Express. Orders are scheduled on Krug Express, and given the best available date, when the upholstery is received at Krug. Some conditions apply.

SEATING & OCCASIONAL TABLES PROGRAM

Orders for seating products on the *KrugExpress* program may be subject to quantity maximums. Please contact Krug Customer Service for more information.

Quantity maximums are dependent upon available capacity, in order to insure that we ship all orders on time. Please note that the CAL 133 option is not available on *KrugExpress*.

Only standard wood finishes are available for *KrugExpress* orders. Laminates are not available on *KrugExpress*.

Krug Express includes all Krug seating and occasional tables as well as Krug conference and casegood products to complement this seating offering.

SOLIS | FINISHES

WOOD FINISHES

Standard wood finishes are:

Finishes on Beech

Appalachian Cherry
 American Cherry
 Imperial Cherry
 Light Cherry
 Medium Cherry
 Natural Cherry
 Sable Cherry
 Standard Cherry
 Light Oak
 Harvest Oak
 Mahogany
 Mellow Oak
 Espresso
 Cordovan Walnut
 Natural Walnut
 Regular Walnut
 SilverGrey on Walnut
 Dark Walnut
 Clear Beech
 Medium Anigre

Finishes on Maple

Clear Maple
 Honey Maple
 Wheat Maple

PALETTE

Palette finishes available for applicable products.

Black
 White
 Soft Green
 Steel Blue
 Slate

NATURAL CHARACTERISTICS OF WOOD

Wood is a natural product with inherent color variations that will never be fully mitigated by the finishing process. Please anticipate variation in colors within a single unit, from piece to piece, and from Krug wood finish samples. If a very close match is required, a sample must be provided with the order and an upcharge will apply. Exact color matches are not possible.

Custom Wood Finishes

Add 10% list to your order for special finishes, minimum upcharge is \$600 list per finish per order. (For example, on all orders up to \$6000 list, an upcharge of \$600 will apply, on orders \$6000 and up add 10% list to your order.)

Special finish upcharges on seating products are calculated on a grade 1 value. For orders with special finishes, a sample that is a minimum 3” by 3” must be received with the order. Special finishes may add additional lead time to production schedules. Since wood is a natural product, some variations in grain, color and stain acceptance will occur. In our finishing processes, we try to minimize variations, but some variation between samples and finished goods should be anticipated.

Dual Finishes

Add 10% list per item if specifying dual finish.

Standard Wood Finishes

No upcharge will be applied when specifying a finish available as standard on one species onto maple seating and occasional tables. Clear finishes are not available on other species since they are a clear finish on top of the natural veneer color.

WOOD FINISHES TO MATCH STANDARD

LAMINATES

Willow on Beech
 Copper on Beech
 Shiraz Cherry on Beech
 Park Avenue Walnut on Beech
 Chocolate on Beech
 Nutmeg on Beech
 Portobello on Beech
 Ash on Beech
 Dune on Maple

LAMINATES

Krug’s in-stock Laminates are available in 17 different laminate selections. Please note that 4 of the colors (Gingerbread, Portobello, Ash and Willow) have textured finishes and may not be appropriate for use in patient areas due to infection control concerns. Minimum order quantities and extended lead times may apply for exotic laminate colors, please check with customer service. Polymer Edge will be selected to match the worksurface. Krug’s previous laminate in-stock program will be phased out as in-stock supply depletes. Please contact customer service for availability.

IN-STOCK LAMINATES

Wood Grain Laminates	High Pressure Laminate Supplier	Textured Wood Grain Laminates	High Pressure Laminate Supplier
Champagne	Tafisa T492CR	Gingerbread	Tafisa T556UR
Hardrock Maple	Formica 86992-58	Portobello	Tafisa T557UR
Dune	Tafisa T491CR	Ash	Tafisa T535AT
Copper	Tafisa T521CR	Willow	Tafisa T543AT
Shiraz Cherry	Tafisa T472CR		
Park Avenue Walnut	Wilsonart 7984-38	Solid Laminates	
Chocolate	Tafisa T498CR	Designer White	Wilsonart D354-60
Nutmeg	Tafisa T477CR	Platinum	Tafisa T202CR
Dark Walnut	Tafisa T469CR	Earth	Tafisa T767CR
		Charcoal	Tafisa T228CR


PHASE OUT LAMINATES

Almond - Black- Shadows - Edgewood Sycamore - Gunstock Walnut

Non-Stocked Laminates


For specific lead time and application questions, please contact Krug Customer Service for your requirement. Upcharges will be applicable for non-stocked laminates, depending on their cost. Non-stock laminates may require a minimum order quantity, please contact customer service. Stocked polymer edges only can be specified for use with non-stocked laminates or tops will be self-edged.

METAL FINISH - STANDARD




Silver Metallic

METAL FINISH -OPTIONAL (minimum order quantity see [page 3](#))



White



Parchment



Sand



Taupe



Warm Grey



Cool Grey



Black

URETHANE COLOR OPTIONS



Taupe



Grey



Black


SOLID SURFACE PROGRAM

The Solid Surface option provides an enhanced durability, protection and cleanability. It is available in 8 standard colors and is replaceable if it becomes damaged or degraded. See individual products for list upcharge chart.

GROUP GRADE A - WHITE




Glacier White



Cameo White

GROUP GRADE A - COLOR




Bisque




Linen

GROUP GRADE B




Antarctica




Savannah

GROUP GRADE C



Dove



Deep Night Sky



All products are air emissions certified and are available as FSC® certified

krug

solutions@krug.ca | www.krug.ca | 1.888.578.KRUG